

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1037679

Luminaire Tested: S124DS-B575DB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1037679
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-16)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DS-B575DB2750-4F0-XX-W2A-D_3500K
Description: Define 4 Direct Surface with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2370.0 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 24
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1037679

CATALOG NUMBER: S124DS-B575DB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1037679

CATALOG NUMBER: S124DS-B575DB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	95	95	95	95	95	95	92
1	105	100	95	91	102	97	93	89	91	88	84	86	83	80	81	79	77	77	77	77	74
2	95	86	79	73	92	84	77	71	79	73	68	74	70	66	70	67	63	63	63	63	60
3	87	75	67	60	83	73	65	59	69	62	57	65	60	55	62	57	53	53	53	53	50
4	79	66	57	50	76	65	56	49	61	54	48	58	52	47	55	49	45	45	45	45	43
5	73	59	50	43	70	58	49	42	55	47	41	52	45	40	49	44	39	39	39	39	37
6	67	53	44	37	64	52	43	37	49	42	36	47	40	35	45	39	34	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	30	28
8	58	44	35	29	56	43	35	29	41	33	28	39	32	28	37	31	27	27	27	27	25
9	54	40	32	26	52	39	31	26	38	30	25	36	29	25	34	29	24	24	24	24	22
10	50	37	29	24	49	36	29	23	35	28	23	33	27	23	32	26	22	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5668	5668	5668
5°	5696	5633	5678
10°	5672	5633	5685
15°	5632	5619	5671
20°	5566	5593	5661
25°	5491	5554	5638
30°	5409	5520	5615
35°	5316	5486	5618
40°	5245	5469	5627
45°	5135	5475	5674
50°	5047	5480	5738
55°	4957	5522	5810
60°	4811	5561	5954
65°	4656	5648	6144
70°	4473	5808	6440
75°	4219	6156	7064
80°	3982	7053	8443
85°	3864	10198	13108

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 87.5°

Luminance: 22695 cd/sqm

TEST NUMBER: P1037679

CATALOG NUMBER: S124DS-B575DB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	2.8
10°-20°	188.7	8.0
20°-30°	285.3	12.0
30°-40°	345.2	14.6
40°-50°	364.9	15.4
50°-60°	343.5	14.5
60°-70°	285.0	12.0
70°-80°	200.0	8.4
80°-90°	112.8	4.8
90°-100°	67.1	2.8
100°-110°	49.7	2.1
110°-120°	33.4	1.4
120°-130°	18.8	0.8
130°-140°	8.1	0.3
140°-150°	1.6	0.1
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	539.9	22.8
0°-40°	885.1	37.3
0°-60°	1593.5	67.2
0°-90°	2191.3	92.5
90°-120°	150.2	6.3
90°-150°	178.7	7.5
90°-180°	179.0	7.6
0°-180°	2370.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	695	695	695	695	695	
5°	696	694	688	694	694	66
15°	667	668	666	673	672	188
25°	610	615	617	626	627	281
35°	534	543	551	562	564	334
45°	445	460	475	488	492	344
55°	349	365	388	404	409	311
65°	241	266	293	312	318	239
75°	134	163	195	217	224	142
85°	41	74	109	132	140	43
90°	12	44	77	100	106	9
95°	10	36	68	89	96	8
105°	7	23	51	71	77	8
115°	5	12	37	54	59	5
125°	3	2	22	37	41	3
135°	2	2	7	20	24	1
145°	1	0	0	5	8	1
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1037679

CATALOG NUMBER: S124DS-B575DB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	695.1	695.1	695.1	695.1	695.1
2.5°	698.2	695.9	689.7	695.1	694.4
5°	695.9	693.6	688.1	694.4	693.6
7.5°	691.2	689.7	685.0	692.0	691.2
10°	685.0	684.2	680.3	687.4	686.6
12.5°	676.5	676.5	674.1	680.3	680.3
15°	667.1	667.9	665.6	672.6	671.8
17.5°	654.7	657.0	656.2	663.2	662.4
20°	641.4	643.8	644.5	652.3	652.3
22.5°	626.6	629.7	631.3	639.1	640.6
25°	610.3	615.0	617.3	625.9	626.6
27.5°	592.4	599.4	602.5	610.3	611.1
30°	574.5	580.7	586.2	594.7	596.3
32.5°	555.0	562.8	569.0	579.1	580.7
35°	534.0	543.3	551.1	562.0	564.4
37.5°	513.0	523.9	533.2	544.1	546.5
40°	492.7	502.9	513.8	525.4	528.6
42.5°	469.4	481.1	494.3	507.5	509.9
45°	445.3	460.1	474.8	488.1	492.0
47.5°	422.7	437.5	454.6	467.8	472.5
50°	397.8	414.9	432.0	447.6	452.3
52.5°	372.9	390.0	410.2	425.8	430.5
55°	348.7	365.1	388.4	404.0	408.7
57.5°	321.5	341.7	364.3	383.0	386.9
60°	295.0	315.3	341.0	358.9	365.1
62.5°	269.3	291.9	317.6	335.5	341.7
65°	241.3	266.2	292.7	312.1	318.4
67.5°	214.8	241.3	269.3	288.8	295.0
70°	187.6	214.1	243.6	264.7	270.1
72.5°	161.1	188.4	220.3	240.5	246.8
75°	133.9	162.7	195.4	217.2	224.2
77.5°	108.2	138.6	172.8	194.6	202.4
80°	84.8	116.0	150.2	173.6	179.8
82.5°	61.5	94.2	128.4	152.6	159.6
85°	41.3	74.0	109.0	132.3	140.1
87.5°	25.7	57.6	91.9	114.4	121.4
90°	12.5	43.6	77.1	99.6	105.9
92.5°	11.7	38.9	72.4	94.2	100.4
95°	10.1	35.8	67.7	88.7	95.7
97.5°	9.3	31.9	63.8	84.1	91.1
100°	8.6	28.8	59.2	80.2	85.6
102.5°	8.6	25.7	55.3	75.5	81.7
105°	7.0	22.6	51.4	70.8	77.1
107.5°	7.0	20.2	47.5	66.9	72.4
110°	6.2	17.1	44.4	62.3	68.5



TEST NUMBER: P1037679

CATALOG NUMBER: S124DS-B575DB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	5.4	14.8	40.5	57.6	63.8
115°	4.7	11.7	36.6	53.7	59.2
117.5°	4.7	9.3	32.7	49.0	55.3
120°	3.9	6.2	28.8	44.4	50.6
122.5°	3.9	3.9	24.9	40.5	45.9
125°	3.1	2.3	21.8	36.6	41.3
127.5°	3.1	2.3	17.9	31.9	37.4
130°	2.3	1.6	14.0	28.0	32.7
132.5°	2.3	1.6	10.9	24.1	28.8
135°	1.6	1.6	7.0	19.5	24.1
137.5°	1.6	0.8	3.9	15.6	19.5
140°	1.6	0.8	1.6	11.7	15.6
142.5°	0.8	0.8	0.0	8.6	11.7
145°	0.8	0.0	0.0	4.7	7.8
147.5°	0.8	0.0	0.0	0.8	3.9
150°	0.8	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)