

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1056184

Luminaire Tested: S124R3DR-H575D930-X4F0-XX-UDD-FLL-B

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2019
Report Number: P1056184
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124R3DR-H575D930-X4F0-XX-UDD-FLL-B
Description: DEFINE 4, BLACK 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 803.7 lumens
Efficiency: N/A
Efficacy: 46.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 0.81 / 0.97
Luminous Opening: Rectangular (W 0.31' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 17.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1056184

CATALOG NUMBER: S124R3DR-H575D930-X4F0-XX-UDD-FLL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1056184

CATALOG NUMBER: S124R3DR-H575D930-X4F0-XX-UDD-FLL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64
5	84	74	66	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52
7	74	63	55	50	73	62	55	50	60	54	50	59	53	49	58	53	49	47
8	70	58	51	46	68	57	50	46	56	50	45	55	49	45	54	49	45	43
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	39	48	42	39	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5084	5084	5084
5°	5038	4993	4988
10°	4995	4798	4671
15°	4933	4510	4232
20°	4853	4159	3697
25°	4746	3745	3086
30°	4627	3286	2452
35°	4497	2787	1825
40°	4359	2270	1216
45°	4209	1734	670
50°	4063	1187	186
55°	3901	643	122
60°	3708	200	69
65°	3467	130	36
70°	3133	59	16
75°	2695	20	0
80°	2037	0	0
85°	862	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4209 cd/sqm



TEST NUMBER: P1056184

CATALOG NUMBER: S124R3DR-H575D930-X4F0-XX-UDD-FLL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.0	6.6
10°-20°	139.3	17.3
20°-30°	180.0	22.4
30°-40°	172.0	21.4
40°-50°	128.6	16.0
50°-60°	76.5	9.5
60°-70°	38.9	4.8
70°-80°	13.5	1.7
80°-90°	1.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	372.3	46.3
0°-40°	544.3	67.7
0°-60°	749.4	93.3
0°-90°	803.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	803.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	575	575	575	575	575	
5°	568	572	563	560	562	54
15°	539	528	493	470	462	152
25°	486	453	384	333	316	224
35°	417	359	258	192	169	261
45°	337	258	139	74	54	260
55°	253	157	42	10	8	226
65°	166	64	6	2	2	164
75°	79	8	1	1	0	84
85°	8	0	0	0	0	14
90°	0	0	0	0	0	



TEST NUMBER: P1056184

CATALOG NUMBER: S124R3DR-H575D930-X4F0-XX-UDD-FLL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	575.0	575.0	575.0	575.0	575.0
2.5°	569.4	576.1	570.5	571.1	571.6
5°	567.7	572.2	562.6	559.8	562.0
7.5°	563.2	564.9	550.8	543.4	544.0
10°	556.4	554.7	534.4	522.0	520.3
12.5°	548.5	542.9	514.7	496.7	492.7
15°	538.9	527.7	492.7	469.6	462.3
17.5°	527.7	511.3	468.5	438.0	429.0
20°	515.8	493.3	442.0	404.2	392.9
22.5°	501.7	473.0	413.2	368.7	354.6
25°	486.5	452.7	383.9	333.2	316.3
27.5°	470.7	430.7	352.9	297.1	277.4
30°	453.2	407.6	321.9	260.4	240.2
32.5°	435.2	383.9	289.8	226.6	204.1
35°	416.6	359.1	258.2	192.2	169.1
37.5°	397.4	334.3	227.8	159.5	135.9
40°	377.7	308.9	196.7	128.5	105.4
42.5°	358.5	283.6	167.4	99.2	77.8
45°	336.6	258.2	138.7	73.8	53.6
47.5°	316.8	233.4	111.1	50.2	31.6
50°	295.4	206.9	86.3	29.3	13.5
52.5°	274.0	182.1	63.1	13.0	10.1
55°	253.1	157.3	41.7	9.6	7.9
57.5°	231.1	132.5	22.5	7.3	5.6
60°	209.7	108.2	11.3	5.6	3.9
62.5°	187.7	85.1	9.0	3.4	2.3
65°	165.7	63.7	6.2	2.3	1.7
67.5°	143.8	43.4	3.9	1.1	0.6
70°	121.2	26.5	2.3	0.6	0.6
72.5°	99.8	13.5	1.1	0.6	0.6
75°	78.9	8.5	0.6	0.6	0.0
77.5°	58.6	4.5	0.6	0.6	0.0
80°	40.0	1.7	0.0	0.0	0.0
82.5°	23.1	0.6	0.0	0.0	0.0
85°	8.5	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1056184
 CATALOG NUMBER: S124R3DR-H575D930-X4F0-XX-UDD-FLL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.10	17.43	16.47	17.75	18.06	0.00	0.00	0.00	0.00	0.00
	3H	17.65	18.82	18.03	19.15	19.52	0.00	0.00	0.00	0.00	0.00
	4H	18.24	19.34	18.64	19.69	20.07	0.00	0.00	0.00	0.00	0.00
	6H	18.66	19.66	19.07	20.03	20.43	0.00	0.00	0.00	0.00	0.00
	8H	18.76	19.71	19.19	20.10	20.50	0.00	0.00	0.00	0.00	0.00
	12H	18.78	19.69	19.21	20.07	20.50	0.00	0.00	0.00	0.00	0.00
4H	2H	15.88	16.98	16.29	17.33	17.71	0.00	0.00	0.00	0.00	0.00
	3H	17.45	18.34	17.86	18.74	19.15	0.00	0.00	0.00	0.00	0.00
	4H	18.03	18.83	18.46	19.25	19.69	0.00	0.00	0.00	0.00	0.00
	6H	18.49	19.18	18.95	19.62	20.09	0.00	0.00	0.00	0.00	0.00
	8H	18.61	19.25	19.08	19.70	20.17	0.00	0.00	0.00	0.00	0.00
	12H	18.65	19.21	19.14	19.70	20.17	0.00	0.00	0.00	0.00	0.00
8H	4H	17.89	18.53	18.36	18.98	19.45	0.00	0.00	0.00	0.00	0.00
	6H	18.33	18.86	18.84	19.35	19.83	0.00	0.00	0.00	0.00	0.00
	8H	18.45	18.92	18.97	19.43	19.93	0.00	0.00	0.00	0.00	0.00
	12H	18.50	18.91	19.01	19.41	19.98	0.00	0.00	0.00	0.00	0.00
12H	4H	17.85	18.41	18.33	18.90	19.37	0.00	0.00	0.00	0.00	0.00
	6H	18.27	18.74	18.79	19.26	19.75	0.00	0.00	0.00	0.00	0.00
	8H	18.41	18.82	18.92	19.31	19.89	0.00	0.00	0.00	0.00	0.00