

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1038002

Luminaire Tested: S125DS-B375DB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1038002
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-12)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DS-B375DB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Direct Surface with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1467.0 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1038002

CATALOG NUMBER: S125DS-B375DB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1038002

CATALOG NUMBER: S125DS-B375DB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92	94	91	89	90	88	86	86	86	84
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	72	72	70
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	62	62	59
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	53	53	51
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	57	51	46	46	46	44
6	71	57	49	42	69	56	48	42	55	47	42	53	46	41	51	46	41	41	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	36	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	33	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30	30	30	28
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	27	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3611	3611	3611
5°	3619	3585	3608
10°	3597	3559	3580
15°	3558	3517	3531
20°	3503	3457	3463
25°	3442	3386	3383
30°	3368	3309	3292
35°	3289	3226	3181
40°	3208	3136	3092
45°	3119	3054	2994
50°	3022	2955	2867
55°	2929	2844	2765
60°	2817	2731	2635
65°	2683	2595	2508
70°	2555	2439	2355
75°	2329	2253	2173
80°	2074	2040	1992
85°	1801	1838	1735

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3119 cd/sqm

TEST NUMBER: P1038002

CATALOG NUMBER: S125DS-B375DB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.2	3.6
10°-20°	150.2	10.2
20°-30°	221.8	15.1
30°-40°	258.8	17.6
40°-50°	259.9	17.7
50°-60°	228.1	15.6
60°-70°	169.9	11.6
70°-80°	97.1	6.6
80°-90°	28.0	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	425.2	29.0
0°-40°	684.0	46.6
0°-60°	1172.0	79.9
0°-90°	1467.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1467.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	564	564	564	564	564	
5°	563	562	557	561	561	53
15°	536	535	530	532	532	151
25°	487	485	479	480	478	224
35°	420	419	412	410	407	263
45°	344	342	337	332	330	265
55°	262	261	255	251	248	234
65°	177	176	171	167	165	176
75°	94	93	91	90	88	100
85°	24	25	25	24	24	28
90°	0	0	0	0	0	

TEST NUMBER: P1038002

CATALOG NUMBER: S125DS-B375DB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	563.6	563.6	563.6	563.6	563.6
2.5°	565.4	564.1	559.6	564.1	563.6
5°	562.7	561.9	557.4	561.4	561.0
7.5°	558.7	557.8	552.9	556.9	556.5
10°	552.9	552.0	547.1	550.7	550.3
12.5°	545.8	544.0	539.6	542.2	542.2
15°	536.4	535.1	530.2	532.4	532.4
17.5°	526.6	524.4	519.5	522.2	519.9
20°	513.7	512.8	507.0	510.1	507.9
22.5°	500.8	499.0	493.6	495.4	494.1
25°	486.9	484.7	478.9	479.8	478.5
27.5°	470.9	469.5	463.7	464.2	462.9
30°	455.3	453.9	447.3	446.4	445.0
32.5°	438.3	436.1	430.3	428.5	425.8
35°	420.5	418.7	412.5	410.2	406.7
37.5°	402.2	400.0	394.2	391.1	388.8
40°	383.5	381.3	375.0	371.0	369.7
42.5°	363.4	361.6	355.4	351.8	349.6
45°	344.2	342.5	337.1	331.8	330.4
47.5°	323.3	323.7	317.0	311.7	308.6
50°	303.2	301.9	296.5	290.7	287.6
52.5°	282.7	281.8	276.0	271.1	267.5
55°	262.2	260.9	254.6	250.6	247.5
57.5°	240.3	239.9	234.6	229.2	227.9
60°	219.8	218.1	213.1	208.7	205.6
62.5°	198.4	197.1	193.1	188.2	185.9
65°	177.0	176.1	171.2	167.2	165.4
67.5°	156.1	154.3	150.7	147.2	146.3
70°	136.4	134.2	130.2	127.5	125.7
72.5°	115.0	113.7	111.5	108.4	106.6
75°	94.1	93.2	91.0	89.6	87.8
77.5°	74.5	74.0	72.7	71.8	70.5
80°	56.2	56.2	55.3	54.8	54.0
82.5°	40.1	39.2	39.2	38.3	38.3
85°	24.5	25.0	25.0	24.5	23.6
87.5°	12.0	12.0	11.6	11.6	10.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)