

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1038127

Luminaire Tested: S125R3DS-B375DB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1038127
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-27)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125R3DS-B375DB2750-4F0-XX-W2A-F_3000K
Description: Define 5 3in Regressed Direct Surface with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4888.0 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1038127

CATALOG NUMBER: S125R3DS-B375DB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1038127

CATALOG NUMBER: S125R3DS-B375DB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	87	87	85
2	100	92	86	80	98	90	84	79	87	82	78	84	79	76	81	77	74	74	74	72
3	92	82	74	68	89	80	73	67	77	71	66	74	69	65	72	67	64	64	64	61
4	84	73	64	58	82	71	64	57	69	62	57	67	61	56	64	59	55	55	55	53
5	78	65	57	50	76	64	56	50	62	55	49	60	54	49	58	53	48	48	48	46
6	72	59	50	44	70	58	50	44	56	49	44	55	48	43	53	47	43	43	43	41
7	67	54	45	39	65	53	45	39	51	44	39	50	43	39	49	43	38	38	38	36
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34	34	34	33
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31	31	31	29
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29	29	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13256	13256	13256
5°	13286	13135	13216
10°	13186	13013	13013
15°	13029	12749	12645
20°	12828	12380	12231
25°	12594	12019	11754
30°	12300	11595	11225
35°	12002	11158	10633
40°	11723	10704	10050
45°	11383	10195	9415
50°	11043	9641	8754
55°	10648	9112	8047
60°	10251	8470	7289
65°	9783	7723	6420
70°	9250	6791	5532
75°	8511	5726	4602
80°	7494	4498	3863
85°	6315	3676	3448

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11383 cd/sqm

TEST NUMBER: P1038127

CATALOG NUMBER: S125R3DS-B375DB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.7	4.0
10°-20°	544.2	11.1
20°-30°	789.0	16.1
30°-40°	898.9	18.4
40°-50°	876.2	17.9
50°-60°	737.4	15.1
60°-70°	516.7	10.6
70°-80°	264.9	5.4
80°-90°	66.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1527.9	31.3
0°-40°	2426.8	49.6
0°-60°	4040.3	82.7
0°-90°	4888.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4888.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2069	2069	2069	2069	2069	
5°	2066	2060	2042	2058	2055	196
15°	1964	1955	1922	1920	1906	554
25°	1781	1758	1700	1680	1663	820
35°	1534	1497	1427	1381	1360	961
45°	1256	1211	1125	1063	1039	969
55°	953	903	816	745	720	852
65°	645	592	509	447	424	639
75°	344	297	231	197	186	363
85°	86	58	50	48	47	99
90°	0	0	0	0	0	

TEST NUMBER: P1038127

CATALOG NUMBER: S125R3DS-B375DB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2068.9	2068.9	2068.9	2068.9	2068.9
2.5°	2073.6	2068.9	2053.2	2068.9	2067.3
5°	2065.7	2059.5	2042.3	2057.9	2054.8
7.5°	2050.1	2043.9	2023.6	2036.1	2032.9
10°	2026.7	2022.0	2000.1	2004.8	2000.1
12.5°	2000.1	1993.9	1962.6	1965.7	1957.9
15°	1964.2	1954.8	1922.0	1920.4	1906.4
17.5°	1926.7	1912.6	1873.5	1865.7	1854.8
20°	1881.4	1865.7	1815.7	1807.9	1793.9
22.5°	1831.4	1815.7	1762.6	1745.4	1734.5
25°	1781.4	1757.9	1700.1	1679.8	1662.6
27.5°	1725.1	1697.0	1636.0	1609.5	1592.3
30°	1662.6	1632.9	1567.3	1531.3	1517.3
32.5°	1601.7	1565.7	1498.5	1457.9	1439.1
35°	1534.5	1497.0	1426.6	1381.3	1359.5
37.5°	1470.4	1425.1	1353.2	1300.1	1278.2
40°	1401.6	1354.8	1279.8	1220.4	1201.6
42.5°	1329.8	1281.3	1203.2	1146.9	1117.3
45°	1256.3	1211.0	1125.1	1062.6	1039.1
47.5°	1179.8	1132.9	1046.9	982.9	956.3
50°	1107.9	1056.3	967.2	901.6	878.2
52.5°	1029.7	976.6	893.8	821.9	798.5
55°	953.2	903.2	815.7	745.4	720.4
57.5°	875.1	821.9	737.5	668.8	646.9
60°	800.0	745.4	661.0	592.2	568.8
62.5°	720.4	668.8	582.8	520.3	496.9
65°	645.3	592.2	509.4	446.9	423.5
67.5°	570.3	517.2	437.5	378.1	359.4
70°	493.8	440.7	362.5	314.1	295.3
72.5°	418.8	367.2	295.3	251.6	240.6
75°	343.8	296.9	231.3	196.9	185.9
77.5°	267.2	229.7	175.0	148.4	139.1
80°	203.1	165.6	121.9	107.8	104.7
82.5°	140.6	107.8	81.3	76.6	75.0
85°	85.9	57.8	50.0	48.4	46.9
87.5°	35.9	25.0	23.4	23.4	21.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)