

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1038228

Luminaire Tested: S125RDS-B375DB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1038228
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-27)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDS-B375DB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Regressed Direct Surface with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1413.0 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1038228

CATALOG NUMBER: S125RDS-B375DB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1038228

CATALOG NUMBER: S125RDS-B375DB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	87	87	85
2	100	92	86	80	98	90	84	79	87	82	78	84	79	76	81	77	74	74	74	72
3	92	82	74	68	89	80	73	67	77	71	66	74	69	65	72	67	64	64	64	61
4	84	73	64	58	82	71	64	57	69	62	57	67	61	56	64	59	55	55	55	53
5	78	65	57	50	76	64	56	50	62	55	49	60	54	49	58	53	48	48	48	46
6	72	59	50	44	70	58	50	44	56	49	44	55	48	43	53	47	43	43	43	41
7	67	54	45	39	65	53	45	39	51	44	39	50	43	39	49	43	38	38	38	36
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34	34	34	33
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31	31	31	29
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29	29	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3832	3832	3832
5°	3841	3797	3820
10°	3812	3762	3762
15°	3766	3685	3656
20°	3708	3579	3536
25°	3640	3475	3398
30°	3556	3352	3245
35°	3470	3226	3074
40°	3389	3094	2906
45°	3291	2947	2722
50°	3193	2787	2531
55°	3077	2634	2326
60°	2964	2449	2107
65°	2829	2233	1856
70°	2673	1963	1600
75°	2461	1656	1332
80°	2166	1299	1118
85°	1823	1066	1000

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3291 cd/sqm

TEST NUMBER: P1038228

CATALOG NUMBER: S125RDS-B375DB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	4.0
10°-20°	157.3	11.1
20°-30°	228.1	16.1
30°-40°	259.9	18.4
40°-50°	253.3	17.9
50°-60°	213.2	15.1
60°-70°	149.4	10.6
70°-80°	76.6	5.4
80°-90°	19.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	441.7	31.3
0°-40°	701.5	49.6
0°-60°	1168.0	82.7
0°-90°	1413.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1413.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	598	598	598	598	598	
5°	597	595	590	595	594	57
15°	568	565	556	555	551	160
25°	515	508	492	486	481	237
35°	444	433	412	399	393	278
45°	363	350	325	307	300	280
55°	276	261	236	216	208	246
65°	187	171	147	129	122	185
75°	99	86	67	57	54	105
85°	25	17	14	14	14	29
90°	0	0	0	0	0	

TEST NUMBER: P1038228

CATALOG NUMBER: S125RDS-B375DB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	598.1	598.1	598.1	598.1	598.1
2.5°	599.4	598.1	593.5	598.1	597.6
5°	597.2	595.3	590.4	594.9	594.0
7.5°	592.6	590.8	585.0	588.6	587.7
10°	585.9	584.5	578.2	579.5	578.2
12.5°	578.2	576.4	567.3	568.2	566.0
15°	567.8	565.1	555.6	555.1	551.1
17.5°	557.0	552.9	541.6	539.3	536.2
20°	543.9	539.3	524.9	522.6	518.6
22.5°	529.4	524.9	509.5	504.6	501.4
25°	514.9	508.2	491.5	485.6	480.6
27.5°	498.7	490.6	472.9	465.3	460.3
30°	480.6	472.0	453.1	442.7	438.6
32.5°	463.0	452.6	433.2	421.4	416.0
35°	443.6	432.7	412.4	399.3	393.0
37.5°	425.1	412.0	391.2	375.8	369.5
40°	405.2	391.6	369.9	352.8	347.4
42.5°	384.4	370.4	347.8	331.6	323.0
45°	363.2	350.1	325.2	307.2	300.4
47.5°	341.0	327.5	302.6	284.1	276.4
50°	320.3	305.4	279.6	260.6	253.9
52.5°	297.7	282.3	258.4	237.6	230.8
55°	275.5	261.1	235.8	215.5	208.2
57.5°	253.0	237.6	213.2	193.3	187.0
60°	231.3	215.5	191.1	171.2	164.4
62.5°	208.2	193.3	168.5	150.4	143.6
65°	186.6	171.2	147.3	129.2	122.4
67.5°	164.9	149.5	126.5	109.3	103.9
70°	142.7	127.4	104.8	90.8	85.4
72.5°	121.1	106.2	85.4	72.7	69.6
75°	99.4	85.8	66.9	56.9	53.8
77.5°	77.2	66.4	50.6	42.9	40.2
80°	58.7	47.9	35.2	31.2	30.3
82.5°	40.7	31.2	23.5	22.1	21.7
85°	24.8	16.7	14.5	14.0	13.6
87.5°	10.4	7.2	6.8	6.8	6.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)