

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1038230

Luminaire Tested: S125RDS-B375DB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1038230
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-27)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDS-B375DB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Regressed Direct Surface with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1353.0 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1038230

CATALOG NUMBER: S125RDS-B375DB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1038230

CATALOG NUMBER: S125RDS-B375DB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	87	87	85
2	100	92	86	80	98	90	84	79	87	82	78	84	79	76	81	77	74	74	74	72
3	92	82	74	68	89	80	73	67	77	71	66	74	69	65	72	67	64	64	64	61
4	84	73	64	58	82	71	64	57	69	62	57	67	61	56	64	59	55	55	55	53
5	78	65	57	50	76	64	56	50	62	55	49	60	54	49	58	53	48	48	48	46
6	72	59	50	44	70	58	50	44	56	49	44	55	48	43	53	47	43	43	43	41
7	67	54	45	39	65	53	45	39	51	44	39	50	43	39	49	43	38	38	38	36
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34	34	34	33
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31	31	31	29
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29	29	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3669	3669	3669
5°	3678	3636	3658
10°	3650	3602	3602
15°	3606	3529	3500
20°	3551	3427	3385
25°	3486	3327	3253
30°	3405	3209	3107
35°	3322	3089	2943
40°	3245	2962	2782
45°	3151	2822	2606
50°	3057	2668	2423
55°	2947	2522	2227
60°	2838	2345	2017
65°	2708	2138	1777
70°	2561	1879	1530
75°	2357	1584	1275
80°	2074	1243	1070
85°	1750	1014	956

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3151 cd/sqm

TEST NUMBER: P1038230

CATALOG NUMBER: S125RDS-B375DB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	4.0
10°-20°	150.6	11.1
20°-30°	218.4	16.1
30°-40°	248.8	18.4
40°-50°	242.5	17.9
50°-60°	204.1	15.1
60°-70°	143.0	10.6
70°-80°	73.3	5.4
80°-90°	18.3	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.9	31.3
0°-40°	671.7	49.6
0°-60°	1118.4	82.7
0°-90°	1353.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1353.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	573	573	573	573	573	
5°	572	570	565	570	569	54
15°	544	541	532	532	528	153
25°	493	487	471	465	460	227
35°	425	414	395	382	376	266
45°	348	335	311	294	288	268
55°	264	250	226	206	199	236
65°	179	164	141	124	117	177
75°	95	82	64	54	52	101
85°	24	16	14	13	13	27
90°	0	0	0	0	0	

TEST NUMBER: P1038230

CATALOG NUMBER: S125RDS-B375DB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	572.7	572.7	572.7	572.7	572.7
2.5°	574.0	572.7	568.3	572.7	572.2
5°	571.8	570.1	565.3	569.6	568.8
7.5°	567.5	565.7	560.1	563.6	562.7
10°	561.0	559.7	553.6	554.9	553.6
12.5°	553.6	551.9	543.3	544.1	542.0
15°	543.7	541.1	532.0	531.6	527.7
17.5°	533.3	529.4	518.6	516.4	513.4
20°	520.8	516.4	502.6	500.4	496.5
22.5°	506.9	502.6	487.9	483.1	480.1
25°	493.1	486.6	470.6	465.0	460.2
27.5°	477.5	469.7	452.9	445.5	440.7
30°	460.2	452.0	433.8	423.9	420.0
32.5°	443.3	433.4	414.8	403.5	398.4
35°	424.7	414.4	394.9	382.4	376.3
37.5°	407.0	394.5	374.6	359.9	353.8
40°	388.0	375.0	354.2	337.8	332.6
42.5°	368.1	354.7	333.0	317.5	309.3
45°	347.8	335.2	311.4	294.1	287.6
47.5°	326.6	313.6	289.8	272.1	264.7
50°	306.7	292.4	267.7	249.6	243.1
52.5°	285.0	270.3	247.4	227.5	221.0
55°	263.8	250.0	225.8	206.3	199.4
57.5°	242.2	227.5	204.2	185.1	179.1
60°	221.5	206.3	183.0	163.9	157.4
62.5°	199.4	185.1	161.3	144.0	137.5
65°	178.6	163.9	141.0	123.7	117.2
67.5°	157.9	143.2	121.1	104.7	99.5
70°	136.7	122.0	100.3	86.9	81.7
72.5°	115.9	101.6	81.7	69.6	66.6
75°	95.2	82.2	64.0	54.5	51.5
77.5°	74.0	63.6	48.4	41.1	38.5
80°	56.2	45.8	33.7	29.8	29.0
82.5°	38.9	29.8	22.5	21.2	20.8
85°	23.8	16.0	13.8	13.4	13.0
87.5°	9.9	6.9	6.5	6.5	6.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)