

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036905

Luminaire Tested: S122DS-B1005DB40-4F0-XX-W2A-D

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036905
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-14)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DS-B1005DB40-4F0-XX-W2A-D
Description: Define 2 Direct Surface with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4021.0 lumens
Efficiency: N/A
Efficacy: 65.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 61.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036905

CATALOG NUMBER: S122DS-B1005DB40-4F0-XX-W2A-D

Luminous Intensity Polar Plot



TEST NUMBER: P1036905

CATALOG NUMBER: S122DS-B1005DB40-4F0-XX-W2A-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	116	116	116	116	112	112	112	112	105	105	105	98	98	98	92	92	92	89		
1	104	98	93	88	100	95	90	86	88	85	81	82	79	77	77	75	72	69		
2	94	84	77	70	90	81	74	68	76	70	65	71	66	62	66	62	59	56		
3	85	73	64	57	81	71	63	56	66	59	54	62	56	51	58	53	49	46		
4	77	64	55	48	74	62	54	47	58	51	45	55	48	43	51	46	42	39		
5	71	57	48	41	68	56	47	40	52	44	39	49	42	37	46	40	36	33		
6	65	51	42	35	63	50	41	35	47	39	34	44	37	32	42	36	31	29		
7	60	46	37	31	58	45	37	31	43	35	30	40	34	29	38	32	28	25		
8	56	42	34	28	54	41	33	27	39	32	26	37	30	25	35	29	25	23		
9	52	39	30	25	50	38	30	24	36	29	24	34	27	23	32	26	22	20		
10	49	36	28	22	47	35	27	22	33	26	21	31	25	21	30	24	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16681	16681	16681
5°	16794	16575	16697
10°	16718	16594	16766
15°	16519	16570	16770
20°	16259	16491	16774
25°	16006	16432	16832
30°	15633	16359	16889
35°	15258	16321	17177
40°	14863	16411	17515
45°	14497	16617	18018
50°	14103	16962	18654
55°	13699	17409	19473
60°	13198	18036	20550
65°	12701	18877	21968
70°	12158	20216	24104
75°	11492	22696	27932
80°	10438	27985	35779
85°	9989	44933	60462

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 87.5°

Luminance: 110865 cd/sqm

TEST NUMBER: P1036905

CATALOG NUMBER: S122DS-B1005DB40-4F0-XX-W2A-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	2.5
10°-20°	286.5	7.1
20°-30°	434.1	10.8
30°-40°	528.7	13.1
40°-50°	568.8	14.1
50°-60°	552.4	13.7
60°-70°	482.4	12.0
70°-80°	371.3	9.2
80°-90°	248.7	6.2
90°-100°	171.6	4.3
100°-110°	125.3	3.1
110°-120°	82.7	2.1
120°-130°	46.1	1.1
130°-140°	19.4	0.5
140°-150°	3.3	0.1
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	820.6	20.4
0°-40°	1349.2	33.6
0°-60°	2470.4	61.4
0°-90°	3572.7	88.9
90°-120°	379.6	9.4
90°-150°	448.3	11.1
90°-180°	448.0	11.1
0°-180°	4021.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1054	1054	1054	1054	1054	
5°	1057	1052	1043	1052	1051	100
15°	1008	1011	1011	1025	1023	284
25°	916	927	941	959	964	421
35°	790	816	845	878	889	494
45°	648	689	742	790	805	500
55°	496	551	631	686	706	444
65°	339	414	504	567	586	337
75°	188	273	371	437	457	199
85°	55	150	247	312	333	58
90°	15	104	202	263	281	11
95°	12	84	176	234	252	10
105°	8	52	131	185	202	9
115°	6	23	92	138	154	6
125°	3	3	52	93	107	3
135°	2	2	17	49	61	2
145°	0	0	0	9	17	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1036905

CATALOG NUMBER: S122DS-B1005DB40-4F0-XX-W2A-D

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1053.8	1053.8	1053.8	1053.8	1053.8
2.5°	1061.5	1056.9	1046.2	1053.8	1050.8
5°	1056.9	1052.3	1043.1	1052.3	1050.8
7.5°	1049.2	1046.2	1038.5	1049.2	1047.7
10°	1040.1	1037.0	1032.4	1044.7	1043.1
12.5°	1024.8	1026.3	1023.3	1035.5	1034.0
15°	1008.0	1011.1	1011.1	1024.8	1023.3
17.5°	986.6	992.7	997.3	1011.1	1011.1
20°	965.2	972.9	979.0	995.8	995.8
22.5°	942.3	951.5	960.7	977.5	980.5
25°	916.4	927.1	940.8	959.1	963.7
27.5°	885.8	902.6	917.9	940.8	943.9
30°	855.3	875.1	895.0	919.4	924.0
32.5°	821.7	844.6	869.0	898.0	907.2
35°	789.6	815.6	844.6	878.2	888.9
37.5°	754.5	783.5	820.1	856.8	867.5
40°	719.3	752.9	794.2	833.9	847.6
42.5°	685.7	719.3	768.2	812.5	826.3
45°	647.6	688.8	742.3	789.6	804.9
47.5°	610.9	655.2	716.3	765.2	782.0
50°	572.7	620.1	688.8	740.7	757.5
52.5°	536.1	586.5	659.8	713.2	731.6
55°	496.4	551.3	630.8	685.7	705.6
57.5°	458.2	519.3	598.7	658.3	678.1
60°	416.9	482.6	569.7	627.7	649.1
62.5°	380.3	449.0	536.1	598.7	618.5
65°	339.1	413.9	504.0	566.6	586.5
67.5°	302.4	380.3	471.9	534.5	555.9
70°	262.7	342.1	436.8	502.5	520.8
72.5°	226.0	308.5	404.7	468.9	491.8
75°	187.9	273.4	371.1	436.8	456.7
77.5°	151.2	239.8	339.1	404.7	426.1
80°	114.5	207.7	307.0	371.1	392.5
82.5°	84.0	175.6	276.4	340.6	360.4
85°	55.0	149.7	247.4	311.6	332.9
87.5°	33.6	125.2	223.0	285.6	305.5
90°	15.3	103.9	201.6	262.7	281.0
92.5°	13.7	94.7	187.9	247.4	265.7
95°	12.2	84.0	175.6	233.7	252.0
97.5°	10.7	76.4	164.9	221.5	239.8
100°	10.7	67.2	152.7	209.2	226.0
102.5°	9.2	59.6	142.0	197.0	213.8
105°	7.6	51.9	131.3	184.8	201.6
107.5°	7.6	44.3	120.7	172.6	189.4
110°	6.1	36.7	111.5	160.4	177.2



TEST NUMBER: P1036905

CATALOG NUMBER: S122DS-B1005DB40-4F0-XX-W2A-D

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	6.1	30.5	100.8	149.7	166.5
115°	6.1	22.9	91.6	137.5	154.3
117.5°	4.6	16.8	80.9	126.8	142.0
120°	4.6	10.7	71.8	114.5	131.3
122.5°	4.6	6.1	62.6	103.9	117.6
125°	3.1	3.1	51.9	93.2	106.9
127.5°	3.1	1.5	42.8	80.9	94.7
130°	3.1	1.5	33.6	70.3	82.5
132.5°	3.1	1.5	24.4	59.6	71.8
135°	1.5	1.5	16.8	48.9	61.1
137.5°	1.5	1.5	9.2	38.2	48.9
140°	1.5	0.0	3.1	27.5	36.7
142.5°	1.5	0.0	0.0	18.3	26.0
145°	0.0	0.0	0.0	9.2	16.8
147.5°	0.0	0.0	0.0	1.5	6.1
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)