

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036930

Luminaire Tested: S122DS-B290DB30-4F0-XX-W2A-F

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036930
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DS-B290DB30-4F0-XX-W2A-F
Description: Define 2 Direct Surface with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1170.0 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036930

CATALOG NUMBER: S122DS-B290DB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1036930

CATALOG NUMBER: S122DS-B290DB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	86	86	84
2	99	91	85	79	97	89	83	78	86	81	76	83	78	74	80	76	73	73	73	71
3	91	80	72	66	88	79	71	65	76	69	64	73	68	63	71	66	62	62	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	54	54	51
5	77	64	55	49	75	63	55	48	61	53	48	59	52	47	57	51	47	47	47	45
6	71	58	49	43	69	57	48	42	55	48	42	53	47	42	52	46	41	41	41	39
7	66	52	44	38	64	52	43	38	50	43	37	49	42	37	47	41	37	37	37	35
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	33	33	31
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	30	30	28
10	54	41	33	28	53	40	33	28	39	32	27	38	32	27	37	32	27	27	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7280	7280	7280
5°	7308	7201	7244
10°	7264	7129	7164
15°	7175	7037	7029
20°	7046	6898	6890
25°	6920	6726	6726
30°	6757	6571	6514
35°	6605	6383	6290
40°	6414	6195	6077
45°	6226	6008	5861
50°	6021	5814	5607
55°	5809	5588	5382
60°	5572	5319	5122
65°	5315	5053	4820
70°	4994	4725	4503
75°	4544	4355	4244
80°	4029	3911	3710
85°	3287	3124	2815

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6226 cd/sqm

TEST NUMBER: P1036930

CATALOG NUMBER: S122DS-B290DB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.3	3.7
10°-20°	121.8	10.4
20°-30°	179.0	15.3
30°-40°	207.9	17.8
40°-50°	207.6	17.7
50°-60°	181.0	15.5
60°-70°	133.8	11.4
70°-80°	75.7	6.5
80°-90°	20.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	344.0	29.4
0°-40°	551.9	47.2
0°-60°	940.5	80.4
0°-90°	1170.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1170.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	460	460	460	460	460	
5°	460	458	453	457	456	44
15°	438	435	429	431	429	123
25°	396	393	385	386	385	182
35°	342	337	330	328	326	213
45°	278	275	268	264	262	215
55°	210	208	202	197	195	188
65°	142	139	135	131	129	140
75°	74	73	71	68	69	79
85°	18	18	17	16	16	21
90°	0	0	0	0	0	

TEST NUMBER: P1036930

CATALOG NUMBER: S122DS-B290DB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	459.9	459.9	459.9	459.9	459.9
2.5°	462.5	460.3	455.5	459.9	459.0
5°	459.9	458.1	453.2	456.8	455.9
7.5°	456.8	454.1	449.3	452.8	451.9
10°	451.9	448.8	443.5	447.1	445.7
12.5°	445.3	442.6	437.3	439.5	438.7
15°	437.8	435.1	429.4	431.1	428.9
17.5°	428.5	425.8	420.1	422.3	420.1
20°	418.3	415.7	409.5	410.8	409.0
22.5°	408.1	404.2	398.4	398.4	397.5
25°	396.2	392.7	385.1	386.0	385.1
27.5°	382.9	379.8	374.1	372.8	370.6
30°	369.7	366.1	359.5	358.2	356.4
32.5°	355.5	352.9	345.8	343.1	341.4
35°	341.8	337.4	330.3	327.7	325.5
37.5°	326.3	322.4	315.3	312.2	310.0
40°	310.4	306.9	299.8	295.8	294.1
42.5°	294.9	291.4	284.3	279.9	277.3
45°	278.1	275.0	268.4	263.5	261.8
47.5°	261.8	258.7	251.6	246.7	244.1
50°	244.5	242.3	236.1	229.9	227.7
52.5°	227.7	224.6	218.9	214.0	210.9
55°	210.5	207.8	202.5	197.2	195.0
57.5°	193.2	191.0	185.3	180.0	178.2
60°	176.0	174.2	168.0	163.2	161.8
62.5°	159.2	156.1	151.7	147.2	145.5
65°	141.9	139.3	134.9	130.9	128.7
67.5°	124.3	122.0	118.1	115.0	113.2
70°	107.9	106.1	102.1	99.1	97.3
72.5°	91.1	89.3	87.1	84.0	82.7
75°	74.3	73.4	71.2	68.5	69.4
77.5°	59.3	57.5	56.6	55.3	53.9
80°	44.2	43.8	42.9	41.6	40.7
82.5°	30.1	30.1	29.6	27.9	27.9
85°	18.1	17.7	17.2	15.9	15.5
87.5°	8.0	7.1	6.2	4.9	4.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)