

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036960

Luminaire Tested: S122DS-B485DB30-4F0-XX-W2A-F

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036960
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DS-B485DB30-4F0-XX-W2A-F
Description: Define 2 Direct Surface with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1968.0 lumens
Efficiency: N/A
Efficacy: 82.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 24
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036960

CATALOG NUMBER: S122DS-B485DB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1036960

CATALOG NUMBER: S122DS-B485DB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	86	86	84
2	99	91	85	79	97	89	83	78	86	81	76	83	78	74	80	76	73	73	73	71
3	91	80	72	66	88	79	71	65	76	69	64	73	68	63	71	66	62	62	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	54	54	51
5	77	64	55	49	75	63	55	48	61	53	48	59	52	47	57	51	47	47	47	45
6	71	58	49	43	69	57	48	42	55	48	42	53	47	42	52	46	41	41	41	39
7	66	52	44	38	64	52	43	38	50	43	37	49	42	37	47	41	37	37	37	35
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	33	33	31
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	30	30	28
10	54	41	33	28	53	40	33	28	39	32	27	38	32	27	37	32	27	27	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12244	12244	12244
5°	12291	12114	12184
10°	12217	11991	12050
15°	12066	11835	11824
20°	11852	11601	11589
25°	11639	11314	11314
30°	11365	11053	10958
35°	11109	10736	10578
40°	10789	10421	10220
45°	10472	10107	9857
50°	10129	9781	9432
55°	9770	9402	9052
60°	9371	8947	8617
65°	8944	8499	8105
70°	8400	7951	7572
75°	7645	7321	7143
80°	6782	6572	6235
85°	5539	5267	4722

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10472 cd/sqm

TEST NUMBER: P1036960

CATALOG NUMBER: S122DS-B485DB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.8	3.7
10°-20°	204.8	10.4
20°-30°	301.0	15.3
30°-40°	349.6	17.8
40°-50°	349.2	17.7
50°-60°	304.5	15.5
60°-70°	225.1	11.4
70°-80°	127.3	6.5
80°-90°	33.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	578.7	29.4
0°-40°	928.3	47.2
0°-60°	1582.0	80.4
0°-90°	1968.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1968.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	774	774	774	774	774	
5°	774	771	762	768	767	73
15°	736	732	722	725	722	207
25°	666	660	648	649	648	307
35°	575	568	556	551	547	359
45°	468	463	452	443	440	361
55°	354	350	341	332	328	317
65°	239	234	227	220	216	236
75°	125	124	120	115	117	133
85°	30	30	29	27	26	36
90°	0	0	0	0	0	

TEST NUMBER: P1036960

CATALOG NUMBER: S122DS-B485DB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	773.5	773.5	773.5	773.5	773.5
2.5°	778.0	774.3	766.1	773.5	772.0
5°	773.5	770.6	762.4	768.3	766.8
7.5°	768.3	763.9	755.7	761.6	760.1
10°	760.1	754.9	746.0	752.0	749.7
12.5°	749.0	744.5	735.6	739.3	737.8
15°	736.3	731.9	722.2	725.2	721.5
17.5°	720.7	716.3	706.6	710.3	706.6
20°	703.6	699.2	688.7	691.0	688.0
22.5°	686.5	679.8	670.2	670.2	668.7
25°	666.4	660.5	647.8	649.3	647.8
27.5°	644.1	638.9	629.2	627.0	623.3
30°	621.8	615.9	604.7	602.5	599.5
32.5°	598.0	593.5	581.6	577.2	574.2
35°	574.9	567.5	555.6	551.1	547.4
37.5°	548.9	542.2	530.3	525.1	521.4
40°	522.1	516.2	504.3	497.6	494.6
42.5°	496.1	490.2	478.3	470.8	466.4
45°	467.8	462.6	451.5	443.3	440.3
47.5°	440.3	435.1	423.2	415.0	410.6
50°	411.3	407.6	397.2	386.8	383.0
52.5°	383.0	377.8	368.2	360.0	354.8
55°	354.0	349.6	340.7	331.7	328.0
57.5°	325.0	321.3	311.6	302.7	299.7
60°	296.0	293.1	282.6	274.5	272.2
62.5°	267.8	262.6	255.1	247.7	244.7
65°	238.8	234.3	226.9	220.2	216.4
67.5°	209.0	205.3	198.6	193.4	190.4
70°	181.5	178.5	171.8	166.6	163.6
72.5°	153.2	150.2	146.5	141.3	139.1
75°	125.0	123.5	119.7	115.3	116.8
77.5°	99.7	96.7	95.2	93.0	90.7
80°	74.4	73.6	72.1	69.9	68.4
82.5°	50.6	50.6	49.8	46.9	46.9
85°	30.5	29.8	29.0	26.8	26.0
87.5°	13.4	11.9	10.4	8.2	7.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)