

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1060647

Luminaire Tested: S124RDR-H1020D840-X4F0-XX-UDD-SVL-W

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1060647
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-74)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDR-H1020D840-X4F0-XX-UDD-SVL-W
Description: DEFINE 4 WHITE REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1503.6 lumens
Efficiency: N/A
Efficacy: 48.2 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 1.12 / 1.01
Luminous Opening: Rectangular (W 0.31' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1060647

CATALOG NUMBER: S124RDR-H1020D840-X4F0-XX-UDD-SVL-W

Luminous Intensity Polar Plot





TEST NUMBER: P1060647

CATALOG NUMBER: S124RDR-H1020D840-X4F0-XX-UDD-SVL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65	63
5	84	73	66	60	82	72	65	60	70	64	60	69	63	59	67	62	58	57
6	79	67	60	54	77	67	59	54	65	59	54	63	58	53	62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	53	48	44	43
9	65	54	46	42	64	53	46	41	52	46	41	51	45	41	50	45	41	39
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9148	9148	9148
5°	8864	8978	9142
10°	8282	8604	9030
15°	7555	8084	8857
20°	6755	7462	8560
25°	5876	6744	8210
30°	4957	5972	7825
35°	3943	5140	7412
40°	2869	4283	7005
45°	1734	3382	6635
50°	1241	2449	6074
55°	1051	1657	5364
60°	859	1349	4333
65°	676	1208	3120
70°	569	1017	1644
75°	512	948	828
80°	531	942	823
85°	701	1403	939

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 6635 cd/sqm



TEST NUMBER: P1060647

CATALOG NUMBER: S124RDR-H1020D840-X4F0-XX-UDD-SVL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.8	6.5
10°-20°	256.3	17.0
20°-30°	332.4	22.1
30°-40°	320.0	21.3
40°-50°	238.0	15.8
50°-60°	146.4	9.7
60°-70°	71.9	4.8
70°-80°	28.0	1.9
80°-90°	12.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	686.5	45.7
0°-40°	1006.4	66.9
0°-60°	1390.8	92.5
0°-90°	1503.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1503.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1062	1062	1062	1062	1062	
5°	1026	1041	1039	1048	1058	95
15°	848	875	907	961	994	237
25°	618	652	710	799	864	283
35°	375	411	489	611	705	234
45°	142	177	278	428	545	118
55°	70	72	110	252	357	63
65°	33	36	59	95	153	34
75°	15	27	28	26	25	17
85°	7	13	14	14	10	7
90°	0	0	0	0	0	



TEST NUMBER: P1060647

CATALOG NUMBER: S124RDR-H1020D840-X4F0-XX-UDD-SVL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1062.3	1062.3	1062.3	1062.3	1062.3
2.5°	1051.7	1063.5	1054.0	1055.2	1056.4
5°	1025.5	1041.0	1038.6	1048.1	1057.6
7.5°	989.9	1007.7	1016.0	1035.0	1048.1
10°	947.2	967.4	984.0	1014.9	1032.7
12.5°	899.7	923.5	947.2	988.7	1016.0
15°	847.5	874.8	906.8	961.4	993.5
17.5°	794.1	821.4	862.9	925.8	966.2
20°	737.1	766.8	814.3	884.3	934.1
22.5°	677.8	709.8	762.0	841.6	900.9
25°	618.4	651.6	709.8	798.8	864.1
27.5°	559.1	591.1	654.0	753.7	824.9
30°	498.5	531.8	600.6	705.1	787.0
32.5°	440.4	471.2	544.8	658.8	745.4
35°	375.1	410.7	489.0	611.3	705.1
37.5°	319.3	351.3	435.6	563.8	664.7
40°	255.2	290.8	381.0	517.5	623.2
42.5°	195.8	231.5	328.8	471.2	584.0
45°	142.4	176.9	277.7	428.5	544.8
47.5°	108.0	128.2	227.9	387.0	500.9
50°	92.6	98.5	182.8	341.8	453.4
52.5°	81.9	84.3	142.4	296.7	405.9
55°	70.0	72.4	110.4	251.6	357.3
57.5°	59.3	60.5	89.0	208.9	305.0
60°	49.9	51.0	78.3	167.4	251.6
62.5°	41.5	42.7	70.0	129.4	200.6
65°	33.2	35.6	59.3	95.0	153.1
67.5°	27.3	32.0	49.9	66.5	106.8
70°	22.6	30.9	40.4	46.3	65.3
72.5°	19.0	28.5	34.4	33.2	32.0
75°	15.4	27.3	28.5	26.1	24.9
77.5°	13.1	23.7	23.7	21.4	20.2
80°	10.7	19.0	19.0	19.0	16.6
82.5°	9.5	15.4	16.6	16.6	13.1
85°	7.1	13.1	14.2	14.2	9.5
87.5°	4.7	11.9	13.1	11.9	7.1
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1060647
 CATALOG NUMBER: S124RDR-H1020D840-X4F0-XX-UDD-SVL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.47	8.81	7.84	9.13	9.44	16.64	17.99	17.01	18.30	18.61
	3H	8.58	9.77	8.96	10.10	10.47	17.15	18.34	17.53	18.67	19.04
	4H	9.10	10.21	9.50	10.56	10.94	17.17	18.28	17.57	18.63	19.01
	6H	9.54	10.56	9.95	10.93	11.32	17.18	18.20	17.60	18.57	18.97
	8H	9.73	10.69	10.16	11.09	11.49	17.18	18.15	17.61	18.54	18.95
	12H	9.91	10.83	10.34	11.22	11.65	17.19	18.11	17.62	18.49	18.92
4H	2H	8.62	9.73	9.02	10.08	10.46	16.53	17.65	16.94	18.00	18.38
	3H	9.96	10.87	10.37	11.27	11.67	17.12	18.03	17.54	18.44	18.84
	4H	10.69	11.51	11.13	11.93	12.37	17.18	18.00	17.62	18.42	18.86
	6H	11.30	12.01	11.77	12.45	12.92	17.26	17.96	17.72	18.41	18.87
	8H	11.55	12.20	12.01	12.65	13.12	17.29	17.95	17.76	18.39	18.86
	12H	11.78	12.36	12.27	12.85	13.32	17.33	17.91	17.82	18.39	18.87
8H	4H	11.16	11.82	11.63	12.26	12.73	17.14	17.80	17.61	18.24	18.71
	6H	12.01	12.55	12.51	13.04	13.52	17.27	17.81	17.77	18.30	18.78
	8H	12.42	12.90	12.94	13.41	13.91	17.35	17.84	17.87	18.35	18.84
	12H	12.84	13.27	13.35	13.76	14.33	17.47	17.90	17.99	18.39	18.97
12H	4H	11.21	11.80	11.70	12.28	12.75	17.11	17.69	17.60	18.18	18.65
	6H	12.14	12.63	12.66	13.14	13.63	17.25	17.73	17.77	18.25	18.74
	8H	12.66	13.09	13.18	13.59	14.16	17.38	17.81	17.90	18.31	18.88