

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929824

Luminaire Tested: DFN2DS-4P2F0-040DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929824
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P2F0-040DS830-RLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3202.8 lumens
Efficiency: N/A
Efficacy: 74.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.07' x L: 2.07' x H: 0')
CIE Type: Direct

Input Watts (W): 43.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929824

CATALOG NUMBER: DFN2DS-4P2F0-040DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P929824

CATALOG NUMBER: DFN2DS-4P2F0-040DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3899	3899	3899
5°	3914	3851	3872
10°	3884	3788	3756
15°	3840	3675	3570
20°	3778	3515	3339
25°	3715	3333	3115
30°	3627	3146	2828
35°	3542	2942	2576
40°	3455	2732	2285
45°	3354	2495	2021
50°	3250	2256	1762
55°	3144	1999	1514
60°	3021	1729	1257
65°	2881	1453	1144
70°	2714	1196	1052
75°	2508	1091	982
80°	2213	973	895
85°	1741	770	770

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3354 cd/sqm

TEST NUMBER: P929824

CATALOG NUMBER: DFN2DS-4P2F0-040DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	4.6
10°-20°	400.7	12.5
20°-30°	562.5	17.6
30°-40°	613.2	19.1
40°-50°	563.6	17.6
50°-60°	442.6	13.8
60°-70°	288.1	9.0
70°-80°	148.3	4.6
80°-90°	37.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1109.1	34.6
0°-40°	1722.3	53.8
0°-60°	2728.5	85.2
0°-90°	3202.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3202.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1557	1557	1557	1557	1557	
5°	1557	1550	1532	1545	1540	148
15°	1481	1466	1418	1391	1377	417
25°	1344	1299	1206	1149	1127	618
35°	1159	1087	963	874	843	725
45°	947	853	705	605	571	731
55°	720	610	458	374	347	644
65°	486	372	245	197	193	482
75°	259	161	113	103	102	274
85°	61	31	27	27	27	73
90°	0	0	0	0	0	

TEST NUMBER: P929824

CATALOG NUMBER: DFN2DS-4P2F0-040DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1557.3	1557.3	1557.3	1557.3	1557.3
2.5°	1564.4	1557.3	1541.8	1556.0	1553.1
5°	1557.3	1550.2	1531.9	1544.6	1540.5
7.5°	1544.6	1536.2	1516.5	1522.0	1515.0
10°	1527.7	1517.8	1489.7	1485.3	1477.1
12.5°	1506.6	1493.9	1455.8	1447.4	1431.8
15°	1481.2	1465.7	1417.8	1391.1	1377.0
17.5°	1451.6	1429.0	1369.8	1338.9	1316.3
20°	1417.8	1389.5	1319.1	1283.9	1252.9
22.5°	1381.2	1348.8	1266.9	1219.0	1198.0
25°	1344.5	1299.4	1206.3	1148.7	1127.4
27.5°	1300.9	1252.9	1150.0	1083.8	1051.3
30°	1254.4	1200.7	1087.9	1016.1	978.1
32.5°	1209.2	1144.3	1028.9	944.3	908.9
35°	1158.6	1086.6	962.6	873.8	842.7
37.5°	1109.2	1031.6	900.6	803.2	768.1
40°	1057.0	972.5	835.7	735.7	699.1
42.5°	1003.4	913.3	770.9	666.6	631.4
45°	947.1	852.6	704.7	604.6	570.8
47.5°	893.6	793.5	641.3	541.2	510.2
50°	834.3	734.3	579.2	481.9	452.4
52.5°	776.5	670.8	520.1	427.0	400.3
55°	720.2	610.2	458.0	373.5	346.8
57.5°	662.4	549.7	403.1	324.1	301.6
60°	603.2	490.4	345.2	273.5	250.9
62.5°	545.5	432.8	295.9	228.3	217.1
65°	486.3	372.0	245.2	197.3	193.0
67.5°	429.9	315.7	197.3	173.3	169.1
70°	370.7	260.7	163.4	149.4	143.7
72.5°	314.3	210.0	136.7	125.5	122.6
75°	259.2	160.6	112.8	102.9	101.5
77.5°	204.4	114.1	88.8	83.2	80.3
80°	153.5	81.8	67.5	62.1	62.1
82.5°	107.1	55.0	46.5	43.6	43.6
85°	60.6	31.0	26.8	26.8	26.8
87.5°	22.6	11.2	11.2	9.9	9.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929824

CATALOG NUMBER: DFN2DS-4P2F0-040DS830-RLI

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.96	17.48	16.33	17.80	18.11	11.92	13.44	12.29	13.76	14.07
	3H	17.73	19.09	18.11	19.42	19.78	13.19	14.55	13.57	14.88	15.24
	4H	18.39	19.68	18.79	20.02	20.40	13.69	14.97	14.09	15.32	15.70
	6H	18.88	20.07	19.30	20.43	20.82	14.07	15.25	14.48	15.62	16.01
	8H	19.05	20.18	19.48	20.56	20.97	14.20	15.32	14.62	15.71	16.11
	12H	19.15	20.23	19.58	20.61	21.04	14.28	15.35	14.71	15.74	16.17
4H	2H	16.07	17.35	16.47	17.70	18.07	12.62	13.90	13.02	14.25	14.63
	3H	18.00	19.06	18.41	19.46	19.86	14.06	15.12	14.47	15.52	15.93
	4H	18.75	19.71	19.18	20.12	20.56	14.66	15.62	15.09	16.03	16.47
	6H	19.34	20.17	19.80	20.62	21.08	15.15	15.98	15.61	16.42	16.88
	8H	19.56	20.33	20.02	20.78	21.24	15.31	16.09	15.77	16.53	17.00
	12H	19.71	20.40	20.19	20.88	21.35	15.43	16.12	15.91	16.60	17.07
8H	4H	18.77	19.55	19.24	20.00	20.46	15.01	15.79	15.48	16.24	16.70
	6H	19.41	20.05	19.91	20.54	21.02	15.60	16.24	16.10	16.74	17.21
	8H	19.66	20.24	20.18	20.75	21.24	15.82	16.40	16.34	16.91	17.40
	12H	19.87	20.38	20.38	20.87	21.43	16.00	16.51	16.51	17.00	17.57
12H	4H	18.76	19.45	19.24	19.93	20.40	15.06	15.75	15.54	16.23	16.70
	6H	19.39	19.97	19.91	20.48	20.97	15.67	16.24	16.18	16.75	17.24
	8H	19.68	20.19	20.19	20.68	21.24	15.94	16.45	16.45	16.94	17.50