

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1056561

Luminaire Tested: S125R3DR-H375D927-X4F0-XX-UDD-FLL-W

Issue Date: 7/25/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1056561  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/25/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S125R3DR-H375D927-X4F0-XX-UDD-FLL-W  
Description: DEFINE 5, WHITE 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 979.1 lumens  
Efficiency: N/A  
Efficacy: 83.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.01 / 1.17  
Luminous Opening: Rectangular (W 0.39' x L: 3.9' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1056561

CATALOG NUMBER: S125R3DR-H375D927-X4F0-XX-UDD-FLL-W

### Luminous Intensity Polar Plot





TEST NUMBER: P1056561

CATALOG NUMBER: S125R3DR-H375D927-X4F0-XX-UDD-FLL-W

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	110	105	101	98	107	103	100	96	99	96	93	95	93	90	91	90	88
2	101	93	87	81	98	91	85	80	88	83	79	84	80	77	81	78	75
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65
4	85	74	66	59	83	73	65	59	70	63	58	68	62	57	66	61	57
5	79	67	58	52	77	66	58	52	63	56	51	62	55	51	60	54	50
6	73	60	52	46	71	59	51	46	58	51	45	56	50	45	55	49	45
7	68	55	47	41	66	54	46	41	53	46	41	51	45	40	50	44	40
8	63	51	42	37	62	50	42	37	49	42	37	47	41	36	46	40	36
9	59	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33
10	56	43	36	31	55	43	35	30	42	35	30	41	35	30	40	34	30

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3265	3265	3265
5°	3247	3244	3247
10°	3225	3166	3136
15°	3192	3069	3006
20°	3149	2950	2844
25°	3101	2809	2650
30°	3041	2656	2446
35°	2974	2491	2233
40°	2908	2320	2022
45°	2837	2142	1813
50°	2762	1960	1603
55°	2692	1759	1395
60°	2597	1547	1226
65°	2469	1311	1139
70°	2317	1174	1067
75°	2095	1082	1005
80°	1820	981	936
85°	1419	868	868

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2837 cd/sqm



TEST NUMBER: P1056561

CATALOG NUMBER: S125R3DR-H375D927-X4F0-XX-UDD-FLL-W

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	43.2	4.4
10°-20°	118.7	12.1
20°-30°	167.6	17.1
30°-40°	184.6	18.8
40°-50°	172.1	17.6
50°-60°	137.4	14.0
60°-70°	92.5	9.4
70°-80°	49.3	5.0
80°-90°	13.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	329.5	33.7
0°-40°	514.1	52.5
0°-60°	823.6	84.1
0°-90°	979.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	979.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	462	462	462	462	462	
5°	458	461	457	456	458	43
15°	436	434	419	412	411	123
25°	398	386	360	344	340	183
35°	345	324	289	266	259	216
45°	284	257	214	188	181	219
55°	218	185	143	120	113	195
65°	148	115	78	70	68	146
75°	77	51	40	37	37	82
85°	18	12	11	11	11	21
90°	0	0	0	0	0	



TEST NUMBER: P1056561

CATALOG NUMBER: S125R3DR-H375D927-X4F0-XX-UDD-FLL-W

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	461.9	461.9	461.9	461.9	461.9
2.5°	459.5	463.3	460.2	460.9	461.6
5°	457.5	461.2	457.1	455.7	457.5
7.5°	454.0	457.1	450.2	447.1	448.5
10°	449.2	451.3	441.0	436.8	436.8
12.5°	443.4	443.4	431.0	425.1	425.1
15°	436.1	433.7	419.3	412.1	410.7
17.5°	427.9	423.4	406.2	396.9	395.2
20°	418.6	411.4	392.1	380.1	378.0
22.5°	408.3	399.0	376.6	361.8	359.4
25°	397.6	385.6	360.1	344.3	339.8
27.5°	385.6	371.1	343.3	325.4	319.9
30°	372.5	356.0	325.4	305.4	299.6
32.5°	359.1	340.5	307.2	285.8	279.3
35°	344.6	324.4	288.6	265.9	258.7
37.5°	330.2	308.2	270.4	246.6	239.1
40°	315.1	291.0	251.4	227.0	219.1
42.5°	299.9	274.1	232.9	208.1	199.8
45°	283.8	256.9	214.3	188.1	181.3
47.5°	268.3	239.4	196.1	170.6	163.0
50°	251.1	221.2	178.2	152.7	145.8
52.5°	235.3	203.3	160.3	136.6	129.3
55°	218.4	185.4	142.7	120.0	113.2
57.5°	200.9	167.5	125.9	104.6	98.0
60°	183.7	149.6	109.4	89.8	86.7
62.5°	166.1	132.8	93.9	78.8	76.7
65°	147.6	115.2	78.4	69.5	68.1
67.5°	130.0	98.4	66.0	60.9	59.5
70°	112.1	81.5	56.8	52.3	51.6
72.5°	94.6	65.4	47.8	44.7	44.0
75°	76.7	50.9	39.6	37.1	36.8
77.5°	60.2	38.2	31.3	30.3	29.6
80°	44.7	28.5	24.1	23.4	23.0
82.5°	30.6	19.6	17.2	17.2	16.5
85°	17.5	12.0	10.7	11.0	10.7
87.5°	6.5	5.2	4.8	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1056561

CATALOG NUMBER: S125R3DR-H375D927-X4F0-XX-UDD-FLL-W

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.40	16.94	15.76	17.25	17.57	11.78	13.32	12.15	13.64	13.95
	3H	17.18	18.57	17.56	18.90	19.26	13.26	14.64	13.64	14.97	15.33
	4H	17.84	19.14	18.24	19.49	19.86	13.85	15.15	14.25	15.50	15.87
	6H	18.31	19.52	18.73	19.88	20.27	14.31	15.51	14.72	15.88	16.27
	8H	18.47	19.61	18.89	20.00	20.40	14.47	15.62	14.90	16.01	16.41
	12H	18.56	19.66	18.99	20.04	20.47	14.59	15.68	15.02	16.06	16.49
4H	2H	15.53	16.83	15.93	17.18	17.56	12.46	13.76	12.86	14.11	14.49
	3H	17.50	18.59	17.91	18.98	19.39	14.14	15.22	14.55	15.62	16.02
	4H	18.25	19.22	18.68	19.64	20.08	14.84	15.81	15.27	16.23	16.67
	6H	18.84	19.69	19.30	20.13	20.59	15.43	16.27	15.88	16.72	17.17
	8H	19.05	19.84	19.51	20.29	20.75	15.63	16.43	16.10	16.87	17.34
	12H	19.20	19.91	19.68	20.38	20.85	15.79	16.50	16.28	16.98	17.45
8H	4H	18.31	19.11	18.78	19.55	20.02	15.20	16.00	15.67	16.44	16.91
	6H	18.97	19.63	19.47	20.12	20.60	15.91	16.56	16.40	17.05	17.53
	8H	19.23	19.82	19.74	20.32	20.81	16.19	16.78	16.70	17.29	17.78
	12H	19.43	19.95	19.94	20.45	21.01	16.43	16.95	16.94	17.44	18.01
12H	4H	18.31	19.02	18.79	19.49	19.96	15.25	15.96	15.73	16.44	16.91
	6H	18.97	19.56	19.48	20.07	20.55	15.98	16.57	16.49	17.08	17.56
	8H	19.26	19.78	19.77	20.27	20.84	16.32	16.84	16.83	17.33	17.90