

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1056494

Luminaire Tested: S125R3DR-H1090D830-X4F0-XX-UDD-F-S

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2024
Report Number: P1056494
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-12)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125R3DR-H1090D830-X4F0-XX-UDD-F-S
Description: DEFINE 5, SILVER 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2297.7 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 0.95 / 1.11
Luminous Opening: Rectangular (W 0.39' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1056494

CATALOG NUMBER: S125R3DR-H1090D830-X4F0-XX-UDD-F-S

Luminous Intensity Polar Plot





TEST NUMBER: P1056494

CATALOG NUMBER: S125R3DR-H1090D830-X4F0-XX-UDD-F-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88
2	102	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8987	8987	8987
5°	8913	8887	8904
10°	8847	8644	8551
15°	8744	8330	8106
20°	8590	7935	7509
25°	8429	7465	6831
30°	8235	6947	6082
35°	8015	6359	5293
40°	7789	5713	4476
45°	7567	5037	3707
50°	7302	4285	2912
55°	7022	3482	2119
60°	6707	2596	1514
65°	6301	1713	1181
70°	5692	1193	827
75°	4952	773	642
80°	3880	574	525
85°	2003	479	381

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7567 cd/sqm



TEST NUMBER: P1056494

CATALOG NUMBER: S125R3DR-H1090D830-X4F0-XX-UDD-F-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.4	5.2
10°-20°	321.9	14.0
20°-30°	445.1	19.4
30°-40°	471.6	20.5
40°-50°	411.6	17.9
50°-60°	292.8	12.7
60°-70°	162.8	7.1
70°-80°	62.6	2.7
80°-90°	10.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	885.5	38.5
0°-40°	1357.1	59.1
0°-60°	2061.5	89.7
0°-90°	2297.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2297.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1271	1271	1271	1271	1271	
5°	1256	1265	1252	1249	1255	119
15°	1195	1184	1138	1114	1108	336
25°	1081	1044	957	898	876	497
35°	929	865	737	647	613	581
45°	757	666	504	403	371	583
55°	570	457	282	195	172	509
65°	377	247	102	75	71	372
75°	181	71	28	24	24	192
85°	25	7	6	5	5	37
90°	0	0	0	0	0	



TEST NUMBER: P1056494

CATALOG NUMBER: S125R3DR-H1090D830-X4F0-XX-UDD-F-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1271.3	1271.3	1271.3	1271.3	1271.3
2.5°	1261.8	1274.8	1264.2	1265.4	1266.5
5°	1256.0	1265.4	1252.4	1248.9	1254.8
7.5°	1246.5	1253.6	1231.2	1223.0	1226.5
10°	1232.4	1234.8	1204.2	1192.4	1191.2
12.5°	1214.8	1211.2	1173.6	1154.7	1153.5
15°	1194.7	1184.2	1138.2	1113.5	1107.6
17.5°	1170.0	1153.5	1097.0	1065.3	1055.8
20°	1141.8	1119.4	1054.7	1013.5	998.2
22.5°	1113.5	1082.9	1007.6	955.8	939.3
25°	1080.6	1044.1	957.0	898.1	875.8
27.5°	1045.3	1001.7	905.2	836.9	809.8
30°	1008.8	958.2	851.0	774.5	745.1
32.5°	969.9	912.2	794.5	711.0	680.4
35°	928.7	865.2	736.9	647.4	613.3
37.5°	887.5	816.9	680.4	585.0	549.7
40°	844.0	767.5	619.1	521.5	485.0
42.5°	801.6	716.8	561.5	461.4	428.5
45°	756.9	666.2	503.8	402.6	370.8
47.5°	711.0	613.3	446.1	347.2	315.5
50°	663.9	561.5	389.6	293.1	264.8
52.5°	616.8	509.7	336.6	241.3	216.6
55°	569.7	456.7	282.5	195.4	171.9
57.5°	522.6	404.9	231.9	153.0	131.8
60°	474.4	351.9	183.6	113.0	107.1
62.5°	426.1	300.2	142.4	93.0	88.3
65°	376.7	247.2	102.4	75.3	70.6
67.5°	327.2	198.9	74.2	57.7	54.1
70°	275.4	151.8	57.7	43.6	40.0
72.5°	226.0	109.5	41.2	31.8	30.6
75°	181.3	70.6	28.3	23.5	23.5
77.5°	136.5	42.4	20.0	17.7	17.7
80°	95.3	24.7	14.1	12.9	12.9
82.5°	57.7	12.9	9.4	8.2	8.2
85°	24.7	7.1	5.9	4.7	4.7
87.5°	4.7	2.4	2.4	2.4	2.4
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1056494
 CATALOG NUMBER: S125R3DR-H1090D830-X4F0-XX-UDD-F-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.79	20.24	19.16	20.55	20.86	11.43	12.87	11.79	13.19	13.50
	3H	20.35	21.64	20.73	21.96	22.33	11.99	13.28	12.37	13.61	13.97
	4H	20.87	22.07	21.27	22.42	22.80	12.11	13.32	12.52	13.67	14.05
	6H	21.21	22.31	21.62	22.68	23.08	12.18	13.29	12.59	13.66	14.05
	8H	21.29	22.34	21.72	22.73	23.13	12.18	13.24	12.61	13.63	14.03
	12H	21.31	22.32	21.75	22.70	23.13	12.18	13.18	12.61	13.56	13.99
4H	2H	18.69	19.89	19.09	20.24	20.62	11.99	13.19	12.39	13.54	13.92
	3H	20.35	21.34	20.76	21.74	22.14	12.67	13.65	13.08	14.05	14.46
	4H	20.90	21.79	21.34	22.20	22.64	12.82	13.71	13.26	14.12	14.56
	6H	21.30	22.06	21.75	22.50	22.97	12.93	13.70	13.39	14.14	14.60
	8H	21.40	22.11	21.87	22.56	23.03	12.95	13.66	13.41	14.10	14.57
	12H	21.45	22.08	21.93	22.56	23.03	12.95	13.58	13.43	14.06	14.53
8H	4H	20.81	21.52	21.27	21.96	22.43	13.09	13.80	13.56	14.25	14.72
	6H	21.19	21.78	21.69	22.27	22.75	13.23	13.81	13.72	14.30	14.78
	8H	21.30	21.82	21.82	22.34	22.83	13.25	13.78	13.77	14.29	14.78
	12H	21.36	21.83	21.88	22.32	22.89	13.27	13.74	13.79	14.23	14.80
12H	4H	20.77	21.40	21.25	21.88	22.36	13.11	13.74	13.59	14.22	14.69
	6H	21.14	21.66	21.66	22.18	22.67	13.24	13.76	13.75	14.27	14.76
	8H	21.27	21.73	21.78	22.22	22.79	13.30	13.76	13.81	14.25	14.82