

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929915

Luminaire Tested: DFN2DS-4P3F0-060DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929915
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-060DS835-FLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5940.0 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 65
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929915

CATALOG NUMBER: DFN2DS-4P3F0-060DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929915

CATALOG NUMBER: DFN2DS-4P3F0-060DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2661	2661	2661
5°	2671	2632	2648
10°	2655	2606	2619
15°	2622	2572	2569
20°	2575	2521	2518
25°	2529	2459	2459
30°	2470	2402	2381
35°	2414	2333	2299
40°	2345	2264	2221
45°	2276	2196	2142
50°	2201	2125	2050
55°	2123	2043	1967
60°	2036	1945	1873
65°	1943	1847	1762
70°	1825	1728	1646
75°	1660	1591	1552
80°	1474	1429	1355
85°	1202	1145	1028

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2276 cd/sqm

TEST NUMBER: P929915

CATALOG NUMBER: DFN2DS-4P3F0-060DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.7	3.7
10°-20°	618.3	10.4
20°-30°	908.6	15.3
30°-40°	1055.3	17.8
40°-50°	1054.0	17.7
50°-60°	919.0	15.5
60°-70°	679.4	11.4
70°-80°	384.4	6.5
80°-90°	101.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1746.6	29.4
0°-40°	2801.8	47.2
0°-60°	4774.8	80.4
0°-90°	5940.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5940.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2335	2335	2335	2335	2335	
5°	2335	2326	2301	2319	2315	222
15°	2222	2209	2180	2189	2178	626
25°	2011	1994	1955	1960	1955	926
35°	1735	1713	1677	1663	1652	1084
45°	1412	1396	1363	1338	1329	1090
55°	1069	1055	1028	1001	990	955
65°	721	707	685	664	653	713
75°	377	373	361	348	352	402
85°	92	90	88	81	79	108
90°	0	0	0	0	0	

TEST NUMBER: P929915

CATALOG NUMBER: DFN2DS-4P3F0-060DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2334.6	2334.6	2334.6	2334.6	2334.6
2.5°	2348.2	2337.0	2312.2	2334.6	2330.3
5°	2334.6	2325.8	2301.0	2318.9	2314.6
7.5°	2318.9	2305.6	2280.8	2298.9	2294.4
10°	2294.4	2278.7	2251.7	2269.6	2262.9
12.5°	2260.6	2247.2	2220.3	2231.5	2227.0
15°	2222.4	2209.1	2179.8	2188.9	2177.7
17.5°	2175.3	2162.0	2132.7	2143.8	2132.7
20°	2123.6	2110.3	2078.8	2085.5	2076.7
22.5°	2072.2	2051.9	2022.6	2022.6	2018.1
25°	2011.4	1993.6	1955.4	1959.7	1955.4
27.5°	1944.0	1928.3	1899.2	1892.6	1881.4
30°	1876.9	1858.7	1825.2	1818.5	1809.4
32.5°	1804.9	1791.6	1755.6	1742.0	1733.0
35°	1735.4	1713.0	1677.0	1663.4	1652.2
37.5°	1656.8	1636.5	1600.6	1584.8	1573.6
40°	1576.0	1557.9	1522.0	1502.0	1492.9
42.5°	1497.4	1479.3	1443.6	1421.0	1407.6
45°	1412.2	1396.4	1362.6	1338.1	1329.0
47.5°	1329.0	1313.3	1277.4	1252.6	1239.2
50°	1241.4	1230.2	1198.8	1167.3	1156.1
52.5°	1156.1	1140.4	1111.3	1086.6	1070.9
55°	1068.7	1055.1	1028.2	1001.3	990.1
57.5°	981.1	969.9	940.6	913.7	904.6
60°	893.4	884.6	853.2	828.4	821.7
62.5°	808.1	792.4	770.0	747.6	738.6
65°	720.7	707.2	684.8	664.5	653.3
67.5°	630.9	619.5	599.5	583.8	574.7
70°	547.8	538.8	518.5	502.8	494.0
72.5°	462.5	453.5	442.3	426.6	419.9
75°	377.0	372.8	361.3	348.0	352.5
77.5°	300.8	291.8	287.2	280.6	273.9
80°	224.6	222.2	217.7	211.0	206.5
82.5°	152.7	152.7	150.5	141.5	141.5
85°	91.9	89.8	87.6	80.7	78.6
87.5°	40.5	36.0	31.4	24.8	22.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929915

CATALOG NUMBER: DFN2DS-4P3F0-060DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.68	16.29	15.05	16.61	16.92	14.24	15.85	14.60	16.16	16.48
	3H	16.43	17.89	16.81	18.21	18.57	15.94	17.40	16.32	17.72	18.08
	4H	17.08	18.45	17.48	18.80	19.17	16.58	17.95	16.98	18.30	18.68
	6H	17.55	18.82	17.96	19.18	19.57	17.05	18.32	17.46	18.68	19.07
	8H	17.69	18.90	18.12	19.29	19.69	17.19	18.40	17.61	18.79	19.19
	12H	17.78	18.94	18.21	19.32	19.75	17.27	18.43	17.70	18.81	19.24
4H	2H	15.24	16.61	15.64	16.96	17.34	14.89	16.26	15.29	16.61	16.98
	3H	17.22	18.36	17.63	18.76	19.16	16.81	17.96	17.22	18.36	18.76
	4H	17.99	19.03	18.43	19.44	19.88	17.57	18.61	18.00	19.02	19.46
	6H	18.59	19.50	19.05	19.94	20.39	18.16	19.06	18.61	19.50	19.96
	8H	18.78	19.63	19.24	20.07	20.53	18.34	19.19	18.80	19.63	20.10
	12H	18.91	19.67	19.39	20.15	20.62	18.46	19.22	18.94	19.70	20.17
8H	4H	18.27	19.11	18.73	19.56	20.02	17.89	18.74	18.35	19.18	19.65
	6H	18.98	19.69	19.48	20.17	20.65	18.60	19.30	19.09	19.79	20.27
	8H	19.24	19.87	19.75	20.38	20.86	18.85	19.48	19.36	19.99	20.47
	12H	19.44	20.00	19.95	20.49	21.05	19.03	19.59	19.54	20.08	20.64
12H	4H	18.29	19.05	18.77	19.53	20.00	17.93	18.69	18.41	19.16	19.63
	6H	19.03	19.66	19.54	20.17	20.65	18.66	19.29	19.17	19.80	20.28
	8H	19.34	19.90	19.85	20.39	20.95	18.96	19.52	19.47	20.01	20.57