

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929863

Luminaire Tested: DFN2DS-4P3F0-030DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929863
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-030DS840-FLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2973.0 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 28.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929863

CATALOG NUMBER: DFN2DS-4P3F0-030DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929863

CATALOG NUMBER: DFN2DS-4P3F0-030DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1332	1332	1332
5°	1337	1317	1325
10°	1329	1304	1311
15°	1312	1287	1286
20°	1289	1262	1260
25°	1266	1231	1231
30°	1236	1202	1192
35°	1208	1168	1150
40°	1173	1133	1112
45°	1139	1099	1072
50°	1102	1064	1026
55°	1063	1022	985
60°	1019	973	937
65°	973	924	882
70°	914	865	824
75°	831	797	777
80°	738	715	679
85°	601	573	514

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1139 cd/sqm

TEST NUMBER: P929863

CATALOG NUMBER: DFN2DS-4P3F0-030DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.0	3.7
10°-20°	309.4	10.4
20°-30°	454.7	15.3
30°-40°	528.2	17.8
40°-50°	527.5	17.7
50°-60°	460.0	15.5
60°-70°	340.0	11.4
70°-80°	192.4	6.5
80°-90°	50.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	874.2	29.4
0°-40°	1402.3	47.2
0°-60°	2389.8	80.4
0°-90°	2973.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2973.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1168	1168	1168	1168	1168	
5°	1168	1164	1152	1161	1158	111
15°	1112	1106	1091	1096	1090	313
25°	1007	998	979	981	979	463
35°	869	857	839	832	827	542
45°	707	699	682	670	665	545
55°	535	528	515	501	496	478
65°	361	354	343	333	327	357
75°	189	187	181	174	176	201
85°	46	45	44	40	39	54
90°	0	0	0	0	0	

TEST NUMBER: P929863

CATALOG NUMBER: DFN2DS-4P3F0-030DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1168.5	1168.5	1168.5	1168.5	1168.5
2.5°	1175.3	1169.7	1157.3	1168.5	1166.4
5°	1168.5	1164.1	1151.7	1160.7	1158.5
7.5°	1160.7	1154.0	1141.5	1150.6	1148.3
10°	1148.3	1140.4	1127.0	1135.9	1132.6
12.5°	1131.4	1124.7	1111.3	1116.8	1114.6
15°	1112.3	1105.7	1091.0	1095.5	1089.9
17.5°	1088.7	1082.1	1067.4	1073.0	1067.4
20°	1062.9	1056.2	1040.4	1043.7	1039.3
22.5°	1037.1	1027.0	1012.3	1012.3	1010.0
25°	1006.7	997.8	978.7	980.9	978.7
27.5°	973.0	965.1	950.5	947.2	941.6
30°	939.3	930.3	913.5	910.1	905.6
32.5°	903.4	896.7	878.7	871.9	867.4
35°	868.6	857.4	839.3	832.5	826.9
37.5°	829.2	819.1	801.1	793.2	787.6
40°	788.8	779.8	761.8	751.8	747.2
42.5°	749.4	740.4	722.5	711.2	704.5
45°	706.8	698.9	682.0	669.7	665.2
47.5°	665.2	657.4	639.3	626.9	620.2
50°	621.3	615.7	600.0	584.3	578.7
52.5°	578.7	570.8	556.3	543.8	535.9
55°	534.9	528.1	514.6	501.2	495.6
57.5°	491.0	485.4	470.8	457.3	452.8
60°	447.1	442.7	427.0	414.6	411.3
62.5°	404.5	396.6	385.4	374.2	369.7
65°	360.8	354.0	342.7	332.6	327.0
67.5°	315.8	310.1	300.0	292.2	287.7
70°	274.2	269.7	259.6	251.7	247.2
72.5°	231.5	226.9	221.3	213.5	210.2
75°	188.7	186.6	180.9	174.2	176.5
77.5°	150.6	146.0	143.7	140.4	137.1
80°	112.4	111.2	108.9	105.6	103.4
82.5°	76.4	76.4	75.4	70.8	70.8
85°	46.0	44.9	43.8	40.4	39.3
87.5°	20.2	18.0	15.7	12.4	11.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929863

CATALOG NUMBER: DFN2DS-4P3F0-030DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.28	13.89	12.64	14.20	14.52	11.83	13.44	12.20	13.76	14.07
	3H	14.03	15.48	14.40	15.81	16.17	13.54	14.99	13.91	15.32	15.68
	4H	14.67	16.04	15.07	16.39	16.77	14.18	15.55	14.58	15.90	16.27
	6H	15.14	16.41	15.55	16.78	17.17	14.64	15.91	15.05	16.28	16.67
	8H	15.29	16.50	15.71	16.89	17.29	14.78	15.99	15.21	16.38	16.78
	12H	15.38	16.54	15.81	16.92	17.35	14.86	16.02	15.29	16.41	16.84
4H	2H	12.84	14.21	13.24	14.55	14.93	12.49	13.85	12.88	14.20	14.58
	3H	14.81	15.96	15.22	16.36	16.76	14.41	15.55	14.82	15.95	16.35
	4H	15.59	16.63	16.02	17.04	17.48	15.17	16.20	15.60	16.62	17.05
	6H	16.19	17.09	16.64	17.53	17.99	15.75	16.66	16.21	17.10	17.56
	8H	16.38	17.22	16.84	17.66	18.13	15.94	16.78	16.40	17.23	17.69
	12H	16.51	17.27	16.99	17.74	18.21	16.06	16.82	16.54	17.29	17.76
8H	4H	15.86	16.71	16.32	17.15	17.62	15.49	16.34	15.95	16.78	17.24
	6H	16.58	17.28	17.07	17.77	18.24	16.20	16.90	16.69	17.39	17.86
	8H	16.84	17.47	17.35	17.97	18.46	16.45	17.08	16.95	17.58	18.07
	12H	17.04	17.59	17.54	18.08	18.65	16.62	17.18	17.13	17.67	18.23
12H	4H	15.89	16.65	16.37	17.12	17.59	15.52	16.28	16.00	16.76	17.23
	6H	16.62	17.25	17.13	17.76	18.25	16.25	16.89	16.76	17.39	17.88
	8H	16.94	17.49	17.44	17.98	18.55	16.56	17.12	17.07	17.61	18.17