

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929864

Luminaire Tested: DFN2DS-4P3F0-030DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929864
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-030DS840-RLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2552.5 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 28.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929864

CATALOG NUMBER: DFN2DS-4P3F0-030DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P929864

CATALOG NUMBER: DFN2DS-4P3F0-030DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1414	1414	1414
5°	1420	1397	1404
10°	1409	1374	1362
15°	1393	1333	1295
20°	1370	1275	1211
25°	1347	1209	1130
30°	1315	1141	1026
35°	1284	1067	934
40°	1253	991	829
45°	1217	905	733
50°	1179	819	639
55°	1140	725	549
60°	1096	627	456
65°	1045	527	415
70°	984	434	382
75°	910	396	356
80°	803	354	324
85°	630	279	279

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1217 cd/sqm

TEST NUMBER: P929864

CATALOG NUMBER: DFN2DS-4P3F0-030DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.3	4.6
10°-20°	319.3	12.5
20°-30°	448.3	17.6
30°-40°	488.7	19.1
40°-50°	449.2	17.6
50°-60°	352.7	13.8
60°-70°	229.6	9.0
70°-80°	118.2	4.6
80°-90°	30.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	884.0	34.6
0°-40°	1372.7	53.8
0°-60°	2174.6	85.2
0°-90°	2552.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2552.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1241	1241	1241	1241	1241	
5°	1241	1236	1221	1231	1228	118
15°	1180	1168	1130	1109	1097	333
25°	1072	1036	962	915	898	493
35°	923	866	767	696	672	578
45°	755	680	562	482	455	583
55°	574	486	365	298	276	513
65°	388	296	195	157	154	384
75°	207	128	90	82	81	219
85°	48	25	21	21	21	58
90°	0	0	0	0	0	

TEST NUMBER: P929864

CATALOG NUMBER: DFN2DS-4P3F0-030DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1241.1	1241.1	1241.1	1241.1	1241.1
2.5°	1246.7	1241.1	1228.7	1240.0	1237.8
5°	1241.1	1235.5	1220.9	1231.0	1227.6
7.5°	1231.0	1224.3	1208.6	1213.0	1207.4
10°	1217.5	1209.7	1187.3	1183.8	1177.2
12.5°	1200.7	1190.6	1160.3	1153.6	1141.1
15°	1180.5	1168.1	1129.9	1108.6	1097.4
17.5°	1156.9	1138.9	1091.7	1067.1	1049.0
20°	1129.9	1107.4	1051.3	1023.3	998.5
22.5°	1100.8	1074.9	1009.7	971.6	954.8
25°	1071.6	1035.5	961.5	915.4	898.5
27.5°	1036.7	998.5	916.5	863.8	837.8
30°	999.7	957.0	867.1	809.9	779.5
32.5°	963.7	912.0	820.0	752.6	724.4
35°	923.3	866.0	767.2	696.4	671.7
37.5°	884.0	822.1	717.7	640.1	612.2
40°	842.4	775.1	666.1	586.3	557.2
42.5°	799.7	727.9	614.4	531.2	503.2
45°	754.9	679.5	561.7	481.8	454.9
47.5°	712.1	632.4	511.1	431.2	406.6
50°	665.0	585.2	461.7	384.1	360.6
52.5°	618.8	534.6	414.5	340.3	319.0
55°	573.9	486.3	365.0	297.7	276.4
57.5°	527.9	438.0	321.3	258.4	240.3
60°	480.7	390.9	275.2	217.9	200.0
62.5°	434.7	344.8	235.8	182.0	173.1
65°	387.5	296.5	195.4	157.3	153.9
67.5°	342.6	251.6	157.3	138.1	134.7
70°	295.4	207.8	130.2	119.0	114.5
72.5°	250.5	167.3	108.9	100.0	97.7
75°	206.6	128.0	89.9	82.0	80.9
77.5°	162.9	90.9	70.8	66.3	64.0
80°	122.4	65.2	53.9	49.4	49.4
82.5°	85.3	43.8	37.0	34.8	34.8
85°	48.2	24.6	21.3	21.3	21.3
87.5°	18.0	8.9	8.9	7.9	7.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929864

CATALOG NUMBER: DFN2DS-4P3F0-030DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.44	13.96	12.80	14.27	14.59	8.40	9.92	8.77	10.24	10.55
	3H	14.20	15.57	14.58	15.90	16.26	9.66	11.03	10.04	11.36	11.72
	4H	14.87	16.15	15.27	16.50	16.88	10.17	11.45	10.57	11.80	12.17
	6H	15.36	16.54	15.77	16.91	17.30	10.55	11.73	10.96	12.10	12.49
	8H	15.52	16.65	15.95	17.04	17.44	10.67	11.80	11.10	12.19	12.59
	12H	15.63	16.71	16.06	17.09	17.52	10.75	11.83	11.18	12.21	12.64
4H	2H	12.54	13.82	12.94	14.17	14.55	9.10	10.38	9.50	10.72	11.10
	3H	14.48	15.54	14.89	15.94	16.34	10.54	11.60	10.95	12.00	12.40
	4H	15.23	16.18	15.66	16.60	17.04	11.14	12.09	11.57	12.51	12.95
	6H	15.82	16.65	16.27	17.09	17.55	11.63	12.46	12.08	12.90	13.36
	8H	16.03	16.81	16.50	17.25	17.72	11.79	12.56	12.25	13.01	13.48
	12H	16.18	16.88	16.67	17.36	17.83	11.90	12.60	12.39	13.08	13.55
8H	4H	15.25	16.03	15.71	16.47	16.94	11.49	12.27	11.95	12.71	13.18
	6H	15.89	16.53	16.38	17.02	17.50	12.08	12.72	12.57	13.21	13.69
	8H	16.14	16.71	16.65	17.22	17.71	12.30	12.88	12.81	13.39	13.87
	12H	16.34	16.85	16.85	17.34	17.91	12.48	12.99	12.99	13.48	14.04
12H	4H	15.23	15.93	15.72	16.41	16.88	11.53	12.23	12.02	12.71	13.18
	6H	15.87	16.45	16.38	16.96	17.44	12.14	12.72	12.65	13.23	13.72
	8H	16.15	16.66	16.66	17.15	17.72	12.41	12.92	12.92	13.42	13.98