

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1062121

Luminaire Tested: S125RDR-H610D927-X4F0-XX-UDD-SVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1062121
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-47)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDR-H610D927-X4F0-XX-UDD-SVL-B
Description: DEFINE 5 BLACK REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 600.3 lumens
Efficiency: N/A
Efficacy: 34.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular (W 0.39' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 17.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1062121
CATALOG NUMBER: S125RDR-H610D927-X4F0-XX-UDD-SVL-B

Luminous Intensity Polar Plot



TEST NUMBER: P1062121

CATALOG NUMBER: S125RDR-H610D927-X4F0-XX-UDD-SVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71
4	90	81	74	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52
7	74	62	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39
10	62	50	43	38	61	50	43	38	49	43	38	48	42	38	47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2858	2858	2858
5°	2854	2807	2807
10°	2832	2699	2629
15°	2794	2549	2410
20°	2732	2365	2164
25°	2657	2156	1880
30°	2558	1925	1585
35°	2452	1684	1286
40°	2332	1422	953
45°	2193	1140	575
50°	2028	837	395
55°	1829	513	329
60°	1555	348	262
65°	1228	267	207
70°	775	191	169
75°	253	141	141
80°	83	103	127
85°	39	87	87

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2193 cd/sqm



TEST NUMBER: P1062121

CATALOG NUMBER: S125RDR-H610D927-X4F0-XX-UDD-SVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.4	6.4
10°-20°	101.4	16.9
20°-30°	133.4	22.2
30°-40°	131.0	21.8
40°-50°	99.1	16.5
50°-60°	60.1	10.0
60°-70°	28.4	4.7
70°-80°	7.4	1.2
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	273.1	45.5
0°-40°	404.2	67.3
0°-60°	563.4	93.9
0°-90°	600.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	600.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	415	415	415	415	415	
5°	413	412	406	407	406	39
15°	392	381	358	344	338	110
25°	350	323	284	257	247	161
35°	292	253	200	165	153	182
45°	225	177	117	74	59	173
55°	152	104	43	29	27	136
65°	75	38	16	14	13	74
75°	10	6	5	5	5	15
85°	0	0	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P1062121

CATALOG NUMBER: S125RDR-H610D927-X4F0-XX-UDD-SVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	415.1	415.1	415.1	415.1	415.1
2.5°	414.6	414.6	411.4	415.1	415.1
5°	413.0	411.9	406.1	406.7	406.1
7.5°	409.8	407.7	397.7	395.0	392.9
10°	405.1	400.9	386.1	379.8	376.1
12.5°	399.8	392.4	372.4	363.4	357.6
15°	391.9	381.3	357.6	343.9	338.1
17.5°	383.4	368.1	340.2	323.8	316.5
20°	372.9	355.0	322.8	302.7	295.4
22.5°	361.3	340.2	302.7	280.6	270.6
25°	349.7	323.3	283.8	257.4	247.4
27.5°	336.5	306.4	262.1	234.7	223.6
30°	321.7	289.6	242.1	213.6	199.4
32.5°	307.0	272.2	221.0	189.9	175.6
35°	291.7	252.6	200.4	165.1	153.0
37.5°	275.3	234.2	179.3	142.4	128.2
40°	259.5	215.7	158.2	119.2	106.0
42.5°	242.6	197.3	137.1	96.5	81.8
45°	225.2	177.2	117.1	74.4	59.1
47.5°	207.3	159.3	97.0	54.9	44.3
50°	189.3	140.3	78.1	40.6	36.9
52.5°	170.9	121.8	59.1	33.8	32.2
55°	152.4	104.4	42.7	29.0	27.4
57.5°	133.4	85.4	32.2	24.8	23.2
60°	112.9	68.6	25.3	20.6	19.0
62.5°	93.9	53.8	20.6	16.9	15.8
65°	75.4	38.5	16.4	13.7	12.7
67.5°	56.4	25.8	12.7	10.5	10.5
70°	38.5	16.9	9.5	8.4	8.4
72.5°	23.2	10.0	6.9	6.9	6.9
75°	9.5	6.3	5.3	5.3	5.3
77.5°	3.2	3.7	3.7	4.2	4.2
80°	2.1	2.1	2.6	3.2	3.2
82.5°	1.1	1.6	1.6	2.1	2.1
85°	0.5	0.5	1.1	1.1	1.1
87.5°	0.0	0.0	0.0	0.5	0.5
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1062121
 CATALOG NUMBER: S125RDR-H610D927-X4F0-XX-UDD-SVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.97	14.31	13.34	14.62	14.93	3.64	4.97	4.00	5.28	5.60
	3H	13.68	14.86	14.06	15.19	15.55	4.41	5.59	4.79	5.92	6.28
	4H	13.70	14.79	14.10	15.14	15.53	4.66	5.76	5.06	6.11	6.49
	6H	13.63	14.63	14.04	15.00	15.40	4.84	5.85	5.26	6.22	6.61
	8H	13.59	14.54	14.02	14.93	15.33	4.89	5.84	5.32	6.23	6.63
	12H	13.55	14.45	13.98	14.84	15.27	4.90	5.80	5.33	6.19	6.62
4H	2H	12.81	13.90	13.21	14.25	14.64	4.13	5.22	4.53	5.57	5.96
	3H	13.55	14.44	13.96	14.85	15.25	5.03	5.92	5.44	6.32	6.73
	4H	13.57	14.36	14.00	14.78	15.23	5.34	6.14	5.78	6.56	7.00
	6H	13.51	14.19	13.97	14.64	15.11	5.60	6.29	6.07	6.73	7.20
	8H	13.46	14.10	13.93	14.54	15.01	5.67	6.31	6.14	6.76	7.23
	12H	13.41	13.98	13.90	14.46	14.93	5.70	6.26	6.18	6.74	7.22
8H	4H	13.45	14.09	13.92	14.54	15.01	5.46	6.09	5.93	6.54	7.01
	6H	13.38	13.90	13.88	14.39	14.88	5.78	6.30	6.28	6.79	7.27
	8H	13.32	13.79	13.85	14.31	14.80	5.88	6.35	6.40	6.86	7.35
	12H	13.28	13.69	13.80	14.19	14.76	5.95	6.36	6.46	6.85	7.43
12H	4H	13.41	13.97	13.90	14.45	14.93	5.43	5.99	5.91	6.47	6.95
	6H	13.32	13.79	13.84	14.30	14.79	5.75	6.21	6.27	6.73	7.22
	8H	13.29	13.70	13.80	14.19	14.76	5.89	6.30	6.40	6.79	7.36