

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1062199

Luminaire Tested: S125RDR-H850D927-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1062199
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-48)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDR-H850D927-X4F0-XX-UDD-BVL-B
Description: DEFINE 5 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 723.3 lumens
Efficiency: N/A
Efficacy: 30.8 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 0.81 / 0.97
Luminous Opening: Rectangular (W 0.39' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 23.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1062199

CATALOG NUMBER: S125RDR-H850D927-X4F0-XX-UDD-BVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1062199

CATALOG NUMBER: S125RDR-H850D927-X4F0-XX-UDD-BVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	83	82
3	98	90	84	80	96	89	83	79	86	82	78	84	80	76	81	78	75	73
4	92	83	76	71	90	82	75	70	79	74	70	77	72	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	81	70	63	58	79	69	62	57	67	61	57	66	61	57	65	60	56	54
7	76	65	58	53	74	64	57	52	63	56	52	61	56	52	60	55	51	50
8	71	60	53	48	70	59	53	48	58	52	48	57	52	48	56	51	47	46
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3855	3855	3855
5°	3849	3778	3778
10°	3826	3615	3501
15°	3770	3375	3164
20°	3680	3096	2755
25°	3569	2772	2345
30°	3418	2431	1914
35°	3272	2074	1434
40°	3094	1673	929
45°	2899	1266	403
50°	2666	807	150
55°	2403	354	107
60°	2034	153	72
65°	1540	96	36
70°	936	44	14
75°	197	19	19
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2899 cd/sqm



TEST NUMBER: P1062199

CATALOG NUMBER: S125RDR-H850D927-X4F0-XX-UDD-BVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	7.1
10°-20°	134.5	18.6
20°-30°	172.7	23.9
30°-40°	162.6	22.5
40°-50°	113.7	15.7
50°-60°	60.7	8.4
60°-70°	24.2	3.3
70°-80°	3.1	0.4
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	358.9	49.6
0°-40°	521.5	72.1
0°-60°	695.9	96.2
0°-90°	723.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	723.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	560	560	560	560	560	
5°	557	555	547	548	547	53
15°	529	512	474	451	444	149
25°	470	428	365	325	309	216
35°	389	327	247	191	171	243
45°	298	223	130	63	41	230
55°	200	123	30	10	9	177
65°	94	38	6	3	2	94
75°	7	2	1	1	1	14
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P1062199

CATALOG NUMBER: S125RDR-H850D927-X4F0-XX-UDD-BVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	559.9	559.9	559.9	559.9	559.9
2.5°	559.1	559.9	554.7	559.1	559.9
5°	556.9	555.4	546.6	548.1	546.6
7.5°	552.5	548.8	534.0	528.9	525.9
10°	547.3	539.2	517.0	506.0	500.8
12.5°	539.2	527.4	496.4	479.4	472.0
15°	528.9	511.9	473.5	451.3	443.9
17.5°	516.3	494.1	449.8	422.5	411.4
20°	502.3	472.7	422.5	390.0	376.0
22.5°	486.0	452.0	394.4	358.2	344.2
25°	469.8	428.4	364.9	325.0	308.7
27.5°	449.8	404.0	335.3	292.5	274.8
30°	429.9	379.7	305.8	259.3	240.8
32.5°	409.9	353.8	276.2	224.5	206.1
35°	389.3	327.2	246.7	190.6	170.6
37.5°	367.1	300.6	214.9	158.1	137.4
40°	344.2	274.8	186.1	126.3	103.4
42.5°	322.0	248.9	157.3	95.3	70.2
45°	297.7	223.1	130.0	62.8	41.4
47.5°	274.8	197.9	101.9	36.2	21.4
50°	248.9	172.1	75.3	19.2	14.0
52.5°	224.5	147.0	50.2	12.6	11.1
55°	200.2	122.6	29.5	10.3	8.9
57.5°	172.1	99.0	16.2	8.1	6.6
60°	147.7	77.6	11.1	5.9	5.2
62.5°	119.7	56.9	8.1	4.4	3.7
65°	94.5	37.7	5.9	3.0	2.2
67.5°	70.2	22.2	3.7	1.5	1.5
70°	46.5	11.8	2.2	0.7	0.7
72.5°	24.4	5.2	1.5	0.7	0.7
75°	7.4	2.2	0.7	0.7	0.7
77.5°	0.0	0.7	0.0	0.0	0.7
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1062199
 CATALOG NUMBER: S125RDR-H850D927-X4F0-XX-UDD-BVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.63	14.90	14.00	15.21	15.52	0.00	0.00	0.00	0.00	0.00
	3H	14.22	15.33	14.60	15.66	16.03	0.00	0.00	0.00	0.00	0.00
	4H	14.18	15.21	14.59	15.57	15.95	0.00	0.00	0.00	0.00	0.00
	6H	14.10	15.04	14.51	15.41	15.81	0.00	0.00	0.00	0.00	0.00
	8H	14.05	14.94	14.48	15.33	15.74	0.00	0.00	0.00	0.00	0.00
	12H	14.00	14.86	14.44	15.24	15.67	0.00	0.00	0.00	0.00	0.00
4H	2H	13.41	14.44	13.81	14.79	15.17	0.00	0.00	0.00	0.00	0.00
	3H	14.00	14.83	14.41	15.24	15.64	0.00	0.00	0.00	0.00	0.00
	4H	13.95	14.69	14.38	15.11	15.56	0.00	0.00	0.00	0.00	0.00
	6H	13.86	14.50	14.33	14.95	15.41	0.00	0.00	0.00	0.00	0.00
	8H	13.80	14.39	14.27	14.84	15.31	0.00	0.00	0.00	0.00	0.00
	12H	13.75	14.27	14.24	14.76	15.23	0.00	0.00	0.00	0.00	0.00
8H	4H	13.80	14.39	14.27	14.84	15.32	0.00	0.00	0.00	0.00	0.00
	6H	13.69	14.17	14.20	14.67	15.16	0.00	0.00	0.00	0.00	0.00
	8H	13.63	14.06	14.15	14.58	15.07	0.00	0.00	0.00	0.00	0.00
	12H	13.58	13.96	14.10	14.46	15.03	0.00	0.00	0.00	0.00	0.00
12H	4H	13.75	14.27	14.24	14.76	15.23	0.00	0.00	0.00	0.00	0.00
	6H	13.63	14.06	14.15	14.58	15.07	0.00	0.00	0.00	0.00	0.00
	8H	13.58	13.96	14.10	14.46	15.03	0.00	0.00	0.00	0.00	0.00