

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929885

Luminaire Tested: DFN2DS-4P3F0-040DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929885
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-040DS927-FLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3136.3 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 40.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929885

CATALOG NUMBER: DFN2DS-4P3F0-040DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929885

CATALOG NUMBER: DFN2DS-4P3F0-040DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1405	1405	1405
5°	1410	1390	1398
10°	1402	1376	1383
15°	1384	1358	1357
20°	1360	1331	1330
25°	1335	1298	1298
30°	1304	1268	1257
35°	1275	1232	1214
40°	1238	1195	1173
45°	1202	1160	1131
50°	1162	1122	1082
55°	1121	1079	1039
60°	1075	1027	989
65°	1026	975	930
70°	964	912	869
75°	877	840	819
80°	778	754	716
85°	634	605	543

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1202 cd/sqm

TEST NUMBER: P929885

CATALOG NUMBER: DFN2DS-4P3F0-040DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.0	3.7
10°-20°	326.4	10.4
20°-30°	479.7	15.3
30°-40°	557.2	17.8
40°-50°	556.5	17.7
50°-60°	485.2	15.5
60°-70°	358.7	11.4
70°-80°	202.9	6.5
80°-90°	53.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	922.2	29.4
0°-40°	1479.4	47.2
0°-60°	2521.1	80.4
0°-90°	3136.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3136.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1233	1233	1233	1233	1233	
5°	1233	1228	1215	1224	1222	117
15°	1173	1166	1151	1156	1150	330
25°	1062	1053	1032	1035	1032	489
35°	916	904	886	878	872	572
45°	746	737	720	706	702	575
55°	564	557	543	529	523	504
65°	381	373	362	351	345	376
75°	199	197	191	184	186	213
85°	48	47	46	43	42	57
90°	0	0	0	0	0	

TEST NUMBER: P929885

CATALOG NUMBER: DFN2DS-4P3F0-040DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1232.7	1232.7	1232.7	1232.7	1232.7
2.5°	1239.9	1233.9	1220.9	1232.7	1230.5
5°	1232.7	1228.0	1214.9	1224.4	1222.1
7.5°	1224.4	1217.3	1204.2	1213.8	1211.4
10°	1211.4	1203.1	1189.0	1198.4	1194.8
12.5°	1193.5	1186.5	1172.3	1178.3	1175.8
15°	1173.4	1166.4	1150.9	1155.7	1149.8
17.5°	1148.6	1141.5	1126.1	1131.9	1126.1
20°	1121.2	1114.2	1097.6	1101.1	1096.5
22.5°	1094.1	1083.4	1067.9	1067.9	1065.6
25°	1062.0	1052.6	1032.5	1034.7	1032.5
27.5°	1026.4	1018.1	1002.8	999.3	993.4
30°	991.0	981.4	963.7	960.1	955.4
32.5°	953.0	946.0	927.0	919.8	915.0
35°	916.3	904.5	885.5	878.3	872.4
37.5°	874.8	864.1	845.1	836.8	830.9
40°	832.2	822.6	803.6	793.0	788.3
42.5°	790.7	781.1	762.2	750.3	743.2
45°	745.6	737.4	719.5	706.5	701.7
47.5°	701.7	693.4	674.5	661.4	654.4
50°	655.5	649.5	633.0	616.3	610.4
52.5°	610.4	602.2	586.8	573.7	565.4
55°	564.3	557.1	542.9	528.7	522.8
57.5°	518.0	512.1	496.6	482.4	477.7
60°	471.7	467.0	450.5	437.4	433.9
62.5°	426.7	418.4	406.6	394.7	390.0
65°	380.6	373.3	361.5	350.9	345.0
67.5°	333.1	327.1	316.6	308.2	303.5
70°	289.2	284.5	273.8	265.5	260.8
72.5°	244.3	239.4	233.6	225.2	221.7
75°	199.1	196.8	190.8	183.7	186.1
77.5°	158.8	154.0	151.7	148.1	144.6
80°	118.6	117.3	114.9	111.4	109.1
82.5°	80.6	80.6	79.5	74.7	74.7
85°	48.5	47.4	46.3	42.6	41.5
87.5°	21.4	19.0	16.6	13.1	11.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929885

CATALOG NUMBER: DFN2DS-4P3F0-040DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.46	14.07	12.83	14.39	14.70	12.02	13.63	12.38	13.94	14.26
	3H	14.21	15.67	14.59	15.99	16.36	13.72	15.18	14.10	15.50	15.86
	4H	14.86	16.23	15.26	16.58	16.95	14.36	15.73	14.76	16.08	16.46
	6H	15.33	16.60	15.74	16.96	17.35	14.83	16.10	15.24	16.46	16.85
	8H	15.47	16.68	15.90	17.07	17.47	14.97	16.18	15.39	16.57	16.97
	12H	15.56	16.72	15.99	17.10	17.53	15.05	16.21	15.48	16.59	17.02
4H	2H	13.02	14.39	13.42	14.74	15.12	12.67	14.04	13.07	14.39	14.76
	3H	15.00	16.15	15.41	16.54	16.94	14.59	15.74	15.00	16.14	16.54
	4H	15.78	16.81	16.21	17.22	17.66	15.35	16.39	15.78	16.80	17.24
	6H	16.37	17.28	16.83	17.72	18.17	15.94	16.84	16.39	17.28	17.74
	8H	16.56	17.41	17.02	17.85	18.32	16.12	16.97	16.58	17.41	17.88
	12H	16.69	17.45	17.17	17.93	18.40	16.24	17.00	16.72	17.48	17.95
8H	4H	16.05	16.90	16.51	17.34	17.80	15.67	16.52	16.14	16.96	17.43
	6H	16.76	17.47	17.26	17.95	18.43	16.38	17.08	16.88	17.57	18.05
	8H	17.02	17.65	17.53	18.16	18.65	16.63	17.26	17.14	17.77	18.25
	12H	17.22	17.78	17.73	18.27	18.83	16.81	17.37	17.32	17.86	18.42
12H	4H	16.07	16.83	16.55	17.31	17.78	15.71	16.47	16.19	16.95	17.42
	6H	16.81	17.44	17.32	17.95	18.43	16.44	17.07	16.95	17.58	18.06
	8H	17.12	17.68	17.63	18.17	18.73	16.74	17.30	17.25	17.79	18.35