

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929886

Luminaire Tested: DFN2DS-4P3F0-040DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929886
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-040DS927-RLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2692.8 lumens
Efficiency: N/A
Efficacy: 66.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 40.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929886

CATALOG NUMBER: DFN2DS-4P3F0-040DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P929886

CATALOG NUMBER: DFN2DS-4P3F0-040DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1492	1492	1492
5°	1498	1473	1482
10°	1486	1449	1437
15°	1469	1406	1366
20°	1446	1345	1277
25°	1421	1275	1192
30°	1388	1204	1082
35°	1355	1126	986
40°	1322	1045	874
45°	1283	955	773
50°	1244	863	674
55°	1203	765	579
60°	1156	662	481
65°	1102	556	438
70°	1039	458	403
75°	960	417	376
80°	847	373	343
85°	666	294	294

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1283 cd/sqm

TEST NUMBER: P929886

CATALOG NUMBER: DFN2DS-4P3F0-040DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	4.6
10°-20°	336.9	12.5
20°-30°	473.0	17.6
30°-40°	515.5	19.1
40°-50°	473.8	17.6
50°-60°	372.1	13.8
60°-70°	242.2	9.0
70°-80°	124.7	4.6
80°-90°	31.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	932.5	34.6
0°-40°	1448.1	53.8
0°-60°	2294.1	85.2
0°-90°	2692.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2692.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1309	1309	1309	1309	1309	
5°	1309	1303	1288	1299	1295	124
15°	1245	1232	1192	1170	1158	351
25°	1130	1092	1014	966	948	520
35°	974	914	809	735	708	610
45°	796	717	592	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	61
90°	0	0	0	0	0	

TEST NUMBER: P929886

CATALOG NUMBER: DFN2DS-4P3F0-040DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1309.3	1309.3	1309.3	1309.3	1309.3
2.5°	1315.3	1309.3	1296.3	1308.2	1305.8
5°	1309.3	1303.4	1288.0	1298.6	1295.2
7.5°	1298.6	1291.6	1275.0	1279.6	1273.8
10°	1284.5	1276.1	1252.5	1248.8	1241.9
12.5°	1266.7	1256.0	1224.0	1216.9	1203.8
15°	1245.3	1232.3	1192.0	1169.5	1157.7
17.5°	1220.5	1201.5	1151.6	1125.7	1106.7
20°	1192.0	1168.3	1109.0	1079.5	1053.4
22.5°	1161.2	1134.0	1065.2	1024.9	1007.3
25°	1130.4	1092.5	1014.2	965.8	947.9
27.5°	1093.8	1053.4	966.9	911.2	883.9
30°	1054.6	1009.5	914.7	854.3	822.3
32.5°	1016.7	962.1	865.0	793.9	764.2
35°	974.1	913.6	809.3	734.7	708.5
37.5°	932.6	867.3	757.2	675.3	645.8
40°	888.7	817.7	702.7	618.6	587.7
42.5°	843.6	767.8	648.2	560.4	530.9
45°	796.3	716.8	592.5	508.3	479.9
47.5°	751.3	667.2	539.2	455.0	428.9
50°	701.5	617.4	487.0	405.2	380.4
52.5°	652.8	564.0	437.3	359.0	336.5
55°	605.5	513.1	385.1	314.0	291.5
57.5°	556.9	462.1	338.9	272.5	253.6
60°	507.1	412.3	290.3	229.9	211.0
62.5°	458.6	363.8	248.8	192.0	182.6
65°	408.8	312.8	206.2	165.9	162.3
67.5°	361.5	265.4	165.9	145.7	142.2
70°	311.7	219.2	137.4	125.6	120.8
72.5°	264.3	176.5	114.9	105.5	103.1
75°	218.0	135.0	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.7	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929886

CATALOG NUMBER: DFN2DS-4P3F0-040DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.62	14.15	12.99	14.46	14.77	8.58	10.11	8.95	10.42	10.73
	3H	14.39	15.76	14.77	16.08	16.45	9.85	11.22	10.23	11.54	11.91
	4H	15.06	16.34	15.46	16.69	17.06	10.35	11.63	10.75	11.98	12.36
	6H	15.55	16.73	15.96	17.10	17.49	10.73	11.92	11.15	12.28	12.67
	8H	15.71	16.84	16.14	17.23	17.63	10.86	11.98	11.28	12.37	12.78
	12H	15.81	16.89	16.24	17.27	17.70	10.94	12.02	11.37	12.40	12.83
4H	2H	12.73	14.01	13.13	14.36	14.74	9.28	10.56	9.68	10.91	11.29
	3H	14.66	15.73	15.07	16.13	16.53	10.72	11.79	11.13	12.19	12.59
	4H	15.41	16.37	15.84	16.78	17.22	11.32	12.28	11.76	12.70	13.13
	6H	16.00	16.84	16.46	17.28	17.74	11.81	12.64	12.27	13.09	13.55
	8H	16.22	17.00	16.68	17.44	17.91	11.97	12.75	12.44	13.20	13.66
	12H	16.37	17.07	16.85	17.54	18.02	12.09	12.79	12.57	13.26	13.74
8H	4H	15.44	16.21	15.90	16.66	17.12	11.68	12.45	12.14	12.90	13.37
	6H	16.07	16.72	16.57	17.21	17.68	12.26	12.91	12.76	13.40	13.88
	8H	16.32	16.90	16.84	17.41	17.90	12.49	13.06	13.00	13.57	14.06
	12H	16.53	17.04	17.04	17.53	18.09	12.66	13.17	13.17	13.67	14.23
12H	4H	15.42	16.11	15.90	16.59	17.06	11.72	12.42	12.20	12.89	13.36
	6H	16.05	16.63	16.57	17.14	17.63	12.33	12.91	12.84	13.41	13.90
	8H	16.34	16.85	16.85	17.34	17.91	12.60	13.11	13.11	13.60	14.17