

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929922

Luminaire Tested: DFN2DS-4P3F0-060DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929922
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-060DS927-RLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4039.2 lumens
Efficiency: N/A
Efficacy: 62.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 65
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929922

CATALOG NUMBER: DFN2DS-4P3F0-060DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P929922

CATALOG NUMBER: DFN2DS-4P3F0-060DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2238	2238	2238
5°	2247	2210	2222
10°	2229	2174	2155
15°	2204	2109	2049
20°	2168	2018	1916
25°	2132	1913	1788
30°	2082	1806	1623
35°	2033	1689	1479
40°	1983	1568	1312
45°	1925	1432	1160
50°	1866	1295	1012
55°	1804	1148	869
60°	1734	992	721
65°	1654	834	657
70°	1557	687	604
75°	1440	626	564
80°	1271	559	513
85°	998	441	441

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1925 cd/sqm

TEST NUMBER: P929922

CATALOG NUMBER: DFN2DS-4P3F0-060DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.1	4.6
10°-20°	505.3	12.5
20°-30°	709.4	17.6
30°-40°	773.3	19.1
40°-50°	710.8	17.6
50°-60°	558.2	13.8
60°-70°	363.3	9.0
70°-80°	187.0	4.6
80°-90°	47.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1398.8	34.6
0°-40°	2172.1	53.8
0°-60°	3441.1	85.2
0°-90°	4039.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4039.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1964	1964	1964	1964	1964	
5°	1964	1955	1932	1948	1943	186
15°	1868	1848	1788	1754	1736	526
25°	1696	1639	1521	1449	1422	780
35°	1461	1370	1214	1102	1063	914
45°	1194	1075	889	762	720	922
55°	908	770	578	471	437	812
65°	613	469	309	249	244	608
75°	327	202	142	130	128	346
85°	76	39	34	34	34	92
90°	0	0	0	0	0	

TEST NUMBER: P929922

CATALOG NUMBER: DFN2DS-4P3F0-060DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.0	1964.0	1964.0	1964.0	1964.0
2.5°	1972.9	1964.0	1944.4	1962.3	1958.7
5°	1964.0	1955.1	1931.9	1948.0	1942.7
7.5°	1948.0	1937.4	1912.5	1919.5	1910.6
10°	1926.6	1914.2	1878.8	1873.3	1862.7
12.5°	1900.1	1884.0	1835.9	1825.4	1805.8
15°	1868.0	1848.4	1788.0	1754.3	1736.5
17.5°	1830.7	1802.2	1727.5	1688.5	1660.0
20°	1788.0	1752.4	1663.6	1619.2	1580.0
22.5°	1741.8	1700.9	1597.8	1537.4	1510.8
25°	1695.7	1638.7	1521.4	1448.6	1421.9
27.5°	1640.6	1580.0	1450.3	1366.8	1325.9
30°	1581.9	1514.2	1372.1	1281.5	1233.5
32.5°	1525.0	1443.2	1297.6	1190.9	1146.3
35°	1461.1	1370.4	1214.1	1102.0	1062.8
37.5°	1398.8	1300.9	1135.8	1013.0	968.7
40°	1333.0	1226.5	1053.9	927.7	881.6
42.5°	1265.5	1151.8	972.3	840.6	796.4
45°	1194.4	1075.2	888.8	762.4	719.8
47.5°	1126.9	1000.8	808.8	682.5	643.4
50°	1052.3	926.1	730.5	607.8	570.6
52.5°	979.2	845.9	655.9	538.6	504.8
55°	908.2	769.6	577.6	471.1	437.3
57.5°	835.4	693.2	508.4	408.8	380.3
60°	760.7	618.6	435.4	344.9	316.4
62.5°	687.9	545.8	373.2	288.0	273.8
65°	613.2	469.2	309.3	248.9	243.5
67.5°	542.1	398.1	248.9	218.6	213.3
70°	467.4	328.8	206.1	188.4	181.2
72.5°	396.4	264.8	172.3	158.2	154.6
75°	327.0	202.5	142.2	129.7	128.1
77.5°	257.8	143.9	112.0	104.9	101.3
80°	193.6	103.1	85.2	78.2	78.2
82.5°	135.0	69.4	58.6	55.0	55.0
85°	76.3	39.0	33.7	33.7	33.7
87.5°	28.5	14.2	14.2	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929922

CATALOG NUMBER: DFN2DS-4P3F0-060DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.03	15.56	14.40	15.87	16.18	9.99	11.52	10.36	11.83	12.14
	3H	15.80	17.16	16.18	17.49	17.85	11.26	12.62	11.64	12.95	13.31
	4H	16.47	17.75	16.87	18.09	18.47	11.76	13.04	12.16	13.39	13.77
	6H	16.95	18.14	17.37	18.50	18.90	12.14	13.33	12.55	13.69	14.08
	8H	17.12	18.25	17.55	18.64	19.04	12.27	13.39	12.69	13.78	14.18
	12H	17.22	18.30	17.65	18.68	19.11	12.35	13.43	12.78	13.81	14.24
4H	2H	14.14	15.42	14.54	15.77	16.15	10.69	11.97	11.09	12.32	12.70
	3H	16.07	17.13	16.48	17.53	17.93	12.13	13.20	12.54	13.60	14.00
	4H	16.82	17.78	17.25	18.19	18.63	12.73	13.69	13.16	14.10	14.54
	6H	17.41	18.24	17.87	18.69	19.15	13.22	14.05	13.68	14.50	14.95
	8H	17.63	18.40	18.09	18.85	19.32	13.38	14.16	13.85	14.60	15.07
	12H	17.78	18.47	18.26	18.95	19.42	13.50	14.19	13.98	14.67	15.14
8H	4H	16.84	17.62	17.31	18.07	18.53	13.09	13.86	13.55	14.31	14.77
	6H	17.48	18.12	17.98	18.62	19.09	13.67	14.32	14.17	14.81	15.28
	8H	17.73	18.31	18.25	18.82	19.31	13.89	14.47	14.41	14.98	15.47
	12H	17.94	18.45	18.45	18.94	19.50	14.07	14.58	14.58	15.07	15.64
12H	4H	16.83	17.52	17.31	18.00	18.47	13.13	13.82	13.61	14.30	14.77
	6H	17.46	18.04	17.98	18.55	19.04	13.74	14.31	14.25	14.82	15.31
	8H	17.75	18.26	18.26	18.75	19.31	14.01	14.52	14.52	15.01	15.58

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7