

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929907

Luminaire Tested: DFN2DS-4P3F0-050DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929907
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-050DS935-FLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4257.0 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 51.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929907

CATALOG NUMBER: DFN2DS-4P3F0-050DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929907

CATALOG NUMBER: DFN2DS-4P3F0-050DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1907	1907	1907
5°	1914	1886	1898
10°	1903	1867	1877
15°	1879	1843	1841
20°	1846	1807	1805
25°	1813	1762	1762
30°	1770	1721	1706
35°	1730	1672	1647
40°	1680	1623	1592
45°	1631	1574	1535
50°	1577	1523	1469
55°	1522	1464	1410
60°	1459	1394	1342
65°	1393	1323	1263
70°	1308	1238	1180
75°	1190	1140	1113
80°	1057	1024	971
85°	862	821	736

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1631 cd/sqm

TEST NUMBER: P929907

CATALOG NUMBER: DFN2DS-4P3F0-050DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.5	3.7
10°-20°	443.1	10.4
20°-30°	651.1	15.3
30°-40°	756.3	17.8
40°-50°	755.3	17.7
50°-60°	658.6	15.5
60°-70°	486.9	11.4
70°-80°	275.5	6.5
80°-90°	72.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1251.7	29.4
0°-40°	2008.0	47.2
0°-60°	3421.9	80.4
0°-90°	4257.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4257.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1673	1673	1673	1673	1673	
5°	1673	1667	1649	1662	1659	159
15°	1593	1583	1562	1569	1561	449
25°	1442	1429	1401	1404	1401	663
35°	1244	1228	1202	1192	1184	777
45°	1012	1001	976	959	952	781
55°	766	756	737	718	710	685
65°	516	507	491	476	468	511
75°	270	267	259	249	253	288
85°	66	64	63	58	56	77
90°	0	0	0	0	0	

TEST NUMBER: P929907

CATALOG NUMBER: DFN2DS-4P3F0-050DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1673.1	1673.1	1673.1	1673.1	1673.1
2.5°	1682.8	1674.8	1657.1	1673.1	1670.1
5°	1673.1	1666.9	1649.0	1661.9	1658.9
7.5°	1661.9	1652.3	1634.6	1647.6	1644.3
10°	1644.3	1633.1	1613.8	1626.5	1621.8
12.5°	1620.1	1610.5	1591.3	1599.3	1596.0
15°	1592.7	1583.2	1562.2	1568.7	1560.6
17.5°	1558.9	1549.4	1528.4	1536.4	1528.4
20°	1521.9	1512.4	1489.9	1494.6	1488.3
22.5°	1485.0	1470.5	1449.5	1449.5	1446.3
25°	1441.5	1428.7	1401.4	1404.5	1401.4
27.5°	1393.2	1381.9	1361.1	1356.3	1348.3
30°	1345.0	1332.1	1308.1	1303.2	1296.8
32.5°	1293.5	1284.0	1258.2	1248.5	1242.0
35°	1243.6	1227.6	1201.8	1192.1	1184.1
37.5°	1187.3	1172.9	1147.1	1135.8	1127.8
40°	1129.5	1116.5	1090.7	1076.4	1069.9
42.5°	1073.2	1060.2	1034.6	1018.3	1008.8
45°	1012.0	1000.8	976.5	959.0	952.4
47.5°	952.4	941.2	915.5	897.7	888.1
50°	889.7	881.7	859.1	836.6	828.5
52.5°	828.5	817.3	796.4	778.7	767.5
55°	765.9	756.2	736.8	717.6	709.6
57.5°	703.0	695.1	674.1	654.8	648.3
60°	640.3	634.0	611.5	593.7	588.9
62.5°	579.2	567.9	551.9	535.8	529.3
65°	516.5	506.8	490.7	476.3	468.2
67.5°	452.2	444.0	429.7	418.4	411.9
70°	392.6	386.1	371.6	360.3	354.1
72.5°	331.5	325.0	317.0	305.7	300.9
75°	270.2	267.1	258.9	249.4	252.7
77.5°	215.6	209.1	205.9	201.1	196.3
80°	161.0	159.3	156.0	151.3	148.0
82.5°	109.4	109.4	107.8	101.4	101.4
85°	65.9	64.3	62.8	57.9	56.3
87.5°	29.0	25.8	22.5	17.7	16.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929907

CATALOG NUMBER: DFN2DS-4P3F0-050DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.53	15.14	13.89	15.45	15.76	13.08	14.69	13.45	15.01	15.32
	3H	15.28	16.73	15.65	17.06	17.42	14.78	16.24	15.16	16.57	16.93
	4H	15.92	17.29	16.32	17.64	18.01	15.43	16.80	15.83	17.14	17.52
	6H	16.39	17.66	16.80	18.02	18.41	15.89	17.16	16.30	17.52	17.91
	8H	16.53	17.74	16.96	18.13	18.53	16.03	17.24	16.46	17.63	18.03
	12H	16.62	17.78	17.05	18.17	18.59	16.11	17.27	16.54	17.65	18.08
4H	2H	14.09	15.45	14.48	15.80	16.18	13.73	15.10	14.13	15.45	15.83
	3H	16.06	17.21	16.47	17.60	18.00	15.65	16.80	16.06	17.20	17.60
	4H	16.84	17.87	17.27	18.29	18.72	16.41	17.45	16.84	17.86	18.30
	6H	17.43	18.34	17.89	18.78	19.24	17.00	17.91	17.46	18.35	18.80
	8H	17.62	18.47	18.08	18.91	19.38	17.19	18.03	17.65	18.47	18.94
	12H	17.75	18.51	18.24	18.99	19.46	17.30	18.06	17.78	18.54	19.01
8H	4H	17.11	17.96	17.57	18.40	18.86	16.74	17.58	17.20	18.03	18.49
	6H	17.82	18.53	18.32	19.02	19.49	17.44	18.15	17.94	18.63	19.11
	8H	18.08	18.71	18.59	19.22	19.71	17.69	18.32	18.20	18.83	19.32
	12H	18.28	18.84	18.79	19.33	19.89	17.87	18.43	18.38	18.92	19.48
12H	4H	17.14	17.90	17.62	18.37	18.84	16.77	17.53	17.25	18.01	18.48
	6H	17.87	18.50	18.38	19.01	19.49	17.50	18.13	18.01	18.64	19.13
	8H	18.18	18.74	18.69	19.23	19.79	17.81	18.36	18.31	18.85	19.42