

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P987522

Luminaire Tested: S122DR-B675DB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P987522
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DR-B675DB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Direct Recessed with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2715.0 lumens
Efficiency: N/A
Efficacy: 75.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 35.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P987522

CATALOG NUMBER: S122DR-B675DB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P987522

CATALOG NUMBER: S122DR-B675DB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86		84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73		71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62		60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54		51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47		45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41		39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37		35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33		31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30		28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16891	16891	16891
5°	16956	16713	16810
10°	16856	16543	16625
15°	16647	16327	16311
20°	16352	16006	15988
25°	16058	15609	15609
30°	15679	15248	15116
35°	15328	14812	14593
40°	14884	14376	14101
45°	14448	13942	13599
50°	13973	13493	13012
55°	13479	12971	12488
60°	12929	12344	11891
65°	12338	11724	11184
70°	11589	10969	10446
75°	10544	10104	9853
80°	9353	9070	8605
85°	7646	7265	6520

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14448 cd/sqm

TEST NUMBER: P987522

CATALOG NUMBER: S122DR-B675DB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.4	3.7
10°-20°	282.6	10.4
20°-30°	415.3	15.3
30°-40°	482.3	17.8
40°-50°	481.7	17.7
50°-60°	420.0	15.5
60°-70°	310.5	11.4
70°-80°	175.7	6.5
80°-90°	46.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	798.3	29.4
0°-40°	1280.6	47.2
0°-60°	2182.4	80.4
0°-90°	2715.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2715.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1067	1067	1067	1067	1067	
5°	1067	1063	1052	1060	1058	101
15°	1016	1010	996	1000	995	286
25°	919	911	894	896	894	423
35°	793	783	766	760	755	495
45°	645	638	623	612	608	498
55°	488	482	470	458	452	437
65°	329	323	313	304	299	326
75°	172	170	165	159	161	184
85°	42	41	40	37	36	49
90°	0	0	0	0	0	

TEST NUMBER: P987522

CATALOG NUMBER: S122DR-B675DB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1067.1	1067.1	1067.1	1067.1	1067.1
2.5°	1073.3	1068.2	1056.9	1067.1	1065.1
5°	1067.1	1063.0	1051.8	1060.0	1057.9
7.5°	1060.0	1053.8	1042.5	1050.7	1048.7
10°	1048.7	1041.5	1029.2	1037.4	1034.3
12.5°	1033.3	1027.1	1014.8	1019.9	1017.9
15°	1015.8	1009.7	996.3	1000.5	995.3
17.5°	994.3	988.1	974.8	979.9	974.8
20°	970.7	964.5	950.2	953.3	949.1
22.5°	947.1	937.9	924.5	924.5	922.5
25°	919.4	911.2	893.7	895.8	893.7
27.5°	888.6	881.4	868.1	865.0	859.9
30°	857.8	849.6	834.2	831.1	827.0
32.5°	825.0	818.8	802.4	796.3	792.2
35°	793.2	782.9	766.5	760.3	755.2
37.5°	757.3	748.0	731.6	724.4	719.3
40°	720.3	712.1	695.7	686.5	682.4
42.5°	684.4	676.2	659.8	649.5	643.4
45°	645.4	638.2	622.8	611.6	607.5
47.5°	607.5	600.3	583.9	572.6	566.4
50°	567.4	562.3	547.9	533.6	528.4
52.5°	528.4	521.3	507.9	496.6	489.5
55°	488.4	482.3	470.0	457.6	452.5
57.5°	448.4	443.3	429.9	417.6	413.5
60°	408.4	404.3	389.9	378.6	375.6
62.5°	369.4	362.2	352.0	341.7	337.6
65°	329.4	323.2	313.0	303.7	298.6
67.5°	288.3	283.2	274.0	266.8	262.7
70°	250.4	246.3	237.0	229.8	225.7
72.5°	211.4	207.3	202.1	195.0	191.9
75°	172.4	170.3	165.2	159.0	161.1
77.5°	137.5	133.4	131.3	128.3	125.2
80°	102.6	101.6	99.5	96.5	94.4
82.5°	69.8	69.8	68.7	64.6	64.6
85°	42.1	41.0	40.0	36.9	35.9
87.5°	18.5	16.4	14.4	11.3	10.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)