

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929891

Luminaire Tested: DFN2DS-4P3F0-040DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929891
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-040DS940-FLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3532.3 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 40.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929891

CATALOG NUMBER: DFN2DS-4P3F0-040DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929891

CATALOG NUMBER: DFN2DS-4P3F0-040DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1582	1582	1582
5°	1588	1565	1575
10°	1579	1550	1557
15°	1559	1529	1528
20°	1531	1499	1498
25°	1504	1462	1462
30°	1469	1428	1416
35°	1436	1387	1367
40°	1394	1346	1321
45°	1353	1306	1274
50°	1309	1264	1219
55°	1263	1215	1170
60°	1211	1156	1114
65°	1156	1098	1048
70°	1086	1028	979
75°	987	946	923
80°	876	849	806
85°	715	681	611

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1353 cd/sqm

TEST NUMBER: P929891

CATALOG NUMBER: DFN2DS-4P3F0-040DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.7	3.7
10°-20°	367.6	10.4
20°-30°	540.3	15.3
30°-40°	627.5	17.8
40°-50°	626.8	17.7
50°-60°	546.5	15.5
60°-70°	404.0	11.4
70°-80°	228.6	6.5
80°-90°	60.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1038.6	29.4
0°-40°	1666.2	47.2
0°-60°	2839.4	80.4
0°-90°	3532.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3532.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1388	1383	1368	1379	1376	132
15°	1322	1314	1296	1302	1295	372
25°	1196	1186	1163	1165	1163	550
35°	1032	1019	997	989	982	644
45°	840	830	810	796	790	648
55°	636	627	612	595	589	568
65°	429	420	407	395	389	424
75°	224	222	215	207	210	239
85°	55	53	52	48	47	64
90°	0	0	0	0	0	

TEST NUMBER: P929891

CATALOG NUMBER: DFN2DS-4P3F0-040DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1396.4	1389.7	1375.0	1388.3	1385.8
5°	1388.3	1383.0	1368.3	1378.9	1376.4
7.5°	1378.9	1371.0	1356.3	1367.1	1364.4
10°	1364.4	1355.0	1339.1	1349.7	1345.7
12.5°	1344.2	1336.3	1320.3	1327.0	1324.3
15°	1321.6	1313.6	1296.3	1301.6	1295.0
17.5°	1293.6	1285.6	1268.2	1274.8	1268.2
20°	1262.8	1254.9	1236.2	1240.1	1235.0
22.5°	1232.2	1220.2	1202.8	1202.8	1200.1
25°	1196.1	1185.5	1162.8	1165.4	1162.8
27.5°	1156.0	1146.7	1129.5	1125.4	1118.8
30°	1116.1	1105.4	1085.4	1081.4	1076.0
32.5°	1073.3	1065.4	1044.0	1036.0	1030.5
35°	1032.0	1018.7	997.3	989.2	982.5
37.5°	985.2	973.2	951.8	942.5	935.8
40°	937.2	926.4	905.0	893.2	887.8
42.5°	890.5	879.7	858.5	845.0	837.1
45°	839.7	830.5	810.3	795.8	790.3
47.5°	790.3	780.9	759.6	744.9	737.0
50°	738.2	731.5	712.9	694.2	687.5
52.5°	687.5	678.2	660.9	646.2	636.8
55°	635.6	627.4	611.5	595.4	588.8
57.5°	583.4	576.8	559.3	543.3	538.0
60°	531.3	526.0	507.4	492.7	488.6
62.5°	480.6	471.2	458.0	444.6	439.2
65°	428.6	420.5	407.2	395.2	388.6
67.5°	375.2	368.4	356.5	347.2	341.8
70°	325.8	320.4	308.4	299.0	293.7
72.5°	275.1	269.7	263.1	253.7	249.7
75°	224.2	221.7	214.9	206.9	209.6
77.5°	178.8	173.5	170.8	166.8	162.9
80°	133.5	132.1	129.4	125.5	122.8
82.5°	90.8	90.8	89.6	84.1	84.1
85°	54.7	53.4	52.1	48.0	46.7
87.5°	24.1	21.4	18.7	14.7	13.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929891

CATALOG NUMBER: DFN2DS-4P3F0-040DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.88	14.49	13.24	14.80	15.12	12.43	14.04	12.80	14.36	14.67
	3H	14.63	16.08	15.00	16.41	16.77	14.14	15.59	14.51	15.92	16.28
	4H	15.27	16.64	15.67	16.99	17.37	14.78	16.15	15.18	16.49	16.87
	6H	15.74	17.01	16.15	17.38	17.77	15.24	16.51	15.65	16.87	17.26
	8H	15.88	17.10	16.31	17.48	17.88	15.38	16.59	15.81	16.98	17.38
	12H	15.98	17.14	16.40	17.52	17.95	15.46	16.62	15.89	17.00	17.43
4H	2H	13.44	14.81	13.84	15.15	15.53	13.08	14.45	13.48	14.80	15.18
	3H	15.41	16.56	15.82	16.96	17.36	15.01	16.15	15.42	16.55	16.95
	4H	16.19	17.22	16.62	17.64	18.07	15.76	16.80	16.20	17.21	17.65
	6H	16.79	17.69	17.24	18.13	18.59	16.35	17.26	16.81	17.70	18.15
	8H	16.97	17.82	17.44	18.26	18.73	16.54	17.38	17.00	17.83	18.29
	12H	17.11	17.87	17.59	18.34	18.81	16.65	17.41	17.13	17.89	18.36
8H	4H	16.46	17.31	16.92	17.75	18.22	16.09	16.93	16.55	17.38	17.84
	6H	17.18	17.88	17.67	18.37	18.84	16.79	17.50	17.29	17.99	18.46
	8H	17.44	18.07	17.95	18.57	19.06	17.04	17.67	17.55	18.18	18.67
	12H	17.64	18.19	18.14	18.68	19.24	17.22	17.78	17.73	18.27	18.83
12H	4H	16.49	17.25	16.97	17.72	18.19	16.12	16.88	16.60	17.36	17.83
	6H	17.22	17.85	17.73	18.36	18.85	16.85	17.48	17.36	17.99	18.48
	8H	17.54	18.09	18.04	18.58	19.14	17.16	17.72	17.66	18.21	18.77