

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P988986

Luminaire Tested: S122RDR-B675DB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P988986
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-24)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDR-B675DB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Regressed Direct Recessed with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2312.0 lumens
Efficiency: N/A
Efficacy: 64.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 35.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P988986

CATALOG NUMBER: S122RDR-B675DB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P988986

CATALOG NUMBER: S122RDR-B675DB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86		
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	74		
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	64		
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	55		
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43		
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39		
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	29		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17795	17795	17795
5°	17863	17572	17669
10°	17726	17284	17138
15°	17522	16773	16288
20°	17241	16040	15235
25°	16952	15211	14215
30°	16549	14356	12904
35°	16161	13426	11757
40°	15766	12466	10427
45°	15305	11388	9223
50°	14832	10296	8043
55°	14348	9124	6908
60°	13784	7892	5733
65°	13147	6630	5221
70°	12385	5461	4804
75°	11449	4978	4477
80°	10109	4448	4084
85°	7937	3505	3505

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15305 cd/sqm

TEST NUMBER: P988986

CATALOG NUMBER: S122RDR-B675DB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	4.6
10°-20°	289.2	12.5
20°-30°	406.1	17.6
30°-40°	442.6	19.1
40°-50°	406.8	17.6
50°-60°	319.5	13.8
60°-70°	208.0	9.0
70°-80°	107.1	4.6
80°-90°	27.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	800.7	34.6
0°-40°	1243.3	53.8
0°-60°	1969.7	85.2
0°-90°	2312.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2312.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1124	1124	1124	1124	1124	
5°	1124	1119	1106	1115	1112	107
15°	1069	1058	1024	1004	994	301
25°	971	938	871	829	814	446
35°	836	784	695	631	608	523
45°	684	616	509	436	412	528
55°	520	440	331	270	250	465
65°	351	269	177	142	139	348
75°	187	116	81	74	73	198
85°	44	22	19	19	19	52
90°	0	0	0	0	0	

TEST NUMBER: P988986

CATALOG NUMBER: S122RDR-B675DB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1124.2	1124.2	1124.2	1124.2	1124.2
2.5°	1129.3	1124.2	1113.0	1123.2	1121.1
5°	1124.2	1119.1	1105.9	1115.0	1112.0
7.5°	1115.0	1108.9	1094.7	1098.7	1093.6
10°	1102.8	1095.7	1075.3	1072.3	1066.2
12.5°	1087.5	1078.4	1050.9	1044.8	1033.6
15°	1069.2	1058.0	1023.5	1004.1	993.9
17.5°	1047.9	1031.6	988.9	966.5	950.2
20°	1023.5	1003.1	952.2	926.8	904.4
22.5°	997.0	973.6	914.6	880.0	864.7
25°	970.6	938.0	870.9	829.1	813.9
27.5°	939.0	904.4	830.2	782.3	758.9
30°	905.4	866.8	785.4	733.5	706.0
32.5°	872.9	826.1	742.7	681.6	656.2
35°	836.3	784.4	694.8	630.8	608.4
37.5°	800.7	744.7	650.1	579.9	554.5
40°	763.0	702.0	603.3	531.1	504.6
42.5°	724.4	659.2	556.5	481.2	455.8
45°	683.7	615.5	508.7	436.4	412.0
47.5°	645.0	572.8	462.9	390.7	368.3
50°	602.3	530.0	418.1	347.9	326.6
52.5°	560.6	484.3	375.4	308.3	288.9
55°	519.9	440.5	330.6	269.6	250.3
57.5°	478.2	396.8	291.0	234.0	217.7
60°	435.4	354.0	249.3	197.4	181.1
62.5°	393.7	312.3	213.6	164.8	156.7
65°	351.0	268.6	177.0	142.4	139.4
67.5°	310.3	227.9	142.4	125.1	122.1
70°	267.6	188.2	118.0	107.8	103.8
72.5°	226.9	151.6	98.7	90.5	88.5
75°	187.2	116.0	81.4	74.3	73.2
77.5°	147.5	82.4	64.1	60.0	58.0
80°	110.9	59.0	48.8	44.8	44.8
82.5°	77.3	39.7	33.6	31.5	31.5
85°	43.7	22.4	19.3	19.3	19.3
87.5°	16.3	8.1	8.1	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)