

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929892

Luminaire Tested: DFN2DS-4P3F0-040DS940-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929892
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-040DS940-RLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3032.8 lumens
Efficiency: N/A
Efficacy: 74.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 40.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929892

CATALOG NUMBER: DFN2DS-4P3F0-040DS940-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P929892

CATALOG NUMBER: DFN2DS-4P3F0-040DS940-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1681	1681	1681
5°	1687	1659	1669
10°	1674	1632	1619
15°	1655	1584	1538
20°	1628	1515	1439
25°	1601	1436	1342
30°	1563	1356	1219
35°	1526	1268	1110
40°	1489	1177	985
45°	1445	1075	871
50°	1401	972	760
55°	1355	862	652
60°	1302	745	542
65°	1242	626	493
70°	1170	516	453
75°	1081	470	424
80°	954	420	386
85°	751	331	331

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1445 cd/sqm

TEST NUMBER: P929892

CATALOG NUMBER: DFN2DS-4P3F0-040DS940-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	4.6
10°-20°	379.4	12.5
20°-30°	532.7	17.6
30°-40°	580.6	19.1
40°-50°	533.7	17.6
50°-60°	419.1	13.8
60°-70°	272.8	9.0
70°-80°	140.4	4.6
80°-90°	35.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1050.3	34.6
0°-40°	1630.9	53.8
0°-60°	2583.7	85.2
0°-90°	3032.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3032.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1475	1475	1475	1475	1475	
5°	1475	1468	1451	1463	1459	140
15°	1403	1388	1342	1317	1304	395
25°	1273	1230	1142	1088	1068	586
35°	1097	1029	912	827	798	687
45°	897	807	667	572	540	693
55°	682	578	434	354	328	609
65°	460	352	232	187	183	457
75°	246	152	107	97	96	260
85°	57	29	25	25	25	69
90°	0	0	0	0	0	

TEST NUMBER: P929892

CATALOG NUMBER: DFN2DS-4P3F0-040DS940-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1474.7	1474.7	1474.7	1474.7	1474.7
2.5°	1481.3	1474.7	1459.9	1473.4	1470.6
5°	1474.7	1468.0	1450.6	1462.6	1458.7
7.5°	1462.6	1454.7	1436.0	1441.2	1434.6
10°	1446.6	1437.3	1410.6	1406.5	1398.7
12.5°	1426.7	1414.6	1378.5	1370.6	1355.8
15°	1402.6	1387.9	1342.5	1317.2	1303.9
17.5°	1374.6	1353.2	1297.1	1267.8	1246.4
20°	1342.5	1315.8	1249.1	1215.8	1186.4
22.5°	1307.9	1277.2	1199.7	1154.3	1134.4
25°	1273.2	1230.4	1142.3	1087.7	1067.5
27.5°	1231.9	1186.4	1089.0	1026.2	995.5
30°	1187.8	1136.9	1030.2	962.2	926.2
32.5°	1145.1	1083.6	974.2	894.1	860.7
35°	1097.1	1028.9	911.5	827.4	798.0
37.5°	1050.3	976.8	852.8	760.6	727.3
40°	1000.9	920.9	791.4	696.7	662.0
42.5°	950.2	864.8	730.0	631.2	597.9
45°	896.8	807.3	667.3	572.5	540.5
47.5°	846.2	751.4	607.3	512.5	483.1
50°	790.0	695.3	548.5	456.3	428.4
52.5°	735.3	635.2	492.5	404.3	379.0
55°	681.9	577.8	433.7	353.7	328.3
57.5°	627.3	520.5	381.7	306.9	285.6
60°	571.1	464.4	326.9	258.9	237.6
62.5°	516.6	409.8	280.2	216.2	205.6
65°	460.5	352.3	232.2	186.9	182.8
67.5°	407.1	298.9	186.9	164.1	160.1
70°	351.0	246.9	154.8	141.5	136.0
72.5°	297.7	198.8	129.4	118.8	116.1
75°	245.5	152.1	106.8	97.4	96.2
77.5°	193.6	108.0	84.1	78.8	76.0
80°	145.4	77.4	64.0	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.4	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929892

CATALOG NUMBER: DFN2DS-4P3F0-040DS940-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.04	14.56	13.40	14.87	15.19	9.00	10.52	9.36	10.83	11.15
	3H	14.80	16.17	15.18	16.50	16.86	10.26	11.63	10.64	11.96	12.32
	4H	15.47	16.75	15.87	17.10	17.48	10.77	12.05	11.16	12.39	12.77
	6H	15.96	17.14	16.37	17.51	17.90	11.15	12.33	11.56	12.70	13.09
	8H	16.12	17.25	16.55	17.64	18.04	11.27	12.40	11.70	12.79	13.19
	12H	16.23	17.31	16.66	17.69	18.12	11.35	12.43	11.78	12.81	13.24
4H	2H	13.14	14.42	13.54	14.77	15.15	9.69	10.97	10.09	11.32	11.70
	3H	15.08	16.14	15.49	16.54	16.94	11.14	12.20	11.55	12.60	13.00
	4H	15.83	16.78	16.26	17.20	17.64	11.74	12.69	12.17	13.11	13.55
	6H	16.42	17.25	16.87	17.69	18.15	12.23	13.06	12.68	13.50	13.96
	8H	16.63	17.41	17.09	17.85	18.32	12.39	13.16	12.85	13.61	14.08
	12H	16.78	17.48	17.27	17.96	18.43	12.50	13.20	12.99	13.68	14.15
8H	4H	15.85	16.63	16.31	17.07	17.54	12.09	12.87	12.55	13.31	13.78
	6H	16.49	17.13	16.98	17.62	18.10	12.68	13.32	13.17	13.81	14.29
	8H	16.74	17.31	17.25	17.82	18.31	12.90	13.47	13.41	13.98	14.47
	12H	16.94	17.45	17.45	17.94	18.51	13.08	13.59	13.59	14.08	14.64
12H	4H	15.83	16.53	16.32	17.01	17.48	12.13	12.83	12.62	13.31	13.78
	6H	16.47	17.05	16.98	17.55	18.04	12.74	13.32	13.25	13.83	14.32
	8H	16.75	17.26	17.26	17.75	18.32	13.01	13.52	13.52	14.02	14.58