

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P988989

Luminaire Tested: S122RDR-B675DB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P988989
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-24)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDR-B675DB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Regressed Direct Recessed with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2319.0 lumens
Efficiency: N/A
Efficacy: 64.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 35.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P988989

CATALOG NUMBER: S122RDR-B675DB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P988989

CATALOG NUMBER: S122RDR-B675DB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86			
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	74			
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	64			
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	55			
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49			
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39			
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	35			
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	32			
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	29			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17849	17849	17849
5°	17917	17625	17722
10°	17779	17337	17189
15°	17576	16824	16339
20°	17293	16089	15282
25°	17003	15256	14257
30°	16600	14399	12945
35°	16209	13469	11791
40°	15814	12504	10458
45°	15350	11421	9252
50°	14877	10328	8067
55°	14389	9151	6927
60°	13825	7915	5749
65°	13184	6652	5236
70°	12422	5480	4818
75°	11486	4991	4495
80°	10137	4467	4093
85°	7973	3523	3523

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15350 cd/sqm

TEST NUMBER: P988989

CATALOG NUMBER: S122RDR-B675DB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.7	4.6
10°-20°	290.1	12.5
20°-30°	407.3	17.6
30°-40°	444.0	19.1
40°-50°	408.1	17.6
50°-60°	320.5	13.8
60°-70°	208.6	9.0
70°-80°	107.4	4.6
80°-90°	27.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	803.1	34.6
0°-40°	1247.1	53.8
0°-60°	1975.6	85.2
0°-90°	2319.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2319.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1128	1128	1128	1128	1128	
5°	1128	1122	1109	1118	1115	107
15°	1072	1061	1027	1007	997	302
25°	974	941	874	832	816	448
35°	839	787	697	633	610	525
45°	686	617	510	438	413	530
55°	521	442	332	270	251	466
65°	352	269	178	143	140	349
75°	188	116	82	74	74	199
85°	44	22	19	19	19	53
90°	0	0	0	0	0	

TEST NUMBER: P988989

CATALOG NUMBER: S122RDR-B675DB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1127.6	1127.6	1127.6	1127.6	1127.6
2.5°	1132.7	1127.6	1116.3	1126.6	1124.5
5°	1127.6	1122.5	1109.2	1118.4	1115.3
7.5°	1118.4	1112.3	1098.0	1102.1	1097.0
10°	1106.1	1099.0	1078.6	1075.5	1069.4
12.5°	1090.8	1081.7	1054.1	1048.0	1036.8
15°	1072.5	1061.2	1026.6	1007.2	997.0
17.5°	1051.0	1034.7	991.9	969.4	953.1
20°	1026.6	1006.1	955.1	929.6	907.2
22.5°	1000.0	976.6	917.4	882.7	867.4
25°	973.5	940.8	873.5	831.6	816.3
27.5°	941.9	907.2	832.7	784.7	761.2
30°	908.2	869.4	787.8	735.7	708.2
32.5°	875.5	828.6	744.9	683.7	658.2
35°	838.8	786.8	697.0	632.7	610.2
37.5°	803.1	747.0	652.1	581.6	556.1
40°	765.3	704.1	605.1	532.7	506.1
42.5°	726.5	661.2	558.2	482.7	457.2
45°	685.7	617.4	510.2	437.8	413.3
47.5°	647.0	574.5	464.3	391.8	369.4
50°	604.1	531.6	419.4	349.0	327.6
52.5°	562.3	485.7	376.5	309.2	289.8
55°	521.4	441.8	331.6	270.4	251.0
57.5°	479.6	398.0	291.8	234.7	218.4
60°	436.7	355.1	250.0	198.0	181.6
62.5°	394.9	313.3	214.3	165.3	157.1
65°	352.0	269.4	177.6	142.9	139.8
67.5°	311.2	228.6	142.9	125.5	122.5
70°	268.4	188.8	118.4	108.2	104.1
72.5°	227.6	152.0	99.0	90.8	88.8
75°	187.8	116.3	81.6	74.5	73.5
77.5°	148.0	82.7	64.3	60.2	58.2
80°	111.2	59.2	49.0	44.9	44.9
82.5°	77.6	39.8	33.7	31.6	31.6
85°	43.9	22.4	19.4	19.4	19.4
87.5°	16.3	8.2	8.2	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)