

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930023

Luminaire Tested: DFN2DS-4P4F0-080DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930023
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-080DS835-FLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7920.0 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 86.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930023

CATALOG NUMBER: DFN2DS-4P4F0-080DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930023

CATALOG NUMBER: DFN2DS-4P4F0-080DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2019	2019	2019
5°	2027	1998	2010
10°	2015	1978	1988
15°	1990	1952	1950
20°	1955	1914	1912
25°	1920	1866	1866
30°	1875	1823	1807
35°	1832	1771	1745
40°	1780	1719	1686
45°	1727	1667	1626
50°	1671	1613	1556
55°	1612	1551	1493
60°	1546	1476	1422
65°	1475	1401	1337
70°	1385	1311	1249
75°	1260	1208	1178
80°	1119	1085	1029
85°	913	870	780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1727 cd/sqm

TEST NUMBER: P930023

CATALOG NUMBER: DFN2DS-4P4F0-080DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.0	3.7
10°-20°	824.3	10.4
20°-30°	1211.5	15.3
30°-40°	1407.0	17.8
40°-50°	1405.3	17.7
50°-60°	1225.4	15.5
60°-70°	905.8	11.4
70°-80°	512.5	6.5
80°-90°	135.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2328.8	29.4
0°-40°	3735.8	47.2
0°-60°	6366.4	80.4
0°-90°	7920.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7920.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3113	3113	3113	3113	3113	
5°	3113	3101	3068	3092	3086	295
15°	2963	2946	2906	2918	2904	835
25°	2682	2658	2607	2613	2607	1234
35°	2314	2284	2236	2218	2203	1445
45°	1883	1862	1817	1784	1772	1453
55°	1425	1407	1371	1335	1320	1274
65°	961	943	913	886	871	950
75°	503	497	482	464	470	537
85°	123	120	117	108	105	144
90°	0	0	0	0	0	

TEST NUMBER: P930023

CATALOG NUMBER: DFN2DS-4P4F0-080DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3112.8	3112.8	3112.8	3112.8	3112.8
2.5°	3130.9	3116.0	3083.0	3112.8	3107.1
5°	3112.8	3101.1	3068.1	3091.9	3086.2
7.5°	3091.9	3074.1	3041.1	3065.2	3059.2
10°	3059.2	3038.2	3002.3	3026.1	3017.3
12.5°	3014.1	2996.3	2960.4	2975.3	2969.3
15°	2963.3	2945.5	2906.4	2918.5	2903.6
17.5°	2900.4	2882.6	2843.5	2858.5	2843.5
20°	2831.5	2813.7	2771.8	2780.7	2768.9
22.5°	2762.9	2735.9	2696.8	2696.8	2690.8
25°	2681.9	2658.1	2607.3	2613.0	2607.3
27.5°	2592.0	2571.1	2532.3	2523.4	2508.5
30°	2502.5	2478.3	2433.6	2424.7	2412.6
32.5°	2406.6	2388.8	2340.8	2322.7	2310.7
35°	2313.8	2284.0	2236.0	2217.9	2203.0
37.5°	2209.0	2182.0	2134.1	2113.1	2098.2
40°	2101.4	2077.2	2029.3	2002.6	1990.5
42.5°	1996.6	1972.4	1924.8	1894.6	1876.9
45°	1882.9	1861.9	1816.8	1784.1	1772.1
47.5°	1772.1	1751.1	1703.1	1670.1	1652.3
50°	1655.2	1640.3	1598.3	1556.4	1541.5
52.5°	1541.5	1520.5	1481.8	1448.8	1427.8
55°	1424.9	1406.8	1371.0	1335.1	1320.1
57.5°	1308.1	1293.2	1254.1	1218.2	1206.1
60°	1191.2	1179.5	1137.5	1104.5	1095.6
62.5°	1077.5	1056.6	1026.7	996.9	984.8
65°	961.0	942.9	913.0	886.0	871.1
67.5°	841.2	826.0	799.3	778.4	766.3
70°	730.4	718.3	691.4	670.4	658.6
72.5°	616.7	604.7	589.7	568.8	559.9
75°	502.7	497.0	481.8	464.0	470.0
77.5°	401.1	389.0	383.0	374.1	365.2
80°	299.5	296.3	290.3	281.4	275.3
82.5°	203.6	203.6	200.7	188.6	188.6
85°	122.6	119.7	116.9	107.7	104.8
87.5°	54.0	48.0	41.9	33.0	29.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930023

CATALOG NUMBER: DFN2DS-4P4F0-080DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.72	15.34	14.09	15.65	15.96	13.28	14.89	13.64	15.20	15.52
	3H	15.47	16.93	15.85	17.26	17.62	14.98	16.44	15.36	16.76	17.12
	4H	16.12	17.49	16.52	17.84	18.21	15.63	16.99	16.02	17.34	17.72
	6H	16.59	17.86	17.00	18.22	18.61	16.09	17.36	16.50	17.72	18.11
	8H	16.73	17.94	17.16	18.33	18.73	16.23	17.44	16.65	17.83	18.23
	12H	16.82	17.98	17.25	18.37	18.79	16.31	17.47	16.74	17.85	18.28
4H	2H	14.29	15.65	14.68	16.00	16.38	13.93	15.30	14.33	15.65	16.02
	3H	16.26	17.41	16.67	17.80	18.20	15.85	17.00	16.26	17.40	17.80
	4H	17.04	18.07	17.47	18.49	18.92	16.61	17.65	17.04	18.06	18.50
	6H	17.63	18.54	18.09	18.98	19.43	17.20	18.11	17.65	18.55	19.00
	8H	17.82	18.67	18.28	19.11	19.58	17.38	18.23	17.84	18.67	19.14
	12H	17.95	18.71	18.43	19.19	19.66	17.50	18.26	17.98	18.74	19.21
8H	4H	17.31	18.16	17.77	18.60	19.06	16.94	17.78	17.40	18.22	18.69
	6H	18.02	18.73	18.52	19.22	19.69	17.64	18.35	18.14	18.83	19.31
	8H	18.28	18.91	18.79	19.42	19.91	17.89	18.52	18.40	19.03	19.52
	12H	18.48	19.04	18.99	19.53	20.09	18.07	18.63	18.58	19.12	19.68
12H	4H	17.34	18.10	17.82	18.57	19.04	16.97	17.73	17.45	18.21	18.68
	6H	18.07	18.70	18.58	19.21	19.69	17.70	18.33	18.21	18.84	19.33
	8H	18.38	18.94	18.89	19.43	19.99	18.01	18.56	18.51	19.05	19.61