

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929975

Luminaire Tested: DFN2DS-4P4F0-050DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929975
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-050DS927-FLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3920.4 lumens
Efficiency: N/A
Efficacy: 77.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 50.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929975

CATALOG NUMBER: DFN2DS-4P4F0-050DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929975

CATALOG NUMBER: DFN2DS-4P4F0-050DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1000	1000	1000
5°	1003	989	995
10°	998	979	984
15°	985	966	965
20°	968	947	946
25°	950	924	924
30°	928	902	895
35°	907	877	864
40°	881	851	834
45°	855	825	805
50°	827	799	770
55°	798	768	739
60°	765	731	704
65°	730	694	662
70°	686	649	619
75°	624	598	583
80°	554	537	509
85°	452	430	386

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 855 cd/sqm

TEST NUMBER: P929975

CATALOG NUMBER: DFN2DS-4P4F0-050DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.0	3.7
10°-20°	408.0	10.4
20°-30°	599.7	15.3
30°-40°	696.5	17.8
40°-50°	695.6	17.7
50°-60°	606.6	15.5
60°-70°	448.4	11.4
70°-80°	253.7	6.5
80°-90°	67.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1152.7	29.4
0°-40°	1849.2	47.2
0°-60°	3151.4	80.4
0°-90°	3920.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3920.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1541	1541	1541	1541	1541	
5°	1541	1535	1519	1530	1528	146
15°	1467	1458	1439	1445	1437	413
25°	1328	1316	1291	1293	1291	611
35°	1145	1131	1107	1098	1090	715
45°	932	922	899	883	877	719
55°	705	696	679	661	654	631
65°	476	467	452	439	431	470
75°	249	246	238	230	233	266
85°	61	59	58	53	52	71
90°	0	0	0	0	0	

TEST NUMBER: P929975

CATALOG NUMBER: DFN2DS-4P4F0-050DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1540.8	1540.8	1540.8	1540.8	1540.8
2.5°	1549.8	1542.4	1526.1	1540.8	1538.1
5°	1540.8	1535.1	1518.7	1530.5	1527.7
7.5°	1530.5	1521.7	1505.4	1517.3	1514.3
10°	1514.3	1503.9	1486.2	1497.9	1493.6
12.5°	1492.0	1483.2	1465.4	1472.8	1469.8
15°	1466.8	1458.0	1438.7	1444.7	1437.2
17.5°	1435.7	1426.9	1407.5	1414.9	1407.5
20°	1401.6	1392.8	1372.1	1376.4	1370.6
22.5°	1367.6	1354.2	1334.9	1334.9	1331.9
25°	1327.6	1315.7	1290.6	1293.4	1290.6
27.5°	1283.0	1272.7	1253.5	1249.1	1241.7
30°	1238.7	1226.8	1204.6	1200.2	1194.3
32.5°	1191.2	1182.5	1158.7	1149.7	1143.8
35°	1145.3	1130.6	1106.8	1097.9	1090.5
37.5°	1093.4	1080.1	1056.4	1046.0	1038.6
40°	1040.2	1028.3	1004.5	991.3	985.3
42.5°	988.3	976.4	952.8	937.8	929.0
45°	932.0	921.7	899.3	883.2	877.1
47.5°	877.1	866.8	843.1	826.7	817.9
50°	819.3	812.0	791.2	770.5	763.0
52.5°	763.0	752.6	733.5	717.2	706.8
55°	705.4	696.4	678.6	660.8	653.5
57.5°	647.5	640.1	620.8	603.0	597.0
60°	589.6	583.9	563.1	546.7	542.4
62.5°	533.4	523.0	508.2	493.4	487.5
65°	475.7	466.7	451.9	438.6	431.2
67.5°	416.4	408.9	395.7	385.3	379.3
70°	361.5	355.6	342.2	331.8	326.1
72.5°	305.3	299.3	291.9	281.6	277.1
75°	248.8	246.0	238.5	229.7	232.7
77.5°	198.6	192.5	189.6	185.2	180.8
80°	148.3	146.7	143.7	139.3	136.3
82.5°	100.7	100.7	99.3	93.4	93.4
85°	60.7	59.2	57.8	53.3	51.9
87.5°	26.7	23.8	20.8	16.3	14.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929975

CATALOG NUMBER: DFN2DS-4P4F0-050DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.28	12.89	11.65	13.21	13.52	10.84	12.45	11.20	12.76	13.08
	3H	13.03	14.49	13.41	14.81	15.17	12.54	13.99	12.92	14.32	14.68
	4H	13.68	15.05	14.08	15.39	15.77	13.18	14.55	13.58	14.90	15.28
	6H	14.15	15.42	14.56	15.78	16.17	13.65	14.91	14.06	15.28	15.67
	8H	14.29	15.50	14.71	15.89	16.29	13.79	15.00	14.21	15.39	15.79
	12H	14.38	15.54	14.81	15.92	16.35	13.87	15.03	14.30	15.41	15.84
4H	2H	11.84	13.21	12.24	13.56	13.93	11.49	12.86	11.89	13.21	13.58
	3H	13.82	14.96	14.23	15.36	15.76	13.41	14.56	13.82	14.95	15.35
	4H	14.59	15.63	15.02	16.04	16.48	14.17	15.21	14.60	15.62	16.06
	6H	15.19	16.09	15.64	16.54	16.99	14.76	15.66	15.21	16.10	16.56
	8H	15.38	16.23	15.84	16.67	17.13	14.94	15.79	15.40	16.23	16.70
	12H	15.51	16.27	15.99	16.75	17.22	15.06	15.82	15.54	16.30	16.76
8H	4H	14.87	15.71	15.33	16.16	16.62	14.49	15.34	14.95	15.78	16.25
	6H	15.58	16.28	16.07	16.77	17.25	15.20	15.90	15.69	16.39	16.87
	8H	15.84	16.47	16.35	16.98	17.46	15.45	16.08	15.96	16.59	17.07
	12H	16.04	16.60	16.55	17.09	17.65	15.63	16.19	16.13	16.68	17.24
12H	4H	14.89	15.65	15.37	16.13	16.60	14.53	15.29	15.01	15.76	16.23
	6H	15.63	16.26	16.14	16.76	17.25	15.26	15.89	15.77	16.40	16.88
	8H	15.94	16.50	16.45	16.99	17.55	15.56	16.12	16.07	16.61	17.17