

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001027

Luminaire Tested: S124RDR-B1020DB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001027
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-26)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDR-B1020DB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Regressed Direct Recessed with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4147.0 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 46.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001027

CATALOG NUMBER: S124RDR-B1020DB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001027

CATALOG NUMBER: S124RDR-B1020DB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	87	87	85
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	74	74	74	72
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	64	64	62
4	84	73	65	58	82	72	64	58	69	62	57	67	61	56	65	60	56	56	56	54
5	78	66	57	51	76	65	56	50	62	55	50	61	54	49	59	53	49	49	49	47
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	43	43	41
7	67	54	46	40	65	53	45	40	52	45	39	50	44	39	49	43	39	39	39	37
8	63	50	41	36	61	49	41	36	48	40	35	46	40	35	45	39	35	35	35	33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	32	32	30
10	55	42	35	29	54	42	34	29	41	34	29	40	33	29	39	33	29	29	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14636	14636	14636
5°	14669	14489	14579
10°	14577	14315	14315
15°	14409	14015	13910
20°	14180	13619	13368
25°	13886	13156	12822
30°	13600	12668	12137
35°	13284	12162	11450
40°	12903	11586	10708
45°	12552	11014	9952
50°	12152	10356	9153
55°	11722	9672	8284
60°	11252	8921	7396
65°	10819	7980	6524
70°	10190	6945	5536
75°	9395	5759	4502
80°	8194	4386	4132
85°	6942	3986	3733

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12552 cd/sqm

TEST NUMBER: P1001027

CATALOG NUMBER: S124RDR-B1020DB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.8	4.1
10°-20°	470.6	11.3
20°-30°	679.4	16.4
30°-40°	769.9	18.6
40°-50°	743.4	17.9
50°-60°	618.1	14.9
60°-70°	426.6	10.3
70°-80°	215.6	5.2
80°-90°	54.7	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1318.7	31.8
0°-40°	2088.6	50.4
0°-60°	3450.1	83.2
0°-90°	4147.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4147.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1795	1795	1795	1795	1795	
5°	1792	1786	1770	1784	1781	170
15°	1707	1694	1660	1657	1648	481
25°	1543	1518	1462	1439	1425	711
35°	1334	1290	1222	1175	1150	834
45°	1088	1038	955	888	863	839
55°	824	770	680	609	583	738
65°	561	502	414	355	338	554
75°	298	247	183	151	143	315
85°	74	47	43	40	40	86
90°	0	0	0	0	0	

TEST NUMBER: P1001027

CATALOG NUMBER: S124RDR-B1020DB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1794.8	1794.8	1794.8	1794.8	1794.8
2.5°	1800.3	1794.8	1779.7	1794.8	1793.4
5°	1792.0	1786.5	1770.0	1783.8	1781.0
7.5°	1779.7	1774.2	1753.5	1763.2	1759.0
10°	1760.4	1753.5	1728.8	1734.3	1728.8
12.5°	1735.7	1727.4	1697.2	1699.9	1691.7
15°	1706.8	1694.4	1660.1	1657.3	1647.7
17.5°	1673.8	1656.0	1616.1	1609.2	1595.5
20°	1634.0	1616.1	1569.4	1558.4	1540.5
22.5°	1590.0	1569.4	1518.5	1500.7	1486.9
25°	1543.3	1518.5	1462.2	1438.8	1425.1
27.5°	1495.2	1464.9	1405.9	1378.4	1359.1
30°	1444.3	1410.0	1345.4	1311.0	1289.0
32.5°	1390.7	1350.9	1283.5	1242.3	1221.7
35°	1334.4	1290.4	1221.7	1175.0	1150.2
37.5°	1275.3	1230.0	1154.4	1103.5	1078.8
40°	1212.1	1166.7	1088.4	1030.7	1005.9
42.5°	1151.6	1103.5	1021.1	962.0	935.9
45°	1088.4	1037.6	955.1	887.8	863.0
47.5°	1023.8	971.6	886.4	816.3	788.8
50°	957.9	904.3	816.3	747.6	721.5
52.5°	890.5	838.3	747.6	677.5	650.0
55°	824.5	769.6	680.3	608.8	582.7
57.5°	760.0	702.2	614.3	541.5	522.2
60°	689.9	634.9	547.0	475.5	453.5
62.5°	626.7	568.9	478.2	413.6	397.2
65°	560.7	501.6	413.6	354.6	338.1
67.5°	492.0	435.6	353.2	301.0	281.7
70°	427.4	369.7	291.3	246.0	232.2
72.5°	358.7	307.8	235.0	197.9	185.5
75°	298.2	247.4	182.8	151.2	142.9
77.5°	235.0	191.0	136.1	114.1	111.3
80°	174.5	134.7	93.4	89.3	88.0
82.5°	122.3	86.6	67.3	64.6	63.2
85°	74.2	46.7	42.6	39.9	39.9
87.5°	31.6	20.6	19.2	17.9	19.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)