

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929960

Luminaire Tested: DFN2DS-4P4F0-040DS930-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929960
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-040DS930-RLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2771.0 lumens
Efficiency: N/A
Efficacy: 70.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 39.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929960

CATALOG NUMBER: DFN2DS-4P4F0-040DS930-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P929960

CATALOG NUMBER: DFN2DS-4P4F0-040DS930-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	874	874	874
5°	877	863	868
10°	871	849	842
15°	861	824	800
20°	847	788	748
25°	833	747	698
30°	813	705	634
35°	794	660	577
40°	774	612	512
45°	752	559	453
50°	728	506	395
55°	705	448	339
60°	677	388	282
65°	646	326	256
70°	608	268	236
75°	562	245	220
80°	496	218	201
85°	390	172	172

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 752 cd/sqm

TEST NUMBER: P929960

CATALOG NUMBER: DFN2DS-4P4F0-040DS930-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	4.6
10°-20°	346.7	12.5
20°-30°	486.7	17.6
30°-40°	530.5	19.1
40°-50°	487.6	17.6
50°-60°	382.9	13.8
60°-70°	249.3	9.0
70°-80°	128.3	4.6
80°-90°	32.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	959.6	34.6
0°-40°	1490.1	53.8
0°-60°	2360.7	85.2
0°-90°	2771.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2771.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1347	1347	1347	1347	1347	
5°	1347	1341	1325	1336	1333	128
15°	1282	1268	1227	1204	1191	361
25°	1163	1124	1044	994	975	535
35°	1002	940	833	756	729	627
45°	819	738	610	523	494	633
55°	623	528	396	323	300	557
65°	421	322	212	171	167	417
75°	224	139	98	89	88	237
85°	52	27	23	23	23	63
90°	0	0	0	0	0	

TEST NUMBER: P929960

CATALOG NUMBER: DFN2DS-4P4F0-040DS930-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.4	1347.4	1347.4	1347.4	1347.4
2.5°	1353.5	1347.4	1333.9	1346.2	1343.7
5°	1347.4	1341.2	1325.4	1336.4	1332.8
7.5°	1336.4	1329.1	1312.1	1316.8	1310.8
10°	1321.8	1313.2	1288.8	1285.1	1277.9
12.5°	1303.5	1292.5	1259.5	1252.2	1238.8
15°	1281.5	1268.1	1226.7	1203.5	1191.4
17.5°	1255.9	1236.4	1185.1	1158.4	1138.8
20°	1226.7	1202.2	1141.2	1110.8	1083.9
22.5°	1195.0	1166.9	1096.1	1054.7	1036.5
25°	1163.2	1124.2	1043.7	993.8	975.4
27.5°	1125.5	1083.9	995.0	937.7	909.5
30°	1085.3	1038.8	941.2	879.1	846.2
32.5°	1046.2	990.1	890.1	817.0	786.4
35°	1002.4	940.1	832.8	756.0	729.1
37.5°	959.7	892.5	779.1	695.0	664.6
40°	914.5	841.4	723.1	636.5	604.8
42.5°	868.1	790.1	667.0	576.7	546.3
45°	819.4	737.7	609.7	523.1	493.8
47.5°	773.1	686.6	554.9	468.2	441.4
50°	721.8	635.3	501.1	417.0	391.4
52.5°	671.8	580.4	450.0	369.4	346.3
55°	623.1	528.0	396.3	323.1	300.0
57.5°	573.1	475.6	348.7	280.4	261.0
60°	521.8	424.3	298.7	236.6	217.1
62.5°	472.0	374.4	256.0	197.6	187.9
65°	420.7	321.8	212.1	170.7	167.0
67.5°	372.0	273.1	170.7	150.0	146.3
70°	320.7	225.6	141.4	129.3	124.3
72.5°	272.0	181.7	118.3	108.6	106.1
75°	224.3	139.0	97.6	89.0	87.9
77.5°	176.9	98.7	76.9	72.0	69.4
80°	132.8	70.7	58.4	53.7	53.7
82.5°	92.7	47.6	40.3	37.7	37.7
85°	52.4	26.8	23.1	23.1	23.1
87.5°	19.6	9.7	9.7	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929960

CATALOG NUMBER: DFN2DS-4P4F0-040DS930-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.77	12.29	11.13	12.60	12.92	6.73	8.25	7.09	8.56	8.88
	3H	12.53	13.90	12.91	14.23	14.59	7.99	9.36	8.37	9.69	10.05
	4H	13.20	14.48	13.60	14.83	15.21	8.49	9.78	8.89	10.12	10.50
	6H	13.69	14.87	14.10	15.24	15.63	8.88	10.06	9.29	10.42	10.82
	8H	13.85	14.98	14.28	15.37	15.77	9.00	10.13	9.43	10.52	10.92
	12H	13.96	15.04	14.39	15.42	15.85	9.08	10.16	9.51	10.54	10.97
4H	2H	10.87	12.15	11.27	12.50	12.88	7.42	8.70	7.82	9.05	9.43
	3H	12.80	13.87	13.22	14.27	14.67	8.87	9.93	9.28	10.33	10.73
	4H	13.55	14.51	13.99	14.93	15.37	9.47	10.42	9.90	10.84	11.28
	6H	14.15	14.98	14.60	15.42	15.88	9.95	10.79	10.41	11.23	11.69
	8H	14.36	15.14	14.82	15.58	16.05	10.12	10.89	10.58	11.34	11.80
	12H	14.51	15.21	15.00	15.69	16.16	10.23	10.93	10.71	11.40	11.88
8H	4H	13.58	14.36	14.04	14.80	15.27	9.82	10.60	10.28	11.04	11.51
	6H	14.22	14.86	14.71	15.35	15.83	10.41	11.05	10.90	11.54	12.02
	8H	14.47	15.04	14.98	15.55	16.04	10.63	11.20	11.14	11.71	12.20
	12H	14.67	15.18	15.18	15.67	16.24	10.81	11.32	11.31	11.81	12.37
12H	4H	13.56	14.26	14.05	14.74	15.21	9.86	10.56	10.35	11.04	11.51
	6H	14.20	14.77	14.71	15.28	15.77	10.47	11.05	10.98	11.56	12.05
	8H	14.48	14.99	14.99	15.48	16.05	10.74	11.25	11.25	11.74	12.31