

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930035

Luminaire Tested: DFN2DS-4P4F0-080DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930035
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-080DS940-FLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7064.6 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 86.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930035

CATALOG NUMBER: DFN2DS-4P4F0-080DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930035

CATALOG NUMBER: DFN2DS-4P4F0-080DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1801	1801	1801
5°	1808	1782	1793
10°	1798	1764	1773
15°	1775	1741	1740
20°	1744	1707	1705
25°	1712	1665	1665
30°	1672	1626	1612
35°	1635	1580	1556
40°	1587	1533	1504
45°	1541	1487	1450
50°	1490	1439	1388
55°	1438	1383	1332
60°	1379	1316	1268
65°	1316	1250	1193
70°	1236	1170	1114
75°	1124	1077	1051
80°	998	967	918
85°	814	776	696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1541 cd/sqm

TEST NUMBER: P930035

CATALOG NUMBER: DFN2DS-4P4F0-080DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.3	3.7
10°-20°	735.3	10.4
20°-30°	1080.6	15.3
30°-40°	1255.1	17.8
40°-50°	1253.5	17.7
50°-60°	1093.0	15.5
60°-70°	808.0	11.4
70°-80°	457.1	6.5
80°-90°	120.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2077.3	29.4
0°-40°	3332.3	47.2
0°-60°	5678.8	80.4
0°-90°	7064.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7064.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2777	2777	2777	2777	2777	
5°	2777	2766	2737	2758	2753	264
15°	2643	2627	2592	2603	2590	744
25°	2392	2371	2326	2331	2326	1101
35°	2064	2037	1994	1978	1965	1289
45°	1680	1661	1621	1591	1581	1296
55°	1271	1255	1223	1191	1178	1136
65°	857	841	814	790	777	847
75°	448	443	430	414	419	479
85°	109	107	104	96	94	129
90°	0	0	0	0	0	

TEST NUMBER: P930035

CATALOG NUMBER: DFN2DS-4P4F0-080DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2776.6	2776.6	2776.6	2776.6	2776.6
2.5°	2792.8	2779.5	2750.0	2776.6	2771.5
5°	2776.6	2766.2	2736.7	2758.0	2752.9
7.5°	2758.0	2742.1	2712.7	2734.2	2728.8
10°	2728.8	2710.1	2678.1	2699.3	2691.4
12.5°	2688.6	2672.7	2640.7	2654.0	2648.6
15°	2643.3	2627.4	2592.5	2603.3	2590.0
17.5°	2587.2	2571.3	2536.4	2549.8	2536.4
20°	2525.7	2509.8	2472.4	2480.4	2469.9
22.5°	2464.5	2440.4	2405.5	2405.5	2400.2
25°	2392.3	2371.0	2325.7	2330.8	2325.7
27.5°	2312.1	2293.4	2258.8	2250.9	2237.6
30°	2232.2	2210.6	2170.8	2162.8	2152.0
32.5°	2146.7	2130.8	2088.0	2071.8	2061.1
35°	2063.9	2037.3	1994.5	1978.4	1965.1
37.5°	1970.4	1946.3	1903.6	1884.9	1871.6
40°	1874.4	1852.9	1810.1	1786.3	1775.5
42.5°	1781.0	1759.4	1716.9	1690.0	1674.2
45°	1679.5	1660.8	1620.6	1591.4	1580.7
47.5°	1580.7	1562.0	1519.2	1489.7	1473.9
50°	1476.4	1463.1	1425.7	1388.3	1375.0
52.5°	1375.0	1356.3	1321.8	1292.3	1273.6
55°	1271.0	1254.9	1222.9	1190.9	1177.5
57.5°	1166.8	1153.5	1118.7	1086.6	1075.8
60°	1062.6	1052.1	1014.6	985.2	977.3
62.5°	961.1	942.5	915.8	889.2	878.4
65°	857.2	841.1	814.4	790.3	777.0
67.5°	750.4	736.8	713.0	694.3	683.5
70°	651.5	640.7	616.7	598.0	587.5
72.5°	550.1	539.4	526.0	507.4	499.4
75°	448.4	443.3	429.8	413.9	419.2
77.5°	357.8	347.0	341.6	333.7	325.8
80°	267.2	264.3	258.9	251.0	245.6
82.5°	181.6	181.6	179.0	168.2	168.2
85°	109.4	106.8	104.3	96.1	93.5
87.5°	48.2	42.8	37.4	29.4	26.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930035

CATALOG NUMBER: DFN2DS-4P4F0-080DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.33	14.94	13.69	15.25	15.57	12.88	14.49	13.25	14.81	15.12
	3H	15.08	16.53	15.45	16.86	17.22	14.59	16.04	14.96	16.37	16.73
	4H	15.72	17.09	16.12	17.44	17.82	15.23	16.60	15.63	16.95	17.32
	6H	16.19	17.46	16.60	17.83	18.22	15.69	16.96	16.10	17.32	17.72
	8H	16.34	17.55	16.76	17.94	18.33	15.83	17.04	16.26	17.43	17.83
	12H	16.43	17.59	16.86	17.97	18.40	15.91	17.07	16.34	17.46	17.88
4H	2H	13.89	15.26	14.29	15.60	15.98	13.53	14.90	13.93	15.25	15.63
	3H	15.86	17.01	16.27	17.41	17.81	15.46	16.60	15.87	17.00	17.40
	4H	16.64	17.68	17.07	18.09	18.52	16.22	17.25	16.65	17.66	18.10
	6H	17.24	18.14	17.69	18.58	19.04	16.80	17.71	17.26	18.15	18.61
	8H	17.43	18.27	17.89	18.71	19.18	16.99	17.83	17.45	18.28	18.74
	12H	17.56	18.32	18.04	18.79	19.26	17.10	17.86	17.59	18.34	18.81
8H	4H	16.91	17.76	17.37	18.20	18.67	16.54	17.38	17.00	17.83	18.29
	6H	17.63	18.33	18.12	18.82	19.29	17.25	17.95	17.74	18.44	18.91
	8H	17.89	18.52	18.40	19.02	19.51	17.49	18.13	18.00	18.63	19.12
	12H	18.09	18.64	18.59	19.13	19.70	17.67	18.23	18.18	18.72	19.28
12H	4H	16.94	17.70	17.42	18.17	18.64	16.57	17.33	17.05	17.81	18.28
	6H	17.67	18.30	18.18	18.81	19.30	17.30	17.94	17.81	18.44	18.93
	8H	17.99	18.54	18.49	19.03	19.60	17.61	18.17	18.12	18.66	19.22