

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1004563

Luminaire Tested: S125DR-B1270DB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1004563
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-12)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DR-B1270DB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct Recessed with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5141.0 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1004563

CATALOG NUMBER: S125DR-B1270DB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1004563

CATALOG NUMBER: S125DR-B1270DB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92	94	91	89	90	88	86	86	86	84
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	72	72	70
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	62	62	59
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	53	53	51
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	57	51	46	46	46	44
6	71	57	49	42	69	56	48	42	55	47	42	53	46	41	51	46	41	41	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	36	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	33	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30	30	30	28
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	27	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12655	12655	12655
5°	12684	12563	12643
10°	12607	12474	12545
15°	12470	12324	12376
20°	12274	12115	12136
25°	12063	11865	11853
30°	11804	11596	11538
35°	11526	11306	11147
40°	11240	10992	10835
45°	10931	10705	10492
50°	10592	10358	10046
55°	10265	9967	9688
60°	9872	9572	9231
65°	9406	9098	8790
70°	8958	8548	8256
75°	8162	7892	7620
80°	7265	7151	6977
85°	6315	6432	6087

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10931 cd/sqm

TEST NUMBER: P1004563

CATALOG NUMBER: S125DR-B1270DB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	3.6
10°-20°	526.5	10.2
20°-30°	777.2	15.1
30°-40°	906.8	17.6
40°-50°	910.8	17.7
50°-60°	799.5	15.6
60°-70°	595.5	11.6
70°-80°	340.1	6.6
80°-90°	98.2	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1490.1	29.0
0°-40°	2396.9	46.6
0°-60°	4107.2	79.9
0°-90°	5141.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5141.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1975	1975	1975	1975	1975	
5°	1972	1969	1953	1967	1966	187
15°	1880	1875	1858	1866	1866	530
25°	1706	1699	1678	1681	1677	785
35°	1474	1467	1446	1438	1425	922
45°	1206	1200	1181	1163	1158	929
55°	919	914	892	878	867	820
65°	620	617	600	586	580	615
75°	330	327	319	314	308	351
85°	86	88	88	86	83	100
90°	0	0	0	0	0	

TEST NUMBER: P1004563

CATALOG NUMBER: S125DR-B1270DB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1975.2	1975.2	1975.2	1975.2	1975.2
2.5°	1981.5	1976.8	1961.2	1976.8	1975.2
5°	1972.1	1969.0	1953.3	1967.4	1965.8
7.5°	1958.0	1954.9	1937.7	1951.8	1950.2
10°	1937.7	1934.6	1917.4	1929.9	1928.3
12.5°	1912.7	1906.5	1890.8	1900.2	1900.2
15°	1879.9	1875.2	1858.0	1865.8	1865.8
17.5°	1845.5	1837.7	1820.5	1829.9	1822.1
20°	1800.2	1797.1	1776.8	1787.7	1779.9
22.5°	1754.9	1748.6	1729.9	1736.1	1731.4
25°	1706.4	1698.6	1678.3	1681.4	1676.7
27.5°	1650.2	1645.5	1625.2	1626.7	1622.1
30°	1595.5	1590.8	1567.4	1564.2	1559.5
32.5°	1536.1	1528.3	1508.0	1501.7	1492.4
35°	1473.6	1467.3	1445.5	1437.7	1425.2
37.5°	1409.5	1401.7	1381.4	1370.5	1362.6
40°	1343.9	1336.1	1314.2	1300.1	1295.5
42.5°	1273.6	1267.3	1245.4	1232.9	1225.1
45°	1206.4	1200.1	1181.4	1162.6	1157.9
47.5°	1132.9	1134.5	1111.1	1092.3	1081.4
50°	1062.6	1057.9	1039.2	1018.9	1007.9
52.5°	990.7	987.6	967.3	950.1	937.6
55°	918.9	914.2	892.3	878.2	867.3
57.5°	842.3	840.7	822.0	803.2	798.5
60°	770.4	764.1	747.0	731.3	720.4
62.5°	695.4	690.7	676.6	659.4	651.6
65°	620.4	617.3	600.1	586.0	579.8
67.5°	546.9	540.7	528.2	515.7	512.6
70°	478.2	470.4	456.3	446.9	440.7
72.5°	403.2	398.5	390.7	379.7	373.5
75°	329.7	326.6	318.8	314.1	307.8
77.5°	261.0	259.4	254.7	251.6	246.9
80°	196.9	196.9	193.8	192.2	189.1
82.5°	140.6	137.5	137.5	134.4	134.4
85°	85.9	87.5	87.5	85.9	82.8
87.5°	42.2	42.2	40.6	40.6	37.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)