

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929966

Luminaire Tested: DFN2DS-4P4F0-040DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929966
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-040DS950-RLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3213.0 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 39.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929966

CATALOG NUMBER: DFN2DS-4P4F0-040DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P929966

CATALOG NUMBER: DFN2DS-4P4F0-040DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1014	1014	1014
5°	1017	1001	1006
10°	1010	984	976
15°	998	955	928
20°	982	914	868
25°	965	866	810
30°	943	818	735
35°	921	765	670
40°	898	710	594
45°	872	649	525
50°	845	586	458
55°	817	520	393
60°	785	449	327
65°	749	378	297
70°	705	311	273
75°	652	283	255
80°	575	253	233
85°	453	199	199

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 872 cd/sqm

TEST NUMBER: P929966

CATALOG NUMBER: DFN2DS-4P4F0-040DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.4	4.6
10°-20°	401.9	12.5
20°-30°	564.3	17.6
30°-40°	615.1	19.1
40°-50°	565.4	17.6
50°-60°	444.0	13.8
60°-70°	289.0	9.0
70°-80°	148.8	4.6
80°-90°	38.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1112.7	34.6
0°-40°	1727.8	53.8
0°-60°	2737.2	85.2
0°-90°	3213.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3213.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1562	1562	1562	1562	1562	
5°	1562	1555	1537	1550	1545	148
15°	1486	1470	1422	1396	1381	419
25°	1349	1304	1210	1152	1131	620
35°	1162	1090	966	877	845	727
45°	950	855	707	606	573	734
55°	722	612	460	375	348	646
65°	488	373	246	198	194	484
75°	260	161	113	103	102	275
85°	61	31	27	27	27	73
90°	0	0	0	0	0	

TEST NUMBER: P929966

CATALOG NUMBER: DFN2DS-4P4F0-040DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1562.3	1562.3	1562.3	1562.3	1562.3
2.5°	1569.4	1562.3	1546.7	1561.0	1558.0
5°	1562.3	1555.2	1536.8	1549.5	1545.4
7.5°	1549.5	1541.1	1521.4	1526.8	1519.8
10°	1532.6	1522.7	1494.4	1490.1	1481.8
12.5°	1511.4	1498.7	1460.4	1452.0	1436.4
15°	1485.9	1470.3	1422.3	1395.5	1381.4
17.5°	1456.2	1433.6	1374.1	1343.1	1320.4
20°	1422.3	1394.0	1323.3	1288.0	1256.8
22.5°	1385.6	1353.1	1270.9	1222.9	1201.9
25°	1348.8	1303.5	1210.2	1152.3	1131.0
27.5°	1305.0	1256.8	1153.7	1087.2	1054.6
30°	1258.4	1204.5	1091.4	1019.4	981.2
32.5°	1213.1	1148.0	1032.1	947.3	911.8
35°	1162.3	1090.1	965.7	876.6	845.4
37.5°	1112.7	1034.9	903.4	805.8	770.6
40°	1060.4	975.6	838.4	738.0	701.3
42.5°	1006.6	916.2	773.4	668.7	633.4
45°	950.1	855.3	707.0	606.5	572.6
47.5°	896.4	796.1	643.4	542.9	511.8
50°	837.0	736.6	581.1	483.5	453.9
52.5°	779.0	672.9	521.7	428.4	401.5
55°	722.5	612.2	459.5	374.7	347.9
57.5°	664.5	551.4	404.4	325.2	302.6
60°	605.1	492.0	346.3	274.3	251.7
62.5°	547.2	434.1	296.8	229.1	217.8
65°	487.8	373.2	246.0	198.0	193.6
67.5°	431.3	316.7	198.0	173.9	169.6
70°	371.9	261.6	164.0	149.9	144.1
72.5°	315.3	210.6	137.1	125.9	123.0
75°	260.1	161.1	113.1	103.2	101.9
77.5°	205.1	114.4	89.1	83.4	80.5
80°	154.0	82.0	67.8	62.3	62.3
82.5°	107.4	55.2	46.7	43.8	43.8
85°	60.8	31.1	26.8	26.8	26.8
87.5°	22.7	11.2	11.2	9.9	9.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929966

CATALOG NUMBER: DFN2DS-4P4F0-040DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.28	12.80	11.65	13.12	13.43	7.24	8.76	7.61	9.08	9.39
	3H	13.05	14.41	13.42	14.74	15.10	8.51	9.87	8.88	10.20	10.56
	4H	13.71	14.99	14.11	15.34	15.72	9.01	10.29	9.41	10.64	11.02
	6H	14.20	15.38	14.61	15.75	16.14	9.39	10.57	9.80	10.94	11.33
	8H	14.37	15.49	14.79	15.88	16.28	9.51	10.64	9.94	11.03	11.43
	12H	14.47	15.55	14.90	15.93	16.36	9.60	10.67	10.03	11.06	11.48
4H	2H	11.39	12.67	11.78	13.01	13.39	7.94	9.22	8.34	9.57	9.95
	3H	13.32	14.38	13.73	14.78	15.18	9.38	10.44	9.79	10.84	11.24
	4H	14.07	15.02	14.50	15.44	15.88	9.98	10.94	10.41	11.35	11.79
	6H	14.66	15.49	15.12	15.93	16.39	10.47	11.30	10.93	11.74	12.20
	8H	14.87	15.65	15.34	16.10	16.56	10.63	11.41	11.09	11.85	12.32
	12H	15.03	15.72	15.51	16.20	16.67	10.75	11.44	11.23	11.92	12.39
8H	4H	14.09	14.87	14.56	15.31	15.78	10.33	11.11	10.80	11.56	12.02
	6H	14.73	15.37	15.23	15.86	16.34	10.92	11.56	11.42	12.05	12.53
	8H	14.98	15.56	15.49	16.07	16.55	11.14	11.72	11.66	12.23	12.72
	12H	15.18	15.69	15.69	16.19	16.75	11.32	11.83	11.83	12.32	12.89
12H	4H	14.08	14.77	14.56	15.25	15.72	10.38	11.07	10.86	11.55	12.02
	6H	14.71	15.29	15.22	15.80	16.29	10.98	11.56	11.50	12.07	12.56
	8H	14.99	15.50	15.50	16.00	16.56	11.26	11.77	11.77	12.26	12.82