

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930020

Luminaire Tested: DFN2DS-4P4F0-070DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930020
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-070DS950-RLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5622.7 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 74.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930020

CATALOG NUMBER: DFN2DS-4P4F0-070DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930020

CATALOG NUMBER: DFN2DS-4P4F0-070DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1774	1774	1774
5°	1780	1751	1761
10°	1767	1723	1708
15°	1746	1672	1624
20°	1718	1599	1518
25°	1690	1516	1417
30°	1650	1431	1286
35°	1611	1338	1172
40°	1571	1242	1039
45°	1525	1135	919
50°	1478	1026	802
55°	1430	909	689
60°	1374	786	572
65°	1310	661	520
70°	1234	544	478
75°	1141	496	447
80°	1007	443	407
85°	791	350	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1525 cd/sqm

TEST NUMBER: P930020

CATALOG NUMBER: DFN2DS-4P4F0-070DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.2	4.6
10°-20°	703.4	12.5
20°-30°	987.6	17.6
30°-40°	1076.5	19.1
40°-50°	989.4	17.6
50°-60°	777.0	13.8
60°-70°	505.8	9.0
70°-80°	260.3	4.6
80°-90°	66.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1947.2	34.6
0°-40°	3023.7	53.8
0°-60°	4790.2	85.2
0°-90°	5622.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5622.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2734	2734	2734	2734	2734	
5°	2734	2722	2689	2712	2704	259
15°	2600	2573	2489	2442	2417	733
25°	2360	2281	2118	2016	1979	1086
35°	2034	1908	1690	1534	1480	1273
45°	1663	1497	1237	1061	1002	1284
55°	1264	1071	804	656	609	1130
65°	854	653	430	346	339	846
75°	455	282	198	181	178	481
85°	106	54	47	47	47	127
90°	0	0	0	0	0	

TEST NUMBER: P930020

CATALOG NUMBER: DFN2DS-4P4F0-070DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2734.0	2734.0	2734.0	2734.0	2734.0
2.5°	2746.3	2734.0	2706.7	2731.6	2726.6
5°	2734.0	2721.6	2689.4	2711.7	2704.3
7.5°	2711.7	2696.9	2662.3	2672.0	2659.7
10°	2682.0	2664.7	2615.3	2607.7	2593.0
12.5°	2645.0	2622.7	2555.8	2541.0	2513.7
15°	2600.4	2573.0	2489.0	2442.1	2417.4
17.5°	2548.4	2508.8	2404.8	2350.4	2310.8
20°	2489.0	2439.4	2315.8	2254.1	2199.5
22.5°	2424.8	2367.8	2224.2	2140.1	2103.2
25°	2360.4	2281.1	2117.8	2016.5	1979.3
27.5°	2283.8	2199.5	2018.9	1902.7	1845.7
30°	2202.1	2107.9	1909.9	1784.0	1717.1
32.5°	2122.8	2009.0	1806.3	1657.7	1595.7
35°	2033.8	1907.6	1690.0	1534.1	1479.5
37.5°	1947.3	1811.0	1581.1	1410.1	1348.5
40°	1855.6	1707.3	1467.1	1291.5	1227.2
42.5°	1761.7	1603.4	1353.4	1170.2	1108.6
45°	1662.7	1496.8	1237.2	1061.3	1002.0
47.5°	1568.7	1393.1	1125.9	950.0	895.7
50°	1464.8	1289.2	1016.9	846.1	794.4
52.5°	1363.2	1177.6	913.0	749.7	702.7
55°	1264.2	1071.3	804.0	655.7	608.8
57.5°	1162.9	964.9	707.7	569.1	529.5
60°	1059.0	861.0	606.1	480.2	440.5
62.5°	957.6	759.7	519.5	400.9	381.1
65°	853.6	653.1	430.5	346.5	338.9
67.5°	754.7	554.1	346.5	304.2	296.9
70°	650.7	457.8	286.9	262.2	252.2
72.5°	551.8	368.5	239.9	220.3	215.3
75°	455.2	281.9	197.9	180.6	178.2
77.5°	358.8	200.2	155.9	145.9	141.0
80°	269.6	143.5	118.7	109.0	109.0
82.5°	188.0	96.6	81.6	76.6	76.6
85°	106.3	54.3	47.0	47.0	47.0
87.5°	39.6	19.7	19.7	17.3	17.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930020

CATALOG NUMBER: DFN2DS-4P4F0-070DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.23	14.75	13.59	15.06	15.38	9.19	10.71	9.55	11.02	11.34
	3H	14.99	16.36	15.37	16.68	17.05	10.45	11.82	10.83	12.14	12.51
	4H	15.66	16.94	16.06	17.29	17.66	10.95	12.23	11.35	12.58	12.96
	6H	16.15	17.33	16.56	17.70	18.09	11.33	12.52	11.75	12.88	13.28
	8H	16.31	17.44	16.74	17.83	18.23	11.46	12.59	11.89	12.97	13.38
	12H	16.41	17.49	16.84	17.87	18.30	11.54	12.62	11.97	13.00	13.43
4H	2H	13.33	14.61	13.73	14.96	15.34	9.88	11.16	10.28	11.51	11.89
	3H	15.26	16.33	15.67	16.73	17.13	11.32	12.39	11.74	12.79	13.19
	4H	16.01	16.97	16.44	17.38	17.82	11.92	12.88	12.36	13.30	13.73
	6H	16.60	17.44	17.06	17.88	18.34	12.41	13.24	12.87	13.69	14.15
	8H	16.82	17.60	17.28	18.04	18.51	12.57	13.35	13.04	13.80	14.26
	12H	16.97	17.67	17.45	18.14	18.62	12.69	13.39	13.17	13.86	14.34
8H	4H	16.04	16.81	16.50	17.26	17.72	12.28	13.06	12.74	13.50	13.97
	6H	16.67	17.32	17.17	17.81	18.28	12.86	13.51	13.36	14.00	14.48
	8H	16.92	17.50	17.44	18.01	18.50	13.09	13.66	13.60	14.17	14.66
	12H	17.13	17.64	17.64	18.13	18.69	13.26	13.77	13.77	14.27	14.83
12H	4H	16.02	16.72	16.50	17.19	17.66	12.32	13.02	12.80	13.49	13.97
	6H	16.65	17.23	17.17	17.74	18.23	12.93	13.51	13.44	14.02	14.50
	8H	16.94	17.45	17.45	17.94	18.51	13.20	13.71	13.71	14.20	14.77