

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930040

Luminaire Tested: DFN2DS-HX2F0-020DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930040
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-020DS830-RLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1601.4 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 17.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930040

CATALOG NUMBER: DFN2DS-HX2F0-020DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930040

CATALOG NUMBER: DFN2DS-HX2F0-020DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1835	1835	1835
5°	1842	1811	1822
10°	1828	1782	1767
15°	1807	1729	1679
20°	1777	1654	1571
25°	1748	1568	1465
30°	1706	1480	1330
35°	1666	1385	1212
40°	1626	1285	1075
45°	1578	1174	951
50°	1529	1062	830
55°	1479	941	712
60°	1421	814	591
65°	1355	684	539
70°	1277	563	495
75°	1180	513	462
80°	1042	459	421
85°	816	362	362

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1578 cd/sqm

TEST NUMBER: P930040

CATALOG NUMBER: DFN2DS-HX2F0-020DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	4.6
10°-20°	200.3	12.5
20°-30°	281.3	17.6
30°-40°	306.6	19.1
40°-50°	281.8	17.6
50°-60°	221.3	13.8
60°-70°	144.1	9.0
70°-80°	74.1	4.6
80°-90°	18.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	554.6	34.6
0°-40°	861.2	53.8
0°-60°	1364.3	85.2
0°-90°	1601.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1601.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	779	779	779	779	779	
5°	779	775	766	772	770	74
15°	741	733	709	696	688	209
25°	672	650	603	574	564	309
35°	579	543	481	437	421	363
45°	474	426	352	302	285	366
55°	360	305	229	187	173	322
65°	243	186	123	99	97	241
75°	130	80	56	51	51	137
85°	30	15	13	13	13	36
90°	0	0	0	0	0	

TEST NUMBER: P930040

CATALOG NUMBER: DFN2DS-HX2F0-020DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	778.7	778.7	778.7	778.7	778.7
2.5°	782.1	778.7	770.8	778.0	776.6
5°	778.7	775.2	765.9	772.3	770.2
7.5°	772.3	768.1	758.2	761.0	757.5
10°	763.9	758.9	744.8	742.7	738.5
12.5°	753.3	746.9	727.9	723.7	715.9
15°	740.6	732.8	708.9	695.5	688.5
17.5°	725.8	714.5	684.9	669.4	658.2
20°	708.9	694.7	659.6	642.0	626.4
22.5°	690.6	674.4	633.5	609.6	599.0
25°	672.3	649.7	603.2	574.3	563.7
27.5°	650.5	626.4	575.0	541.8	525.6
30°	627.2	600.3	544.0	508.1	489.0
32.5°	604.6	572.2	514.4	472.1	454.5
35°	579.2	543.3	481.4	436.9	421.4
37.5°	554.6	515.7	450.3	401.7	384.1
40°	528.5	486.3	417.9	367.9	349.5
42.5°	501.7	456.7	385.5	333.3	315.8
45°	473.5	426.3	352.4	302.3	285.3
47.5°	446.8	396.8	320.7	270.5	255.1
50°	417.2	367.2	289.7	241.0	226.3
52.5°	388.2	335.4	260.0	213.6	200.2
55°	360.0	305.1	229.0	186.8	173.3
57.5°	331.2	274.8	201.6	162.1	150.8
60°	301.6	245.2	172.7	136.8	125.5
62.5°	272.7	216.4	148.0	114.2	108.5
65°	243.1	186.0	122.6	98.7	96.6
67.5°	215.0	157.8	98.7	86.7	84.6
70°	185.3	130.4	81.7	74.7	71.9
72.5°	157.1	104.9	68.3	62.7	61.3
75°	129.6	80.3	56.3	51.4	50.8
77.5°	102.2	57.1	44.4	41.5	40.1
80°	76.8	40.9	33.8	31.0	31.0
82.5°	53.5	27.5	23.3	21.9	21.9
85°	30.2	15.4	13.4	13.4	13.4
87.5°	11.3	5.7	5.7	4.9	4.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930040

CATALOG NUMBER: DFN2DS-HX2F0-020DS830-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.34	14.86	13.71	15.18	15.49	9.30	10.83	9.67	11.14	11.45
	3H	15.11	16.47	15.49	16.80	17.16	10.57	11.94	10.95	12.26	12.63
	4H	15.77	17.05	16.17	17.40	17.78	11.07	12.35	11.47	12.70	13.08
	6H	16.26	17.45	16.68	17.81	18.20	11.45	12.63	11.86	13.00	13.39
	8H	16.43	17.55	16.85	17.94	18.35	11.58	12.70	12.00	13.09	13.49
	12H	16.53	17.61	16.96	17.99	18.42	11.66	12.74	12.09	13.12	13.55
4H	2H	13.45	14.73	13.85	15.08	15.45	10.00	11.28	10.40	11.63	12.01
	3H	15.38	16.44	15.79	16.84	17.24	11.44	12.51	11.85	12.91	13.31
	4H	16.13	17.09	16.56	17.50	17.94	12.04	13.00	12.47	13.41	13.85
	6H	16.72	17.55	17.18	18.00	18.46	12.53	13.36	12.99	13.80	14.26
	8H	16.94	17.71	17.40	18.16	18.62	12.69	13.47	13.16	13.91	14.38
	12H	17.09	17.78	17.57	18.26	18.73	12.81	13.50	13.29	13.98	14.45
8H	4H	16.15	16.93	16.62	17.37	17.84	12.40	13.17	12.86	13.62	14.08
	6H	16.79	17.43	17.29	17.92	18.40	12.98	13.62	13.48	14.11	14.59
	8H	17.04	17.62	17.56	18.13	18.62	13.20	13.78	13.72	14.29	14.78
	12H	17.24	17.75	17.75	18.25	18.81	13.38	13.89	13.89	14.39	14.95
12H	4H	16.14	16.83	16.62	17.31	17.78	12.44	13.13	12.92	13.61	14.08
	6H	16.77	17.35	17.29	17.86	18.35	13.04	13.62	13.56	14.13	14.62
	8H	17.06	17.57	17.57	18.06	18.62	13.32	13.83	13.83	14.32	14.89