

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930057

Luminaire Tested: DFN2DS-HX2F0-030DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930057
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-030DS830-FLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2797.8 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 27.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930057

CATALOG NUMBER: DFN2DS-HX2F0-030DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930057

CATALOG NUMBER: DFN2DS-HX2F0-030DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2591	2591	2591
5°	2601	2563	2578
10°	2586	2537	2550
15°	2553	2504	2502
20°	2508	2455	2452
25°	2463	2394	2394
30°	2405	2339	2319
35°	2351	2272	2238
40°	2283	2205	2163
45°	2216	2139	2086
50°	2143	2070	1996
55°	2068	1989	1916
60°	1983	1894	1824
65°	1893	1798	1716
70°	1777	1683	1603
75°	1617	1549	1512
80°	1436	1391	1320
85°	1171	1116	1000

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2216 cd/sqm

TEST NUMBER: P930057

CATALOG NUMBER: DFN2DS-HX2F0-030DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.5	3.7
10°-20°	291.2	10.4
20°-30°	427.9	15.3
30°-40°	497.0	17.8
40°-50°	496.4	17.7
50°-60°	432.9	15.5
60°-70°	320.0	11.4
70°-80°	181.1	6.5
80°-90°	47.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	822.6	29.4
0°-40°	1319.7	47.2
0°-60°	2249.0	80.4
0°-90°	2797.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2797.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1100	1100	1100	1100	1100	
5°	1100	1096	1084	1092	1090	104
15°	1047	1040	1027	1031	1026	295
25°	947	939	921	923	921	436
35°	817	807	790	784	778	510
45°	665	658	642	630	626	513
55°	503	497	484	472	466	450
65°	340	333	322	313	308	336
75°	178	176	170	164	166	190
85°	43	42	41	38	37	51
90°	0	0	0	0	0	

TEST NUMBER: P930057

CATALOG NUMBER: DFN2DS-HX2F0-030DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1099.6	1099.6	1099.6	1099.6	1099.6
2.5°	1106.0	1100.7	1089.0	1099.6	1097.6
5°	1099.6	1095.5	1083.8	1092.2	1090.2
7.5°	1092.2	1085.9	1074.3	1082.8	1080.7
10°	1080.7	1073.2	1060.6	1069.0	1065.9
12.5°	1064.7	1058.4	1045.8	1051.0	1048.9
15°	1046.8	1040.5	1026.7	1030.9	1025.6
17.5°	1024.5	1018.3	1004.5	1009.7	1004.5
20°	1000.2	993.9	979.1	982.2	978.1
22.5°	976.0	966.5	952.6	952.6	950.5
25°	947.4	939.0	921.0	923.1	921.0
27.5°	915.6	908.2	894.5	891.4	886.1
30°	884.0	875.5	859.7	856.5	852.2
32.5°	850.2	843.8	826.9	820.5	816.2
35°	817.4	806.8	789.9	783.5	778.2
37.5°	780.4	770.8	753.9	746.4	741.2
40°	742.3	733.8	716.9	707.4	703.2
42.5°	705.3	696.8	679.9	669.3	663.0
45°	665.1	657.7	641.8	630.2	626.0
47.5°	626.0	618.6	601.7	590.0	583.7
50°	584.7	579.4	564.6	549.8	544.6
52.5°	544.6	537.1	523.5	511.8	504.3
55°	503.4	497.0	484.3	471.7	466.4
57.5°	462.1	456.8	443.0	430.3	426.1
60°	420.8	416.6	401.9	390.2	387.1
62.5°	380.7	373.2	362.7	352.1	347.9
65°	339.5	333.1	322.5	313.0	307.8
67.5°	297.2	291.8	282.3	275.0	270.7
70°	258.0	253.8	244.3	236.8	232.7
72.5°	217.9	213.6	208.3	200.9	197.8
75°	177.6	175.6	170.2	163.9	166.1
77.5°	141.7	137.4	135.3	132.2	129.1
80°	105.8	104.7	102.5	99.4	97.3
82.5°	71.9	71.9	70.9	66.6	66.6
85°	43.3	42.3	41.3	38.1	37.0
87.5°	19.0	17.0	14.8	11.7	10.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930057

CATALOG NUMBER: DFN2DS-HX2F0-030DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.59	16.20	14.95	16.51	16.83	14.15	15.76	14.51	16.07	16.38
	3H	16.34	17.79	16.72	18.12	18.48	15.85	17.30	16.23	17.63	17.99
	4H	16.99	18.36	17.39	18.70	19.08	16.49	17.86	16.89	18.21	18.58
	6H	17.46	18.72	17.87	19.09	19.48	16.95	18.22	17.37	18.59	18.98
	8H	17.60	18.81	18.02	19.20	19.60	17.10	18.31	17.52	18.70	19.10
	12H	17.69	18.85	18.12	19.23	19.66	17.18	18.34	17.61	18.72	19.15
4H	2H	15.15	16.52	15.55	16.87	17.24	14.80	16.17	15.20	16.51	16.89
	3H	17.13	18.27	17.54	18.67	19.07	16.72	17.87	17.13	18.26	18.66
	4H	17.90	18.94	18.33	19.35	19.79	17.48	18.51	17.91	18.93	19.36
	6H	18.50	19.40	18.95	19.84	20.30	18.07	18.97	18.52	19.41	19.87
	8H	18.69	19.53	19.15	19.98	20.44	18.25	19.10	18.71	19.54	20.00
	12H	18.82	19.58	19.30	20.06	20.53	18.37	19.13	18.85	19.60	20.07
8H	4H	18.18	19.02	18.64	19.46	19.93	17.80	18.65	18.26	19.09	19.56
	6H	18.89	19.59	19.38	20.08	20.56	18.51	19.21	19.00	19.70	20.18
	8H	19.15	19.78	19.66	20.29	20.77	18.76	19.39	19.27	19.90	20.38
	12H	19.35	19.91	19.86	20.40	20.96	18.94	19.49	19.44	19.98	20.55
12H	4H	18.20	18.96	18.68	19.44	19.91	17.84	18.60	18.32	19.07	19.54
	6H	18.94	19.57	19.44	20.07	20.56	18.57	19.20	19.08	19.71	20.19
	8H	19.25	19.81	19.76	20.30	20.86	18.87	19.43	19.38	19.92	20.48