

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007186

Luminaire Tested: S125RDR-B610DB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007186
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-27)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDR-B610DB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Regressed Direct Recessed with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2347.0 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 24
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007186

CATALOG NUMBER: S125RDR-B610DB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007186

CATALOG NUMBER: S125RDR-B610DB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	87	87	85
2	100	92	86	80	98	90	84	79	87	82	78	84	79	76	81	77	74	74	74	72
3	92	82	74	68	89	80	73	67	77	71	66	74	69	65	72	67	64	64	64	61
4	84	73	64	58	82	71	64	57	69	62	57	67	61	56	64	59	55	55	55	53
5	78	65	57	50	76	64	56	50	62	55	49	60	54	49	58	53	48	48	48	46
6	72	59	50	44	70	58	50	44	56	49	44	55	48	43	53	47	43	43	43	41
7	67	54	45	39	65	53	45	39	51	44	39	50	43	39	49	43	38	38	38	36
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34	34	34	33
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31	31	31	29
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29	29	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6365	6365	6365
5°	6379	6307	6345
10°	6331	6248	6248
15°	6256	6122	6071
20°	6159	5944	5873
25°	6046	5771	5644
30°	5906	5567	5390
35°	5763	5358	5105
40°	5629	5140	4826
45°	5466	4895	4521
50°	5303	4629	4203
55°	5113	4374	3864
60°	4922	4067	3500
65°	4698	3708	3082
70°	4442	3261	2656
75°	4087	2748	2211
80°	3597	2158	1856
85°	3036	1764	1654

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5466 cd/sqm

TEST NUMBER: P1007186

CATALOG NUMBER: S125RDR-B610DB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	4.0
10°-20°	261.3	11.1
20°-30°	378.8	16.1
30°-40°	431.6	18.4
40°-50°	420.7	17.9
50°-60°	354.1	15.1
60°-70°	248.1	10.6
70°-80°	127.2	5.4
80°-90°	31.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	733.6	31.3
0°-40°	1165.2	49.6
0°-60°	1940.0	82.7
0°-90°	2347.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2347.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	992	989	981	988	987	94
15°	943	939	923	922	915	266
25°	855	844	816	807	798	394
35°	737	719	685	663	653	461
45°	603	582	540	510	499	465
55°	458	434	392	358	346	409
65°	310	284	245	215	203	307
75°	165	143	111	94	89	174
85°	41	28	24	23	22	48
90°	0	0	0	0	0	

TEST NUMBER: P1007186

CATALOG NUMBER: S125RDR-B610DB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	993.4	993.4	993.4	993.4	993.4
2.5°	995.6	993.4	985.9	993.4	992.6
5°	991.9	988.9	980.6	988.1	986.6
7.5°	984.4	981.4	971.6	977.6	976.1
10°	973.1	970.9	960.4	962.6	960.4
12.5°	960.4	957.4	942.4	943.9	940.1
15°	943.1	938.6	922.9	922.1	915.3
17.5°	925.1	918.3	899.6	895.8	890.6
20°	903.3	895.8	871.8	868.1	861.3
22.5°	879.3	871.8	846.3	838.1	832.8
25°	855.3	844.1	816.3	806.6	798.3
27.5°	828.3	814.8	785.5	772.8	764.5
30°	798.3	784.0	752.5	735.3	728.5
32.5°	769.0	751.8	719.5	700.0	691.0
35°	736.8	718.8	685.0	663.3	652.7
37.5°	706.0	684.3	649.7	624.2	613.7
40°	673.0	650.5	614.5	586.0	577.0
42.5°	638.5	615.2	577.7	550.7	536.5
45°	603.2	581.5	540.2	510.2	498.9
47.5°	566.5	544.0	502.7	471.9	459.2
50°	532.0	507.2	464.4	432.9	421.7
52.5°	494.4	468.9	429.2	394.7	383.4
55°	457.7	433.7	391.6	357.9	345.9
57.5°	420.2	394.7	354.1	321.1	310.6
60°	384.1	357.9	317.4	284.4	273.1
62.5°	345.9	321.1	279.9	249.8	238.6
65°	309.9	284.4	244.6	214.6	203.3
67.5°	273.9	248.3	210.1	181.6	172.6
70°	237.1	211.6	174.1	150.8	141.8
72.5°	201.1	176.3	141.8	120.8	115.5
75°	165.1	142.6	111.0	94.5	89.3
77.5°	128.3	110.3	84.0	71.3	66.8
80°	97.5	79.5	58.5	51.8	50.3
82.5°	67.5	51.8	39.0	36.8	36.0
85°	41.3	27.8	24.0	23.3	22.5
87.5°	17.3	12.0	11.3	11.3	10.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)