

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930111

Luminaire Tested: DFN2DS-HX2F0-060DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930111
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-060DS830-FLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5595.4 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 61.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930111

CATALOG NUMBER: DFN2DS-HX2F0-060DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930111

CATALOG NUMBER: DFN2DS-HX2F0-060DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5182	5182	5182
5°	5201	5126	5157
10°	5171	5075	5100
15°	5107	5009	5004
20°	5016	4910	4905
25°	4926	4789	4789
30°	4810	4678	4637
35°	4702	4544	4477
40°	4566	4410	4325
45°	4433	4277	4171
50°	4286	4139	3992
55°	4135	3979	3831
60°	3966	3787	3647
65°	3785	3596	3431
70°	3555	3365	3205
75°	3233	3098	3023
80°	2871	2783	2639
85°	2341	2230	2000

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4433 cd/sqm

TEST NUMBER: P930111

CATALOG NUMBER: DFN2DS-HX2F0-060DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.0	3.7
10°-20°	582.4	10.4
20°-30°	855.9	15.3
30°-40°	994.1	17.8
40°-50°	992.8	17.7
50°-60°	865.7	15.5
60°-70°	639.9	11.4
70°-80°	362.1	6.5
80°-90°	95.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1645.3	29.4
0°-40°	2639.3	47.2
0°-60°	4497.9	80.4
0°-90°	5595.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5595.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2199	2199	2199	2199	2199	
5°	2199	2191	2168	2184	2180	209
15°	2094	2081	2053	2062	2051	590
25°	1895	1878	1842	1846	1842	872
35°	1635	1614	1580	1567	1556	1021
45°	1330	1315	1284	1260	1252	1027
55°	1007	994	969	943	933	900
65°	679	666	645	626	615	671
75°	355	351	340	328	332	379
85°	87	85	82	76	74	102
90°	0	0	0	0	0	

TEST NUMBER: P930111

CATALOG NUMBER: DFN2DS-HX2F0-060DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2199.2	2199.2	2199.2	2199.2	2199.2
2.5°	2212.0	2201.5	2178.1	2199.2	2195.1
5°	2199.2	2190.9	2167.5	2184.4	2180.4
7.5°	2184.4	2171.9	2148.5	2165.6	2161.3
10°	2161.3	2146.5	2121.1	2138.0	2131.7
12.5°	2129.5	2116.9	2091.5	2102.1	2097.8
15°	2093.5	2081.0	2053.4	2061.9	2051.4
17.5°	2049.1	2036.6	2009.0	2019.5	2009.0
20°	2000.4	1987.9	1958.2	1964.5	1956.3
22.5°	1952.0	1932.9	1905.3	1905.3	1901.1
25°	1894.7	1878.0	1842.0	1846.0	1842.0
27.5°	1831.2	1816.5	1789.0	1782.8	1772.3
30°	1768.0	1750.9	1719.3	1713.0	1704.5
32.5°	1700.2	1687.7	1653.8	1641.0	1632.5
35°	1634.7	1613.6	1579.7	1566.9	1556.4
37.5°	1560.7	1541.6	1507.8	1492.9	1482.3
40°	1484.6	1467.5	1433.7	1414.9	1406.3
42.5°	1410.6	1393.5	1359.9	1338.6	1326.0
45°	1330.3	1315.4	1283.6	1260.5	1251.9
47.5°	1251.9	1237.1	1203.3	1179.9	1167.3
50°	1169.4	1158.8	1129.3	1099.6	1089.0
52.5°	1089.0	1074.3	1046.8	1023.6	1008.8
55°	1006.7	993.9	968.6	943.2	932.7
57.5°	924.2	913.6	886.0	860.7	852.1
60°	841.6	833.3	803.7	780.4	774.0
62.5°	761.2	746.4	725.3	704.2	695.8
65°	678.9	666.2	645.1	626.0	615.4
67.5°	594.3	583.6	564.7	549.9	541.4
70°	516.0	507.5	488.4	473.6	465.3
72.5°	435.7	427.2	416.6	401.9	395.5
75°	355.1	351.2	340.3	327.8	332.1
77.5°	283.4	274.9	270.5	264.3	258.0
80°	211.6	209.3	205.1	198.8	194.5
82.5°	143.8	143.8	141.8	133.3	133.3
85°	86.6	84.6	82.5	76.0	74.0
87.5°	38.2	33.9	29.6	23.4	21.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930111

CATALOG NUMBER: DFN2DS-HX2F0-060DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.00	18.61	17.36	18.92	19.24	16.55	18.16	16.92	18.48	18.79
	3H	18.75	20.20	19.13	20.53	20.89	18.26	19.71	18.63	20.04	20.40
	4H	19.39	20.76	19.79	21.11	21.49	18.90	20.27	19.30	20.62	20.99
	6H	19.86	21.13	20.27	21.50	21.89	19.36	20.63	19.77	21.00	21.39
	8H	20.01	21.22	20.43	21.61	22.01	19.50	20.71	19.93	21.10	21.50
	12H	20.10	21.26	20.53	21.64	22.07	19.59	20.75	20.01	21.13	21.56
4H	2H	17.56	18.93	17.96	19.28	19.65	17.21	18.58	17.60	18.92	19.30
	3H	19.53	20.68	19.94	21.08	21.48	19.13	20.27	19.54	20.67	21.07
	4H	20.31	21.35	20.74	21.76	22.20	19.89	20.92	20.32	21.34	21.77
	6H	20.91	21.81	21.36	22.25	22.71	20.47	21.38	20.93	21.82	22.28
	8H	21.10	21.94	21.56	22.39	22.85	20.66	21.50	21.12	21.95	22.41
	12H	21.23	21.99	21.71	22.46	22.93	20.78	21.54	21.26	22.01	22.48
8H	4H	20.58	21.43	21.04	21.87	22.34	20.21	21.06	20.67	21.50	21.96
	6H	21.30	22.00	21.79	22.49	22.96	20.92	21.62	21.41	22.11	22.58
	8H	21.56	22.19	22.07	22.69	23.18	21.17	21.80	21.68	22.30	22.79
	12H	21.76	22.31	22.26	22.81	23.37	21.34	21.90	21.85	22.39	22.95
12H	4H	20.61	21.37	21.09	21.85	22.31	20.25	21.00	20.73	21.48	21.95
	6H	21.34	21.98	21.85	22.48	22.97	20.97	21.61	21.48	22.11	22.60
	8H	21.66	22.22	22.16	22.71	23.27	21.28	21.84	21.79	22.33	22.89