

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930112

Luminaire Tested: DFN2DS-HX2F0-060DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930112
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-060DS830-RLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4804.2 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 61.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930112

CATALOG NUMBER: DFN2DS-HX2F0-060DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930112

CATALOG NUMBER: DFN2DS-HX2F0-060DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5504	5504	5504
5°	5525	5435	5465
10°	5482	5346	5301
15°	5420	5188	5038
20°	5332	4961	4712
25°	5243	4704	4397
30°	5119	4440	3991
35°	4998	4153	3636
40°	4877	3855	3225
45°	4734	3522	2853
50°	4587	3185	2488
55°	4437	2822	2136
60°	4264	2440	1773
65°	4066	2051	1615
70°	3830	1688	1485
75°	3541	1539	1386
80°	3125	1376	1263
85°	2455	1084	1084

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4734 cd/sqm

TEST NUMBER: P930112

CATALOG NUMBER: DFN2DS-HX2F0-060DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.9	4.6
10°-20°	601.0	12.5
20°-30°	843.8	17.6
30°-40°	919.8	19.1
40°-50°	845.4	17.6
50°-60°	663.9	13.8
60°-70°	432.2	9.0
70°-80°	222.5	4.6
80°-90°	56.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1663.7	34.6
0°-40°	2583.5	53.8
0°-60°	4092.8	85.2
0°-90°	4804.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4804.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2336	2336	2336	2336	2336	
5°	2336	2325	2298	2317	2311	221
15°	2222	2198	2127	2086	2065	626
25°	2017	1949	1810	1723	1691	928
35°	1738	1630	1444	1311	1264	1088
45°	1421	1279	1057	907	856	1097
55°	1080	915	687	560	520	965
65°	729	558	368	296	290	723
75°	389	241	169	154	152	411
85°	91	46	40	40	40	109
90°	0	0	0	0	0	

TEST NUMBER: P930112

CATALOG NUMBER: DFN2DS-HX2F0-060DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2336.0	2336.0	2336.0	2336.0	2336.0
2.5°	2346.5	2336.0	2312.6	2333.9	2329.7
5°	2336.0	2325.4	2297.8	2316.9	2310.6
7.5°	2316.9	2304.3	2274.7	2283.0	2272.5
10°	2291.5	2276.7	2234.6	2228.1	2215.5
12.5°	2260.0	2240.8	2183.7	2171.1	2147.8
15°	2221.8	2198.4	2126.7	2086.5	2065.4
17.5°	2177.4	2143.5	2054.7	2008.2	1974.4
20°	2126.7	2084.3	1978.7	1925.9	1879.3
22.5°	2071.7	2023.0	1900.4	1828.6	1797.0
25°	2016.8	1949.1	1809.6	1723.0	1691.2
27.5°	1951.4	1879.3	1725.0	1625.6	1577.0
30°	1881.6	1801.0	1631.9	1524.3	1467.1
32.5°	1813.8	1716.5	1543.4	1416.4	1363.5
35°	1737.8	1629.9	1444.0	1310.7	1264.1
37.5°	1663.8	1547.3	1350.9	1204.9	1152.2
40°	1585.5	1458.8	1253.5	1103.5	1048.5
42.5°	1505.2	1370.0	1156.4	999.8	947.2
45°	1420.6	1278.9	1057.1	906.8	856.1
47.5°	1340.4	1190.3	962.0	811.7	765.3
50°	1251.5	1101.5	868.9	722.9	678.7
52.5°	1164.7	1006.2	780.1	640.6	600.4
55°	1080.2	915.3	687.0	560.3	520.1
57.5°	993.6	824.4	604.7	486.3	452.3
60°	904.8	735.7	517.9	410.2	376.3
62.5°	818.2	649.1	443.9	342.5	325.6
65°	729.4	558.0	367.9	296.1	289.6
67.5°	644.8	473.4	296.1	260.0	253.7
70°	556.0	391.1	245.1	224.1	215.5
72.5°	471.5	314.9	205.0	188.2	183.9
75°	389.0	240.9	169.1	154.3	152.3
77.5°	306.6	171.2	133.2	124.7	120.5
80°	230.3	122.6	101.4	93.1	93.1
82.5°	160.6	82.5	69.7	65.5	65.5
85°	90.8	46.4	40.1	40.1	40.1
87.5°	33.9	16.9	16.9	14.8	14.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930112

CATALOG NUMBER: DFN2DS-HX2F0-060DS830-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.16	18.68	17.52	18.99	19.31	13.12	14.64	13.49	14.96	15.27
	3H	18.92	20.29	19.30	20.62	20.98	14.39	15.75	14.76	16.08	16.44
	4H	19.59	20.87	19.99	21.22	21.60	14.89	16.17	15.29	16.52	16.90
	6H	20.08	21.26	20.49	21.63	22.02	15.27	16.45	15.68	16.82	17.21
	8H	20.25	21.37	20.67	21.76	22.16	15.39	16.52	15.82	16.91	17.31
	12H	20.35	21.43	20.78	21.81	22.24	15.47	16.55	15.90	16.93	17.36
4H	2H	17.26	18.54	17.66	18.89	19.27	13.82	15.10	14.22	15.45	15.82
	3H	19.20	20.26	19.61	20.66	21.06	15.26	16.32	15.67	16.72	17.12
	4H	19.95	20.90	20.38	21.32	21.76	15.86	16.82	16.29	17.23	17.67
	6H	20.54	21.37	21.00	21.81	22.27	16.35	17.18	16.80	17.62	18.08
	8H	20.75	21.53	21.22	21.97	22.44	16.51	17.29	16.97	17.73	18.20
	12H	20.91	21.60	21.39	22.08	22.55	16.63	17.32	17.11	17.80	18.27
8H	4H	19.97	20.75	20.43	21.19	21.66	16.21	16.99	16.68	17.43	17.90
	6H	20.61	21.25	21.10	21.74	22.22	16.80	17.44	17.30	17.93	18.41
	8H	20.86	21.44	21.37	21.94	22.43	17.02	17.60	17.53	18.11	18.60
	12H	21.06	21.57	21.57	22.06	22.63	17.20	17.71	17.71	18.20	18.77
12H	4H	19.96	20.65	20.44	21.13	21.60	16.26	16.95	16.74	17.43	17.90
	6H	20.59	21.17	21.10	21.68	22.16	16.86	17.44	17.38	17.95	18.44
	8H	20.87	21.38	21.38	21.88	22.44	17.14	17.65	17.65	18.14	18.70