

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930078

Luminaire Tested: DFN2DS-HX2F0-040DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930078
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-040DS835-RLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3400.0 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 38.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930078

CATALOG NUMBER: DFN2DS-HX2F0-040DS835-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930078

CATALOG NUMBER: DFN2DS-HX2F0-040DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3895	3895	3895
5°	3910	3846	3868
10°	3880	3783	3751
15°	3835	3671	3566
20°	3774	3511	3335
25°	3711	3329	3111
30°	3623	3142	2825
35°	3538	2939	2573
40°	3451	2729	2282
45°	3350	2493	2019
50°	3247	2254	1761
55°	3140	1997	1512
60°	3017	1727	1255
65°	2878	1451	1142
70°	2711	1195	1051
75°	2505	1090	981
80°	2212	973	894
85°	1738	768	768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3350 cd/sqm

TEST NUMBER: P930078

CATALOG NUMBER: DFN2DS-HX2F0-040DS835-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.9	4.6
10°-20°	425.3	12.5
20°-30°	597.2	17.6
30°-40°	650.9	19.1
40°-50°	598.3	17.6
50°-60°	469.9	13.8
60°-70°	305.8	9.0
70°-80°	157.4	4.6
80°-90°	40.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1177.4	34.6
0°-40°	1828.4	53.8
0°-60°	2896.5	85.2
0°-90°	3400.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3400.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1653	1653	1653	1653	1653	
5°	1653	1646	1626	1640	1635	157
15°	1572	1556	1505	1477	1462	443
25°	1427	1379	1281	1219	1197	656
35°	1230	1154	1022	928	895	770
45°	1005	905	748	642	606	776
55°	764	648	486	396	368	683
65°	516	395	260	210	205	512
75°	275	170	120	109	108	291
85°	64	33	28	28	28	77
90°	0	0	0	0	0	

TEST NUMBER: P930078

CATALOG NUMBER: DFN2DS-HX2F0-040DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.2	1653.2	1653.2	1653.2	1653.2
2.5°	1660.7	1653.2	1636.7	1651.8	1648.7
5°	1653.2	1645.7	1626.2	1639.7	1635.3
7.5°	1639.7	1630.8	1609.9	1615.7	1608.3
10°	1621.8	1611.3	1581.4	1576.8	1568.0
12.5°	1599.4	1585.9	1545.4	1536.5	1520.0
15°	1572.4	1555.9	1505.1	1476.7	1461.8
17.5°	1541.0	1517.0	1454.1	1421.3	1397.3
20°	1505.1	1475.1	1400.3	1363.0	1330.0
22.5°	1466.2	1431.8	1344.9	1294.1	1271.8
25°	1427.3	1379.4	1280.6	1219.4	1196.8
27.5°	1381.0	1330.0	1220.8	1150.5	1116.0
30°	1331.6	1274.6	1154.9	1078.7	1038.3
32.5°	1283.7	1214.8	1092.2	1002.4	964.9
35°	1229.9	1153.5	1021.9	927.6	894.6
37.5°	1177.5	1095.1	956.0	852.7	815.4
40°	1122.1	1032.4	887.2	781.0	742.1
42.5°	1065.2	969.5	818.4	707.6	670.3
45°	1005.4	905.1	748.1	641.8	605.9
47.5°	948.6	842.4	680.8	574.5	541.6
50°	885.7	779.5	614.9	511.6	480.3
52.5°	824.3	712.1	552.1	453.3	424.9
55°	764.5	647.8	486.2	396.5	368.1
57.5°	703.2	583.5	427.9	344.1	320.2
60°	640.3	520.6	366.5	290.3	266.4
62.5°	579.1	459.4	314.1	242.4	230.5
65°	516.2	394.9	260.3	209.5	204.9
67.5°	456.4	335.1	209.5	184.0	179.5
70°	393.5	276.8	173.5	158.6	152.5
72.5°	333.7	222.9	145.1	133.2	130.2
75°	275.2	170.5	119.7	109.2	107.8
77.5°	217.0	121.1	94.3	88.3	85.2
80°	163.0	86.8	71.7	65.9	65.9
82.5°	113.7	58.4	49.4	46.3	46.3
85°	64.3	32.9	28.4	28.4	28.4
87.5°	24.0	11.9	11.9	10.5	10.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930078

CATALOG NUMBER: DFN2DS-HX2F0-040DS835-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.96	17.48	16.32	17.79	18.11	11.92	13.44	12.28	13.75	14.07
	3H	17.72	19.09	18.10	19.42	19.78	13.18	14.55	13.56	14.88	15.24
	4H	18.39	19.67	18.79	20.02	20.40	13.69	14.97	14.09	15.32	15.69
	6H	18.88	20.06	19.29	20.43	20.82	14.07	15.25	14.48	15.62	16.01
	8H	19.04	20.17	19.47	20.56	20.96	14.19	15.32	14.62	15.71	16.11
	12H	19.15	20.23	19.58	20.61	21.04	14.27	15.35	14.70	15.73	16.16
4H	2H	16.06	17.34	16.46	17.69	18.07	12.61	13.90	13.01	14.24	14.62
	3H	18.00	19.06	18.41	19.46	19.86	14.06	15.12	14.47	15.52	15.92
	4H	18.75	19.70	19.18	20.12	20.56	14.66	15.61	15.09	16.03	16.47
	6H	19.34	20.17	19.79	20.61	21.07	15.15	15.98	15.60	16.42	16.88
	8H	19.55	20.33	20.02	20.77	21.24	15.31	16.08	15.77	16.53	17.00
	12H	19.71	20.40	20.19	20.88	21.35	15.42	16.12	15.91	16.60	17.07
8H	4H	18.77	19.55	19.23	19.99	20.46	15.01	15.79	15.47	16.23	16.70
	6H	19.41	20.05	19.90	20.54	21.02	15.60	16.24	16.09	16.73	17.21
	8H	19.66	20.23	20.17	20.74	21.23	15.82	16.40	16.33	16.91	17.39
	12H	19.86	20.37	20.37	20.86	21.43	16.00	16.51	16.51	17.00	17.56
12H	4H	18.75	19.45	19.24	19.93	20.40	15.05	15.75	15.54	16.23	16.70
	6H	19.39	19.97	19.90	20.48	20.96	15.66	16.24	16.18	16.75	17.24
	8H	19.67	20.18	20.18	20.67	21.24	15.93	16.44	16.44	16.94	17.50