

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930095

Luminaire Tested: DFN2DS-HX2F0-050DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930095
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-050DS835-FLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4950.0 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 49.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930095

CATALOG NUMBER: DFN2DS-HX2F0-050DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930095

CATALOG NUMBER: DFN2DS-HX2F0-050DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4584	4584	4584
5°	4601	4535	4562
10°	4574	4490	4512
15°	4518	4431	4427
20°	4437	4344	4339
25°	4358	4236	4236
30°	4255	4138	4102
35°	4159	4020	3960
40°	4040	3901	3827
45°	3921	3784	3690
50°	3792	3662	3531
55°	3658	3520	3389
60°	3508	3350	3227
65°	3348	3181	3035
70°	3145	2977	2836
75°	2860	2741	2675
80°	2540	2461	2335
85°	2071	1973	1771

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3921 cd/sqm

TEST NUMBER: P930095

CATALOG NUMBER: DFN2DS-HX2F0-050DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.1	3.7
10°-20°	515.2	10.4
20°-30°	757.2	15.3
30°-40°	879.4	17.8
40°-50°	878.3	17.7
50°-60°	765.8	15.5
60°-70°	566.1	11.4
70°-80°	320.3	6.5
80°-90°	84.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1455.5	29.4
0°-40°	2334.9	47.2
0°-60°	3979.0	80.4
0°-90°	4950.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4950.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1946	1938	1918	1932	1929	185
15°	1852	1841	1816	1824	1815	522
25°	1676	1661	1630	1633	1630	771
35°	1446	1428	1398	1386	1377	903
45°	1177	1164	1136	1115	1108	908
55°	891	879	857	834	825	796
65°	601	589	571	554	544	594
75°	314	311	301	290	294	335
85°	77	75	73	67	66	90
90°	0	0	0	0	0	

TEST NUMBER: P930095

CATALOG NUMBER: DFN2DS-HX2F0-050DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1945.5	1945.5	1945.5	1945.5	1945.5
2.5°	1956.8	1947.5	1926.9	1945.5	1942.0
5°	1945.5	1938.2	1917.5	1932.4	1928.9
7.5°	1932.4	1921.3	1900.7	1915.8	1912.0
10°	1912.0	1898.9	1876.5	1891.3	1885.8
12.5°	1883.8	1872.7	1850.3	1859.6	1855.8
15°	1852.0	1840.9	1816.5	1824.1	1814.7
17.5°	1812.7	1801.6	1777.2	1786.5	1777.2
20°	1769.7	1758.6	1732.4	1737.9	1730.6
22.5°	1726.8	1709.9	1685.5	1685.5	1681.7
25°	1676.2	1661.3	1629.5	1633.1	1629.5
27.5°	1620.0	1606.9	1582.7	1577.1	1567.8
30°	1564.0	1549.0	1521.0	1515.4	1507.9
32.5°	1504.1	1493.0	1463.0	1451.7	1444.2
35°	1446.1	1427.5	1397.5	1386.2	1376.9
37.5°	1380.6	1363.8	1333.8	1320.7	1311.4
40°	1313.4	1298.3	1268.3	1251.6	1244.1
42.5°	1247.9	1232.8	1203.0	1184.1	1173.0
45°	1176.8	1163.7	1135.5	1115.1	1107.5
47.5°	1107.5	1094.4	1064.5	1043.8	1032.7
50°	1034.5	1025.2	999.0	972.8	963.4
52.5°	963.4	950.3	926.1	905.5	892.4
55°	890.6	879.3	856.8	834.4	825.1
57.5°	817.5	808.2	783.8	761.4	753.8
60°	744.5	737.2	711.0	690.3	684.8
62.5°	673.5	660.4	641.7	623.0	615.5
65°	600.6	589.3	570.6	553.8	544.4
67.5°	525.8	516.3	499.6	486.5	478.9
70°	456.5	449.0	432.1	419.0	411.7
72.5°	385.5	377.9	368.6	355.5	349.9
75°	314.2	310.6	301.1	290.0	293.8
77.5°	250.7	243.1	239.4	233.8	228.3
80°	187.2	185.2	181.4	175.9	172.1
82.5°	127.2	127.2	125.4	117.9	117.9
85°	76.6	74.8	73.0	67.3	65.5
87.5°	33.7	30.0	26.2	20.6	18.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930095

CATALOG NUMBER: DFN2DS-HX2F0-050DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.57	18.18	16.94	18.50	18.81	16.13	17.74	16.49	18.05	18.37
	3H	18.32	19.78	18.70	20.10	20.46	17.83	19.29	18.21	19.61	19.97
	4H	18.97	20.34	19.37	20.69	21.06	18.47	19.84	18.87	20.19	20.57
	6H	19.44	20.71	19.85	21.07	21.46	18.94	20.21	19.35	20.57	20.96
	8H	19.58	20.79	20.01	21.18	21.58	19.08	20.29	19.50	20.68	21.08
	12H	19.67	20.83	20.10	21.21	21.64	19.16	20.32	19.59	20.70	21.13
4H	2H	17.13	18.50	17.53	18.85	19.23	16.78	18.15	17.18	18.50	18.87
	3H	19.11	20.25	19.52	20.65	21.05	18.70	19.85	19.11	20.25	20.65
	4H	19.88	20.92	20.32	21.33	21.77	19.46	20.50	19.89	20.91	21.35
	6H	20.48	21.39	20.94	21.83	22.28	20.05	20.95	20.50	21.39	21.85
	8H	20.67	21.52	21.13	21.96	22.42	20.23	21.08	20.69	21.52	21.99
	12H	20.80	21.56	21.28	22.04	22.51	20.35	21.11	20.83	21.59	22.06
8H	4H	20.16	21.00	20.62	21.45	21.91	19.78	20.63	20.24	21.07	21.54
	6H	20.87	21.58	21.37	22.06	22.54	20.49	21.19	20.98	21.68	22.16
	8H	21.13	21.76	21.64	22.27	22.75	20.74	21.37	21.25	21.88	22.36
	12H	21.33	21.89	21.84	22.38	22.94	20.92	21.48	21.43	21.97	22.53
12H	4H	20.18	20.94	20.66	21.42	21.89	19.82	20.58	20.30	21.06	21.52
	6H	20.92	21.55	21.43	22.06	22.54	20.55	21.18	21.06	21.69	22.17
	8H	21.23	21.79	21.74	22.28	22.84	20.85	21.41	21.36	21.90	22.46