

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930113

Luminaire Tested: DFN2DS-HX2F0-060DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930113
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-060DS835-FLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5940.0 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 61.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930113

CATALOG NUMBER: DFN2DS-HX2F0-060DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930113

CATALOG NUMBER: DFN2DS-HX2F0-060DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5501	5501	5501
5°	5522	5442	5474
10°	5489	5387	5414
15°	5421	5317	5312
20°	5325	5212	5207
25°	5229	5083	5083
30°	5106	4966	4923
35°	4992	4824	4752
40°	4847	4681	4592
45°	4706	4540	4428
50°	4550	4394	4238
55°	4390	4224	4067
60°	4210	4021	3872
65°	4018	3818	3642
70°	3774	3572	3403
75°	3432	3289	3209
80°	3047	2954	2802
85°	2484	2368	2125

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4706 cd/sqm

TEST NUMBER: P930113

CATALOG NUMBER: DFN2DS-HX2F0-060DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.7	3.7
10°-20°	618.3	10.4
20°-30°	908.6	15.3
30°-40°	1055.3	17.8
40°-50°	1054.0	17.7
50°-60°	919.0	15.5
60°-70°	679.4	11.4
70°-80°	384.4	6.5
80°-90°	101.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1746.6	29.4
0°-40°	2801.8	47.2
0°-60°	4774.8	80.4
0°-90°	5940.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5940.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2335	2335	2335	2335	2335	
5°	2335	2326	2301	2319	2315	222
15°	2222	2209	2180	2189	2178	626
25°	2011	1994	1955	1960	1955	926
35°	1735	1713	1677	1663	1652	1084
45°	1412	1396	1363	1338	1329	1090
55°	1069	1055	1028	1001	990	955
65°	721	707	685	664	653	713
75°	377	373	361	348	352	402
85°	92	90	88	81	79	108
90°	0	0	0	0	0	

TEST NUMBER: P930113

CATALOG NUMBER: DFN2DS-HX2F0-060DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2334.6	2334.6	2334.6	2334.6	2334.6
2.5°	2348.2	2337.0	2312.2	2334.6	2330.3
5°	2334.6	2325.8	2301.0	2318.9	2314.6
7.5°	2318.9	2305.6	2280.8	2298.9	2294.4
10°	2294.4	2278.7	2251.7	2269.6	2262.9
12.5°	2260.6	2247.2	2220.3	2231.5	2227.0
15°	2222.4	2209.1	2179.8	2188.9	2177.7
17.5°	2175.3	2162.0	2132.7	2143.8	2132.7
20°	2123.6	2110.3	2078.8	2085.5	2076.7
22.5°	2072.2	2051.9	2022.6	2022.6	2018.1
25°	2011.4	1993.6	1955.4	1959.7	1955.4
27.5°	1944.0	1928.3	1899.2	1892.6	1881.4
30°	1876.9	1858.7	1825.2	1818.5	1809.4
32.5°	1804.9	1791.6	1755.6	1742.0	1733.0
35°	1735.4	1713.0	1677.0	1663.4	1652.2
37.5°	1656.8	1636.5	1600.6	1584.8	1573.6
40°	1576.0	1557.9	1522.0	1502.0	1492.9
42.5°	1497.4	1479.3	1443.6	1421.0	1407.6
45°	1412.2	1396.4	1362.6	1338.1	1329.0
47.5°	1329.0	1313.3	1277.4	1252.6	1239.2
50°	1241.4	1230.2	1198.8	1167.3	1156.1
52.5°	1156.1	1140.4	1111.3	1086.6	1070.9
55°	1068.7	1055.1	1028.2	1001.3	990.1
57.5°	981.1	969.9	940.6	913.7	904.6
60°	893.4	884.6	853.2	828.4	821.7
62.5°	808.1	792.4	770.0	747.6	738.6
65°	720.7	707.2	684.8	664.5	653.3
67.5°	630.9	619.5	599.5	583.8	574.7
70°	547.8	538.8	518.5	502.8	494.0
72.5°	462.5	453.5	442.3	426.6	419.9
75°	377.0	372.8	361.3	348.0	352.5
77.5°	300.8	291.8	287.2	280.6	273.9
80°	224.6	222.2	217.7	211.0	206.5
82.5°	152.7	152.7	150.5	141.5	141.5
85°	91.9	89.8	87.6	80.7	78.6
87.5°	40.5	36.0	31.4	24.8	22.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930113

CATALOG NUMBER: DFN2DS-HX2F0-060DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.21	18.82	17.57	19.13	19.45	16.76	18.37	17.13	18.69	19.00
	3H	18.96	20.41	19.33	20.74	21.10	18.47	19.92	18.84	20.25	20.61
	4H	19.60	20.97	20.00	21.32	21.70	19.11	20.48	19.51	20.82	21.20
	6H	20.07	21.34	20.48	21.70	22.10	19.57	20.84	19.98	21.20	21.59
	8H	20.21	21.43	20.64	21.81	22.21	19.71	20.92	20.14	21.31	21.71
	12H	20.30	21.46	20.73	21.85	22.28	19.79	20.95	20.22	21.33	21.76
4H	2H	17.77	19.14	18.17	19.48	19.86	17.41	18.78	17.81	19.13	19.51
	3H	19.74	20.89	20.15	21.29	21.69	19.33	20.48	19.74	20.88	21.28
	4H	20.52	21.55	20.95	21.97	22.40	20.09	21.13	20.53	21.54	21.98
	6H	21.11	22.02	21.57	22.46	22.92	20.68	21.59	21.14	22.03	22.48
	8H	21.30	22.15	21.76	22.59	23.06	20.87	21.71	21.33	22.16	22.62
	12H	21.44	22.20	21.92	22.67	23.14	20.98	21.74	21.46	22.22	22.69
8H	4H	20.79	21.64	21.25	22.08	22.55	20.42	21.26	20.88	21.71	22.17
	6H	21.51	22.21	22.00	22.70	23.17	21.12	21.83	21.62	22.32	22.79
	8H	21.76	22.40	22.27	22.90	23.39	21.37	22.00	21.88	22.51	23.00
	12H	21.96	22.52	22.47	23.01	23.57	21.55	22.11	22.06	22.60	23.16
12H	4H	20.82	21.58	21.30	22.05	22.52	20.45	21.21	20.93	21.69	22.16
	6H	21.55	22.18	22.06	22.69	23.18	21.18	21.81	21.69	22.32	22.81
	8H	21.87	22.42	22.37	22.91	23.47	21.49	22.04	21.99	22.54	23.10