

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036896

Luminaire Tested: S122DS-B1005DB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036896
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DS-B1005DB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Direct Surface with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4041.0 lumens
Efficiency: N/A
Efficacy: 65.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036896

CATALOG NUMBER: S122DS-B1005DB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1036896

CATALOG NUMBER: S122DS-B1005DB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	86	86	84
2	99	91	85	79	97	89	83	78	86	81	76	83	78	74	80	76	73	73	73	71
3	91	80	72	66	88	79	71	65	76	69	64	73	68	63	71	66	62	62	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	54	54	51
5	77	64	55	49	75	63	55	48	61	53	48	59	52	47	57	51	47	47	47	45
6	71	58	49	43	69	57	48	42	55	48	42	53	47	42	52	46	41	41	41	39
7	66	52	44	38	64	52	43	38	50	43	37	49	42	37	47	41	37	37	37	35
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	33	33	31
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	30	30	28
10	54	41	33	28	53	40	33	28	39	32	27	38	32	27	37	32	27	27	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25142	25142	25142
5°	25238	24874	25020
10°	25089	24621	24745
15°	24778	24303	24277
20°	24338	23822	23797
25°	23900	23233	23233
30°	23337	22696	22500
35°	22814	22047	21722
40°	22154	21397	20986
45°	21504	20752	20239
50°	20799	20085	19368
55°	20063	19304	18587
60°	19242	18375	17697
65°	18361	17447	16645
70°	17245	16328	15551
75°	15694	15039	14666
80°	13920	13500	12808
85°	11369	10825	9717

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21504 cd/sqm

TEST NUMBER: P1036896

CATALOG NUMBER: S122DS-B1005DB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.5	3.7
10°-20°	420.6	10.4
20°-30°	618.1	15.3
30°-40°	717.9	17.8
40°-50°	717.0	17.7
50°-60°	625.2	15.5
60°-70°	462.2	11.4
70°-80°	261.5	6.5
80°-90°	69.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1188.2	29.4
0°-40°	1906.1	47.2
0°-60°	3248.3	80.4
0°-90°	4041.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4041.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1588	1588	1588	1588	1588	
5°	1588	1582	1565	1578	1575	151
15°	1512	1503	1483	1489	1481	426
25°	1368	1356	1330	1333	1330	630
35°	1181	1165	1141	1132	1124	737
45°	961	950	927	910	904	741
55°	727	718	700	681	674	650
65°	490	481	466	452	444	485
75°	257	254	246	237	240	274
85°	63	61	60	55	54	74
90°	0	0	0	0	0	



TEST NUMBER: P1036896

CATALOG NUMBER: S122DS-B1005DB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1588.3	1588.3	1588.3	1588.3	1588.3
2.5°	1597.5	1589.9	1573.1	1588.3	1585.3
5°	1588.3	1582.2	1565.4	1577.7	1574.6
7.5°	1577.7	1568.5	1551.7	1563.9	1560.9
10°	1560.9	1550.2	1531.8	1544.1	1539.5
12.5°	1537.9	1528.8	1510.5	1518.1	1515.0
15°	1512.0	1502.8	1483.0	1489.1	1481.4
17.5°	1479.9	1470.7	1450.9	1458.5	1450.9
20°	1444.8	1435.6	1414.2	1418.8	1412.7
22.5°	1409.7	1395.9	1376.1	1376.1	1373.0
25°	1368.4	1356.2	1330.2	1333.3	1330.2
27.5°	1322.6	1311.9	1292.1	1287.5	1279.8
30°	1276.8	1264.6	1241.7	1237.1	1231.0
32.5°	1227.9	1218.7	1194.3	1185.1	1179.0
35°	1180.6	1165.3	1140.9	1131.7	1124.1
37.5°	1127.1	1113.4	1088.9	1078.2	1070.6
40°	1072.1	1059.9	1035.5	1021.7	1015.6
42.5°	1018.7	1006.5	982.0	966.8	957.6
45°	960.6	950.0	927.0	910.2	904.1
47.5°	904.1	893.4	869.0	852.2	843.0
50°	844.6	836.9	815.6	794.2	786.5
52.5°	786.5	775.8	756.0	739.2	728.5
55°	727.0	717.8	699.5	681.2	673.5
57.5°	667.4	659.8	639.9	621.6	615.5
60°	607.8	601.7	580.4	563.6	559.0
62.5°	549.8	539.1	523.8	508.6	502.5
65°	490.2	481.1	465.8	452.1	444.4
67.5°	429.2	421.5	407.8	397.1	391.0
70°	372.6	366.5	352.8	342.1	336.0
72.5°	314.6	308.5	300.9	290.2	285.6
75°	256.6	253.5	245.9	236.7	239.8
77.5°	204.7	198.5	195.5	190.9	186.3
80°	152.7	151.2	148.1	143.6	140.5
82.5°	103.9	103.9	102.3	96.2	96.2
85°	62.6	61.1	59.6	55.0	53.5
87.5°	27.5	24.4	21.4	16.8	15.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)