

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930080

Luminaire Tested: DFN2DS-HX2F0-040DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930080
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-040DS840-RLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3403.4 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 38.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930080

CATALOG NUMBER: DFN2DS-HX2F0-040DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930080

CATALOG NUMBER: DFN2DS-HX2F0-040DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92	90	88	86
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82	79	76	74
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74	69	66	64
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66	62	57	55
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60	55	51	49
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55	50	45	43
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51	45	41	39
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47	41	37	35
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44	38	34	32
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3899	3899	3899
5°	3914	3850	3871
10°	3884	3787	3755
15°	3839	3675	3569
20°	3778	3515	3338
25°	3714	3333	3114
30°	3626	3145	2828
35°	3541	2942	2576
40°	3455	2732	2285
45°	3353	2495	2021
50°	3250	2256	1762
55°	3144	1999	1514
60°	3020	1729	1257
65°	2881	1453	1143
70°	2714	1197	1052
75°	2508	1091	982
80°	2214	974	896
85°	1741	768	768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3353 cd/sqm

TEST NUMBER: P930080

CATALOG NUMBER: DFN2DS-HX2F0-040DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.1	4.6
10°-20°	425.8	12.5
20°-30°	597.8	17.6
30°-40°	651.6	19.1
40°-50°	598.9	17.6
50°-60°	470.3	13.8
60°-70°	306.1	9.0
70°-80°	157.6	4.6
80°-90°	40.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1178.6	34.6
0°-40°	1830.2	53.8
0°-60°	2899.4	85.2
0°-90°	3403.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3403.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1655	1655	1655	1655	1655	
5°	1655	1647	1628	1641	1637	157
15°	1574	1558	1507	1478	1463	444
25°	1429	1381	1282	1221	1198	657
35°	1231	1155	1023	928	896	771
45°	1006	906	749	642	606	777
55°	765	648	487	397	368	684
65°	517	395	261	210	205	512
75°	276	171	120	109	108	291
85°	64	33	28	28	28	77
90°	0	0	0	0	0	

TEST NUMBER: P930080

CATALOG NUMBER: DFN2DS-HX2F0-040DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1654.9	1654.9	1654.9	1654.9	1654.9
2.5°	1662.4	1654.9	1638.3	1653.5	1650.3
5°	1654.9	1647.3	1627.8	1641.3	1636.9
7.5°	1641.3	1632.4	1611.5	1617.3	1609.9
10°	1623.4	1612.9	1583.0	1578.4	1569.6
12.5°	1601.0	1587.5	1546.9	1538.0	1521.5
15°	1574.0	1557.5	1506.6	1478.2	1463.3
17.5°	1542.5	1518.5	1455.6	1422.7	1398.7
20°	1506.6	1476.6	1401.7	1364.4	1331.3
22.5°	1467.7	1433.2	1346.2	1295.4	1273.1
25°	1428.7	1380.8	1281.9	1220.6	1198.0
27.5°	1382.4	1331.3	1222.0	1151.7	1117.1
30°	1332.9	1275.9	1156.1	1079.8	1039.3
32.5°	1285.0	1216.0	1093.3	1003.4	965.9
35°	1231.1	1154.7	1022.9	928.5	895.5
37.5°	1178.7	1096.2	957.0	853.6	816.2
40°	1123.2	1033.4	888.1	781.8	742.8
42.5°	1066.3	970.5	819.2	708.3	671.0
45°	1006.4	906.0	748.8	642.4	606.5
47.5°	949.5	843.2	681.5	575.1	542.1
50°	886.6	780.3	615.5	512.1	480.8
52.5°	825.1	712.8	552.7	453.8	425.3
55°	765.3	648.4	486.7	396.9	368.5
57.5°	703.9	584.1	428.3	344.4	320.5
60°	640.9	521.1	366.9	290.6	266.7
62.5°	579.7	459.9	314.4	242.6	230.7
65°	516.7	395.3	260.6	209.7	205.1
67.5°	456.9	335.4	209.7	184.2	179.7
70°	393.9	277.1	173.7	158.8	152.7
72.5°	334.0	223.1	145.2	133.3	130.3
75°	275.5	170.7	119.8	109.3	107.9
77.5°	217.2	121.2	94.4	88.4	85.3
80°	163.2	86.9	71.8	66.0	66.0
82.5°	113.8	58.5	49.4	46.3	46.3
85°	64.4	32.9	28.4	28.4	28.4
87.5°	24.0	11.9	11.9	10.5	10.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930080

CATALOG NUMBER: DFN2DS-HX2F0-040DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.96	17.48	16.33	17.80	18.11	11.92	13.44	12.29	13.76	14.07
	3H	17.73	19.09	18.11	19.42	19.78	13.19	14.55	13.57	14.88	15.24
	4H	18.39	19.67	18.79	20.02	20.40	13.69	14.97	14.09	15.32	15.70
	6H	18.88	20.07	19.30	20.43	20.82	14.07	15.25	14.48	15.62	16.01
	8H	19.05	20.18	19.47	20.56	20.97	14.20	15.32	14.62	15.71	16.11
	12H	19.15	20.23	19.58	20.61	21.04	14.28	15.35	14.71	15.74	16.17
4H	2H	16.07	17.35	16.47	17.70	18.07	12.62	13.90	13.02	14.25	14.63
	3H	18.00	19.06	18.41	19.46	19.86	14.06	15.12	14.47	15.52	15.93
	4H	18.75	19.71	19.18	20.12	20.56	14.66	15.62	15.09	16.03	16.47
	6H	19.34	20.17	19.80	20.62	21.08	15.15	15.98	15.61	16.42	16.88
	8H	19.56	20.33	20.02	20.78	21.24	15.31	16.09	15.77	16.53	17.00
	12H	19.71	20.40	20.19	20.88	21.35	15.43	16.12	15.91	16.60	17.07
8H	4H	18.77	19.55	19.24	19.99	20.46	15.01	15.79	15.48	16.24	16.70
	6H	19.41	20.05	19.91	20.54	21.02	15.60	16.24	16.10	16.74	17.21
	8H	19.66	20.24	20.18	20.75	21.24	15.82	16.40	16.34	16.91	17.40
	12H	19.87	20.38	20.38	20.87	21.43	16.00	16.51	16.51	17.00	17.57
12H	4H	18.76	19.45	19.24	19.93	20.40	15.06	15.75	15.54	16.23	16.70
	6H	19.39	19.97	19.91	20.48	20.97	15.67	16.24	16.18	16.75	17.24
	8H	19.68	20.19	20.19	20.68	21.24	15.94	16.45	16.45	16.94	17.50