

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930081

Luminaire Tested: DFN2DS-HX2F0-040DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930081
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-040DS850-FLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4391.7 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930081

CATALOG NUMBER: DFN2DS-HX2F0-040DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930081

CATALOG NUMBER: DFN2DS-HX2F0-040DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4067	4067	4067
5°	4082	4024	4047
10°	4058	3983	4003
15°	4008	3931	3927
20°	3937	3854	3850
25°	3866	3758	3758
30°	3775	3671	3640
35°	3690	3566	3514
40°	3584	3461	3395
45°	3479	3357	3274
50°	3364	3249	3133
55°	3246	3123	3007
60°	3112	2973	2863
65°	2971	2823	2693
70°	2790	2641	2516
75°	2538	2432	2372
80°	2252	2183	2072
85°	1838	1752	1571

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3479 cd/sqm

TEST NUMBER: P930081

CATALOG NUMBER: DFN2DS-HX2F0-040DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	3.7
10°-20°	457.1	10.4
20°-30°	671.7	15.3
30°-40°	780.2	17.8
40°-50°	779.2	17.7
50°-60°	679.5	15.5
60°-70°	502.3	11.4
70°-80°	284.2	6.5
80°-90°	75.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1291.3	29.4
0°-40°	2071.5	47.2
0°-60°	3530.2	80.4
0°-90°	4391.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4391.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1726	1720	1701	1714	1711	164
15°	1643	1633	1612	1618	1610	463
25°	1487	1474	1446	1449	1446	684
35°	1283	1266	1240	1230	1222	801
45°	1044	1032	1007	989	983	806
55°	790	780	760	740	732	706
65°	533	523	506	491	483	527
75°	279	276	267	257	261	298
85°	68	66	65	60	58	80
90°	0	0	0	0	0	

TEST NUMBER: P930081

CATALOG NUMBER: DFN2DS-HX2F0-040DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1736.1	1727.8	1709.5	1726.0	1722.9
5°	1726.0	1719.5	1701.2	1714.4	1711.3
7.5°	1714.4	1704.5	1686.2	1699.7	1696.3
10°	1696.3	1684.7	1664.8	1678.0	1673.0
12.5°	1671.3	1661.4	1641.5	1649.9	1646.4
15°	1643.1	1633.2	1611.6	1618.3	1610.0
17.5°	1608.3	1598.4	1576.8	1585.0	1576.8
20°	1570.0	1560.1	1537.0	1541.8	1535.4
22.5°	1532.0	1517.0	1495.4	1495.4	1492.0
25°	1487.1	1473.9	1445.7	1448.9	1445.7
27.5°	1437.3	1425.6	1404.2	1399.2	1391.0
30°	1387.6	1374.3	1349.4	1344.4	1337.8
32.5°	1334.5	1324.6	1298.0	1288.0	1281.2
35°	1283.0	1266.5	1239.9	1229.9	1221.6
37.5°	1224.9	1209.9	1183.3	1171.8	1163.5
40°	1165.2	1151.8	1125.2	1110.4	1103.8
42.5°	1107.1	1093.7	1067.3	1050.6	1040.7
45°	1044.0	1032.5	1007.4	989.3	982.6
47.5°	982.6	970.9	944.4	926.1	916.3
50°	917.8	909.5	886.3	863.0	854.7
52.5°	854.7	843.2	821.7	803.4	791.7
55°	790.2	780.1	760.2	740.3	732.1
57.5°	725.3	717.1	695.3	675.5	668.8
60°	660.5	654.0	630.8	612.5	607.5
62.5°	597.5	585.9	569.4	552.7	546.1
65°	532.9	522.8	506.3	491.3	483.1
67.5°	466.4	458.0	443.3	431.6	425.0
70°	405.0	398.4	383.4	371.7	365.2
72.5°	342.0	335.3	327.0	315.4	310.4
75°	278.8	275.6	267.2	257.3	260.6
77.5°	222.4	215.7	212.4	207.4	202.5
80°	166.0	164.2	160.9	156.0	152.7
82.5°	112.9	112.9	111.3	104.6	104.6
85°	68.0	66.4	64.8	59.7	58.1
87.5°	29.9	26.6	23.3	18.3	16.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930081

CATALOG NUMBER: DFN2DS-HX2F0-040DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.16	17.77	16.52	18.08	18.40	15.71	17.32	16.08	17.64	17.95
	3H	17.91	19.36	18.28	19.69	20.05	17.42	18.87	17.79	19.20	19.56
	4H	18.55	19.92	18.95	20.27	20.65	18.06	19.43	18.46	19.78	20.15
	6H	19.02	20.29	19.43	20.66	21.05	18.52	19.79	18.93	20.15	20.54
	8H	19.17	20.38	19.59	20.77	21.16	18.66	19.87	19.09	20.26	20.66
	12H	19.26	20.42	19.69	20.80	21.23	18.74	19.90	19.17	20.29	20.71
4H	2H	16.72	18.09	17.12	18.43	18.81	16.36	17.73	16.76	18.08	18.46
	3H	18.69	19.84	19.10	20.24	20.64	18.29	19.43	18.70	19.83	20.23
	4H	19.47	20.50	19.90	20.92	21.35	19.04	20.08	19.48	20.49	20.93
	6H	20.07	20.97	20.52	21.41	21.87	19.63	20.54	20.09	20.98	21.43
	8H	20.25	21.10	20.72	21.54	22.01	19.82	20.66	20.28	21.11	21.57
	12H	20.39	21.15	20.87	21.62	22.09	19.93	20.69	20.41	21.17	21.64
8H	4H	19.74	20.59	20.20	21.03	21.50	19.37	20.21	19.83	20.66	21.12
	6H	20.46	21.16	20.95	21.65	22.12	20.07	20.78	20.57	21.27	21.74
	8H	20.72	21.35	21.23	21.85	22.34	20.32	20.95	20.83	21.46	21.95
	12H	20.92	21.47	21.42	21.96	22.53	20.50	21.06	21.01	21.55	22.11
12H	4H	19.77	20.53	20.25	21.00	21.47	19.40	20.16	19.88	20.64	21.11
	6H	20.50	21.13	21.01	21.64	22.13	20.13	20.77	20.64	21.27	21.76
	8H	20.82	21.37	21.32	21.86	22.43	20.44	21.00	20.94	21.49	22.05