

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930100

Luminaire Tested: DFN2DS-HX2F0-050DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930100
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-050DS850-RLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4713.3 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 49.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930100

CATALOG NUMBER: DFN2DS-HX2F0-050DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930100

CATALOG NUMBER: DFN2DS-HX2F0-050DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5400	5400	5400
5°	5420	5332	5362
10°	5379	5245	5200
15°	5317	5090	4943
20°	5232	4867	4623
25°	5144	4615	4313
30°	5022	4356	3916
35°	4904	4075	3567
40°	4784	3783	3164
45°	4644	3455	2798
50°	4501	3125	2440
55°	4353	2768	2096
60°	4183	2394	1740
65°	3989	2012	1584
70°	3758	1657	1457
75°	3474	1510	1360
80°	3066	1350	1239
85°	2411	1065	1065

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4644 cd/sqm

TEST NUMBER: P930100

CATALOG NUMBER: DFN2DS-HX2F0-050DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	4.6
10°-20°	589.6	12.5
20°-30°	827.8	17.6
30°-40°	902.4	19.1
40°-50°	829.4	17.6
50°-60°	651.3	13.8
60°-70°	424.0	9.0
70°-80°	218.2	4.6
80°-90°	55.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1632.2	34.6
0°-40°	2534.6	53.8
0°-60°	4015.3	85.2
0°-90°	4713.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4713.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2292	2292	2292	2292	2292	
5°	2292	2281	2254	2273	2267	217
15°	2180	2157	2086	2047	2026	614
25°	1979	1912	1775	1690	1659	910
35°	1705	1599	1417	1286	1240	1067
45°	1394	1255	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	716	548	361	290	284	709
75°	382	236	166	151	149	404
85°	89	46	39	39	39	107
90°	0	0	0	0	0	

TEST NUMBER: P930100

CATALOG NUMBER: DFN2DS-HX2F0-050DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.7	2291.7	2291.7	2291.7	2291.7
2.5°	2302.1	2291.7	2268.9	2289.8	2285.5
5°	2291.7	2281.4	2254.4	2273.0	2266.9
7.5°	2273.0	2260.7	2231.6	2239.8	2229.4
10°	2248.2	2233.6	2192.3	2185.9	2173.5
12.5°	2217.1	2198.5	2142.4	2130.1	2107.1
15°	2179.7	2156.9	2086.5	2047.1	2026.4
17.5°	2136.2	2103.0	2015.8	1970.2	1937.0
20°	2086.5	2044.9	1941.2	1889.5	1843.7
22.5°	2032.6	1984.8	1864.5	1794.0	1763.0
25°	1978.6	1912.1	1775.3	1690.3	1659.1
27.5°	1914.4	1843.7	1692.3	1594.9	1547.2
30°	1845.9	1767.0	1601.1	1495.4	1439.3
32.5°	1779.5	1684.0	1514.1	1389.6	1337.7
35°	1704.9	1599.1	1416.6	1285.9	1240.2
37.5°	1632.2	1518.1	1325.4	1182.1	1130.4
40°	1555.5	1431.2	1229.8	1082.6	1028.7
42.5°	1476.7	1344.0	1134.5	980.9	929.2
45°	1393.8	1254.7	1037.0	889.6	839.8
47.5°	1314.9	1167.8	943.8	796.4	750.8
50°	1227.9	1080.6	852.5	709.2	665.8
52.5°	1142.7	987.1	765.3	628.5	589.1
55°	1059.8	898.0	673.9	549.6	510.3
57.5°	974.8	808.9	593.2	477.1	443.8
60°	887.6	721.7	508.0	402.5	369.2
62.5°	802.7	636.8	435.5	336.0	319.5
65°	715.5	547.5	360.9	290.4	284.1
67.5°	632.6	464.6	290.4	255.1	248.9
70°	545.5	383.7	240.5	219.8	211.5
72.5°	462.6	309.0	201.2	184.6	180.4
75°	381.6	236.3	165.9	151.4	149.4
77.5°	300.8	167.9	130.8	122.3	118.1
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.6	81.0	68.4	64.2	64.2
85°	89.2	45.6	39.4	39.4	39.4
87.5°	33.3	16.5	16.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930100

CATALOG NUMBER: DFN2DS-HX2F0-050DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.09	18.62	17.46	18.93	19.24	13.05	14.58	13.42	14.89	15.20
	3H	18.86	20.22	19.24	20.55	20.91	14.32	15.69	14.70	16.01	16.37
	4H	19.53	20.81	19.93	21.15	21.53	14.82	16.10	15.22	16.45	16.83
	6H	20.01	21.20	20.43	21.56	21.96	15.20	16.39	15.61	16.75	17.14
	8H	20.18	21.31	20.61	21.70	22.10	15.33	16.45	15.75	16.84	17.24
	12H	20.28	21.36	20.71	21.74	22.17	15.41	16.49	15.84	16.87	17.30
4H	2H	17.20	18.48	17.60	18.83	19.21	13.75	15.03	14.15	15.38	15.76
	3H	19.13	20.19	19.54	20.59	20.99	15.19	16.26	15.60	16.66	17.06
	4H	19.88	20.84	20.31	21.25	21.69	15.79	16.75	16.23	17.16	17.60
	6H	20.47	21.30	20.93	21.75	22.21	16.28	17.11	16.74	17.56	18.01
	8H	20.69	21.46	21.15	21.91	22.38	16.44	17.22	16.91	17.66	18.13
	12H	20.84	21.54	21.32	22.01	22.48	16.56	17.25	17.04	17.73	18.20
8H	4H	19.90	20.68	20.37	21.13	21.59	16.15	16.92	16.61	17.37	17.84
	6H	20.54	21.18	21.04	21.68	22.15	16.73	17.38	17.23	17.87	18.34
	8H	20.79	21.37	21.31	21.88	22.37	16.95	17.53	17.47	18.04	18.53
	12H	21.00	21.51	21.51	22.00	22.56	17.13	17.64	17.64	18.13	18.70
12H	4H	19.89	20.58	20.37	21.06	21.53	16.19	16.88	16.67	17.36	17.83
	6H	20.52	21.10	21.04	21.61	22.10	16.80	17.37	17.31	17.88	18.37
	8H	20.81	21.32	21.32	21.81	22.37	17.07	17.58	17.58	18.07	18.64