

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1037178

Luminaire Tested: S122RDS-B485DB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1037178
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-24)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDS-B485DB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Regressed Direct Surface with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1690.0 lumens
Efficiency: N/A
Efficacy: 70.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 24
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1037178

CATALOG NUMBER: S122RDS-B485DB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1037178

CATALOG NUMBER: S122RDS-B485DB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86		
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	74		
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	64		
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	55		
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43		
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39		
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	29		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13007	13007	13007
5°	13057	12844	12915
10°	12957	12634	12526
15°	12809	12260	11906
20°	12602	11726	11136
25°	12390	11119	10390
30°	12096	10493	9433
35°	11813	9815	8593
40°	11524	9113	7623
45°	11186	8323	6743
50°	10840	7526	5878
55°	10487	6670	5048
60°	10077	5768	4192
65°	9611	4847	3817
70°	9053	3994	3513
75°	8367	3639	3272
80°	7393	3254	2981
85°	5812	2561	2561

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11186 cd/sqm

TEST NUMBER: P1037178

CATALOG NUMBER: S122RDS-B485DB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	4.6
10°-20°	211.4	12.5
20°-30°	296.8	17.6
30°-40°	323.6	19.1
40°-50°	297.4	17.6
50°-60°	233.5	13.8
60°-70°	152.0	9.0
70°-80°	78.3	4.6
80°-90°	20.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	585.3	34.6
0°-40°	908.8	53.8
0°-60°	1439.7	85.2
0°-90°	1690.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1690.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	822	822	822	822	822	
5°	822	818	808	815	813	78
15°	782	773	748	734	726	220
25°	709	686	637	606	595	326
35°	611	573	508	461	445	383
45°	500	450	372	319	301	386
55°	380	322	242	197	183	340
65°	257	196	129	104	102	254
75°	137	85	60	54	54	145
85°	32	16	14	14	14	38
90°	0	0	0	0	0	

TEST NUMBER: P1037178

CATALOG NUMBER: S122RDS-B485DB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	821.7	821.7	821.7	821.7	821.7
2.5°	825.5	821.7	813.6	821.0	819.5
5°	821.7	818.0	808.3	815.0	812.8
7.5°	815.0	810.6	800.2	803.1	799.4
10°	806.1	800.9	786.0	783.8	779.3
12.5°	795.0	788.3	768.2	763.7	755.5
15°	781.6	773.4	748.1	734.0	726.5
17.5°	766.0	754.1	722.8	706.5	694.6
20°	748.1	733.2	696.1	677.5	661.1
22.5°	728.8	711.7	668.5	643.3	632.1
25°	709.4	685.6	636.6	606.1	594.9
27.5°	686.4	661.1	606.8	571.9	554.8
30°	661.8	633.6	574.1	536.2	516.1
32.5°	638.1	603.8	542.9	498.2	479.7
35°	611.3	573.4	507.9	461.1	444.7
37.5°	585.3	544.4	475.2	423.9	405.3
40°	557.7	513.1	441.0	388.2	368.9
42.5°	529.5	481.9	406.8	351.7	333.2
45°	499.7	449.9	371.8	319.0	301.2
47.5°	471.5	418.7	338.4	285.6	269.2
50°	440.2	387.4	305.6	254.3	238.7
52.5°	409.8	354.0	274.4	225.3	211.2
55°	380.0	322.0	241.7	197.1	182.9
57.5°	349.5	290.0	212.7	171.0	159.1
60°	318.3	258.8	182.2	144.3	132.4
62.5°	287.8	228.3	156.2	120.5	114.5
65°	256.6	196.3	129.4	104.1	101.9
67.5°	226.8	166.6	104.1	91.5	89.2
70°	195.6	137.6	86.3	78.8	75.9
72.5°	165.8	110.8	72.1	66.2	64.7
75°	136.8	84.8	59.5	54.3	53.5
77.5°	107.8	60.2	46.8	43.9	42.4
80°	81.1	43.1	35.7	32.7	32.7
82.5°	56.5	29.0	24.5	23.1	23.1
85°	32.0	16.4	14.1	14.1	14.1
87.5°	11.9	5.9	5.9	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)