

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1037201

Luminaire Tested: S122RDS-B675DB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1037201
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-24)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDS-B675DB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Regressed Direct Surface with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2242.0 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 35.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1037201

CATALOG NUMBER: S122RDS-B675DB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1037201

CATALOG NUMBER: S122RDS-B675DB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86		
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	74		
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	64		
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	55		
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43		
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39		
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	29		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17256	17256	17256
5°	17321	17040	17134
10°	17189	16761	16618
15°	16992	16265	15796
20°	16719	15555	14773
25°	16439	14750	13784
30°	16048	13921	12515
35°	15670	13021	11401
40°	15289	12088	10111
45°	14842	11043	8945
50°	14382	9986	7799
55°	13912	8848	6698
60°	13366	7652	5559
65°	12750	6431	5064
70°	12010	5295	4656
75°	11100	4825	4342
80°	9799	4321	3956
85°	7701	3396	3396

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14842 cd/sqm

TEST NUMBER: P1037201

CATALOG NUMBER: S122RDS-B675DB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.2	4.6
10°-20°	280.5	12.5
20°-30°	393.8	17.6
30°-40°	429.2	19.1
40°-50°	394.5	17.6
50°-60°	309.8	13.8
60°-70°	201.7	9.0
70°-80°	103.8	4.6
80°-90°	26.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	776.4	34.6
0°-40°	1205.7	53.8
0°-60°	1910.0	85.2
0°-90°	2242.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2242.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1090	1090	1090	1090	1090	
5°	1090	1085	1072	1081	1078	103
15°	1037	1026	992	974	964	292
25°	941	910	844	804	789	433
35°	811	761	674	612	590	508
45°	663	597	493	423	400	512
55°	504	427	321	261	243	450
65°	340	260	172	138	135	337
75°	182	112	79	72	71	192
85°	42	22	19	19	19	51
90°	0	0	0	0	0	

TEST NUMBER: P1037201

CATALOG NUMBER: S122RDS-B675DB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1090.1	1090.1	1090.1	1090.1	1090.1
2.5°	1095.1	1090.1	1079.3	1089.1	1087.2
5°	1090.1	1085.2	1072.4	1081.3	1078.3
7.5°	1081.3	1075.3	1061.5	1065.5	1060.5
10°	1069.4	1062.5	1042.8	1039.8	1033.9
12.5°	1054.6	1045.7	1019.1	1013.2	1002.3
15°	1036.9	1026.0	992.5	973.7	963.9
17.5°	1016.1	1000.4	958.9	937.2	921.4
20°	992.5	972.7	923.4	898.7	877.0
22.5°	966.8	944.1	886.9	853.4	838.6
25°	941.2	909.6	844.5	804.0	789.2
27.5°	910.6	877.0	805.0	758.7	736.0
30°	878.0	840.5	761.6	711.3	684.7
32.5°	846.5	801.1	720.2	661.0	636.3
35°	810.9	760.6	673.8	611.7	590.0
37.5°	776.4	722.2	630.4	562.3	537.7
40°	739.9	680.7	585.0	515.0	489.3
42.5°	702.4	639.3	539.6	466.6	442.0
45°	663.0	596.9	493.3	423.2	399.6
47.5°	625.5	555.4	448.9	378.8	357.1
50°	584.0	514.0	405.5	337.4	316.7
52.5°	543.6	469.6	364.0	298.9	280.2
55°	504.1	427.2	320.6	261.4	242.7
57.5°	463.7	384.8	282.2	226.9	211.1
60°	422.2	343.3	241.7	191.4	175.6
62.5°	381.8	302.9	207.2	159.8	151.9
65°	340.4	260.4	171.7	138.1	135.2
67.5°	300.9	221.0	138.1	121.3	118.4
70°	259.5	182.5	114.4	104.6	100.6
72.5°	220.0	147.0	95.7	87.8	85.8
75°	181.5	112.5	78.9	72.0	71.0
77.5°	143.0	79.9	62.2	58.2	56.2
80°	107.5	57.2	47.4	43.4	43.4
82.5°	75.0	38.5	32.6	30.6	30.6
85°	42.4	21.7	18.7	18.7	18.7
87.5°	15.8	7.9	7.9	6.9	6.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)