

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1037364

Luminaire Tested: S123DS-B775DB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1037364
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DS-B775DB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Direct Surface with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3200.0 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 35.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1037364

CATALOG NUMBER: S123DS-B775DB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1037364

CATALOG NUMBER: S123DS-B775DB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	109	104	100	96	106	102	98	95	98	94	92	94	91	89	90	88	86	84			
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	70			
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	59			
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	51			
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	57	51	46	44			
6	71	57	49	42	69	56	48	42	55	47	42	53	46	41	51	46	41	39			
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34			
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31			
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30	28			
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13235	13235	13235
5°	13297	13114	13206
10°	13208	13000	13081
15°	13054	12853	12878
20°	12873	12643	12655
25°	12632	12393	12368
30°	12366	12116	12024
35°	12086	11822	11670
40°	11795	11498	11320
45°	11475	11201	10928
50°	11154	10834	10535
55°	10734	10457	10138
60°	10310	10015	9696
65°	9936	9533	9235
70°	9382	8985	8585
75°	8576	8268	7914
80°	7736	7407	7339
85°	6793	6533	6262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11475 cd/sqm

TEST NUMBER: P1037364

CATALOG NUMBER: S123DS-B775DB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.9	3.6
10°-20°	327.3	10.2
20°-30°	483.4	15.1
30°-40°	564.6	17.6
40°-50°	567.5	17.7
50°-60°	498.6	15.6
60°-70°	371.3	11.6
70°-80°	211.3	6.6
80°-90°	60.1	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	926.6	29.0
0°-40°	1491.2	46.6
0°-60°	2557.3	79.9
0°-90°	3200.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3200.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1171	1167	1153	1162	1156	330
25°	1064	1057	1044	1044	1041	490
35°	920	913	900	893	888	575
45°	754	750	736	723	718	582
55°	572	571	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	220
85°	55	53	53	51	51	63
90°	0	0	0	0	0	

TEST NUMBER: P1037364

CATALOG NUMBER: S123DS-B775DB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1229.6	1229.6	1229.6	1229.6	1229.6
2.5°	1234.8	1230.6	1219.0	1229.6	1228.5
5°	1230.6	1225.3	1213.7	1224.3	1222.2
7.5°	1221.1	1215.8	1204.2	1213.7	1212.6
10°	1208.4	1203.1	1189.4	1198.9	1196.8
12.5°	1191.5	1187.3	1174.6	1180.9	1179.9
15°	1171.4	1167.2	1153.4	1161.9	1155.6
17.5°	1149.2	1143.9	1130.2	1136.5	1134.4
20°	1123.8	1117.5	1103.7	1108.0	1104.8
22.5°	1095.3	1088.9	1075.2	1078.4	1074.1
25°	1063.6	1057.2	1043.5	1044.5	1041.4
27.5°	1030.8	1024.5	1009.7	1010.7	1007.5
30°	994.9	989.6	974.8	974.8	967.4
32.5°	958.9	951.5	940.9	933.5	930.4
35°	919.8	913.4	899.7	893.4	888.1
37.5°	880.7	872.2	858.5	851.1	847.9
40°	839.4	833.1	818.3	809.8	805.6
42.5°	798.2	790.8	776.0	767.5	763.3
45°	753.8	749.6	735.8	723.1	717.9
47.5°	710.5	704.1	691.4	678.7	674.5
50°	666.1	660.8	647.0	635.4	629.1
52.5°	619.5	616.4	601.6	592.0	585.7
55°	572.0	570.9	557.2	545.5	540.2
57.5°	527.6	523.3	512.8	502.2	495.8
60°	478.9	477.9	465.2	455.7	450.4
62.5°	435.6	432.4	419.7	410.2	407.0
65°	390.1	384.8	374.3	365.8	362.6
67.5°	341.5	337.3	328.8	321.4	317.2
70°	298.1	291.8	285.5	278.1	272.8
72.5°	252.7	248.4	241.0	234.7	232.6
75°	206.2	201.9	198.8	193.5	190.3
77.5°	164.9	162.8	158.6	154.4	154.4
80°	124.8	121.6	119.5	118.4	118.4
82.5°	85.6	85.6	85.6	83.5	82.5
85°	55.0	52.9	52.9	50.7	50.7
87.5°	27.5	24.3	23.3	22.2	22.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)